



RWI Series Datasheet

SMD | Power Wirewound Resistors | Pulse Version | Ceramic core
Epoxy Encapsulation

ORDERING CODE - Example

New SAP Part Nr.:

RWI	502	J	K	-	13-	100R	AA
Serie	Size	Tol.	Pack-Code	TCR	Package type	R Value	Special
	502 = 5020	F = ±1% G = ±2% J = ±5%	K = Blister Tape	- Base on spec.	13- = 13 inch (Reel diameter)		AA = Standard

Historical VTM Part Nr.:

RWI	5020	J	K	-	13	100R
Type	Size	Tol.	K = Blister tape reel	TC	Reel diam.	R Value

APPLICATIONS



Automotive



Industrial



Power & Energy


FEATURES

Suitable for automatic pick and place
Best in class inrush current capability (IEC61000-4 5)
All welded construction
Small package size
Molded encapsulation
RoHs & REACH Compliant


ELECTRICAL SPECIFICATIONS

Type			RWI502
Historical Part Number			RWI5020
Nominal Power Rating	P ₂₅	[W]	3,0
	P ₇₀		2,2
Resistance Range		[Ω]	0R1 ... 220R (Other values upon request)
E-Series (preferred)			E24 (Other upon request)
Tolerances		±[%]	F = 1% ; G = 2% ; J = 5%
Working Temperature Range		[°C]	-55 ... +200
Thermal Resistance		[KW ⁻¹]	100
Max. Working Voltage		[V] _{RMS}	$\sqrt{P_{70} \times R}$
Dielectric Withstanding Voltage IEC115-1 clause 4.7 (1[min])		[V] _{RMS}	1000
Insulation Resistance IEC115-1 clause 4.6		[MΩ]	>1000

DIMENSIONS [mm]



SOLDER PAD




RWI Series Datasheet

PERFORMANCE DATA


Type		RWI502
Historical Part Number		RWI5020
Derating Linear	[°C]	70...200 (0W)
Climatic Category		55/200/56
Surge Test IEC61000-4-5 Internal impedance 12[Ω], 10 pulses, 20[s] interval	±[%]	2,0
Endurance IEC60115-1 clause 4.25 (P_{70} , @ 70[°C], 1000[h])	±[%]	1,0
Damp Heat, Steady State IEC60115-1 clause 4.24 (40[°C], 93[% r.h.], 56[d])	±[%]	0,25
Climatic Sequence IEC60115-1 clause 4.23	±[%]	0,25
Resistance to Soldering Heat IEC60115-1 clause 4.18 (260 ^{±5} [°C], 3,5 ^{±1} [s])	±[%]	0,25
Short Time Overload IEC60115-1 clause 4.13 ($U=5 \cdot \sqrt{P_{10}} \cdot R$, 5[s])	±[%]	1,0
Rapid change of temperature IEC115-1 clause 4.19 and IEC60068-2-14 (30 [min] -55 [°C] and 30 [min] +125 [°C])	±[%]	0,25
Board-bending test		No interruption
Solderability IEC60068-2-20 (245 ^{±5} [°C] 3 ^{±0,5} [s])		Solder bath method (> 95% coverage)
Marking IEC60062		Printed in clear (Type – Value – Tolerance)

PERFORMANCE GRAPHS


Derating – P₂₅



Derating – P₇₀




Temperature Rise




RWI Series Datasheet

PULSE PERFORMANCE


Energy Capability Graph (based on a wire temperature)




Maximum Pulse Voltage (IEC61000-4-5)



Maximum Pulse Power




Maximum Pulse Current




PACKAGING


The standard packaging for RWI dimensions below.



Type	A0	B0	W	D1	P	T2
RWI502	5,4	12,4	24	1,5	8	5



Type	W1	W2	N	A
RWI502	25,4	29,5	90	330



Type	Packaging	Pieces
RWI502	13(inch) Blister tape	1500

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

YAGEO:

[RWI502JK-13-100RAA](#) [RWI502JK-13-10RAA](#) [RWI502JK-13-1RAA](#) [RWI502JK-13-110RAA](#) [RWI502JK-13-11RAA](#)
[RWI502JK-13-120RAA](#) [RWI502JK-13-12RAA](#) [RWI502JK-13-130RAA](#) [RWI502JK-13-13RAA](#) [RWI502JK-13-150RAA](#)
[RWI502JK-13-15RAA](#) [RWI502JK-13-160RAA](#) [RWI502JK-13-16RAA](#) [RWI502JK-13-180RAA](#) [RWI502JK-13-18RAA](#)
[RWI502JK-13-1R1AA](#) [RWI502JK-13-1R2AA](#) [RWI502JK-13-1R3AA](#) [RWI502JK-13-1R5AA](#) [RWI502JK-13-1R6AA](#)
[RWI502JK-13-1R8AA](#) [RWI502JK-13-200RAA](#) [RWI502JK-13-20RAA](#) [RWI502JK-13-220RAA](#) [RWI502JK-13-22RAA](#)
[RWI502JK-13-24RAA](#) [RWI502JK-13-27RAA](#) [RWI502JK-13-2R2AA](#) [RWI502JK-13-2R4AA](#) [RWI502JK-13-2R7AA](#)
[RWI502JK-13-2RAA](#) [RWI502JK-13-30RAA](#) [RWI502JK-13-33RAA](#) [RWI502JK-13-36RAA](#) [RWI502JK-13-39RAA](#)
[RWI502JK-13-3R3AA](#) [RWI502JK-13-3R6AA](#) [RWI502JK-13-3R9AA](#) [RWI502JK-13-3RAA](#) [RWI502JK-13-43RAA](#)
[RWI502JK-13-47RAA](#) [RWI502JK-13-4R3AA](#) [RWI502JK-13-51RAA](#) [RWI502JK-13-56RAA](#) [RWI502JK-13-5R1AA](#)
[RWI502JK-13-5R6AA](#) [RWI502JK-13-62RAA](#) [RWI502JK-13-6R2AA](#) [RWI502JK-13-6R8AA](#) [RWI502JK-13-75RAA](#)
[RWI502JK-13-7R5AA](#) [RWI502JK-13-82RAA](#) [RWI502JK-13-8R2AA](#) [RWI502JK-13-91RAA](#) [RWI502JK-13-9R1AA](#)
[RWI502JK-13-R11AA](#) [RWI502JK-13-R12AA](#) [RWI502JK-13-R13AA](#) [RWI502JK-13-R15AA](#) [RWI502JK-13-R16AA](#)
[RWI502JK-13-R18AA](#) [RWI502JK-13-R1AA](#) [RWI502JK-13-R22AA](#) [RWI502JK-13-R24AA](#) [RWI502JK-13-R27AA](#)
[RWI502JK-13-R2AA](#) [RWI502JK-13-R33AA](#) [RWI502JK-13-R36AA](#) [RWI502JK-13-R39AA](#) [RWI502JK-13-R3AA](#)
[RWI502JK-13-R43AA](#) [RWI502JK-13-R47AA](#) [RWI502JK-13-R51AA](#) [RWI502JK-13-R56AA](#) [RWI502JK-13-R62AA](#)
[RWI502JK-13-R68AA](#) [RWI502JK-13-R75AA](#) [RWI502JK-13-R82AA](#) [RWI502JK-13-R91AA](#)