


Terminal Boards for Motion Control

For General Purpose

DIN-814-GP



Terminal Board for General Purpose with 100-pin SCSI-II connector

- Supports Specific Servos by Cable Selecting
- On-board Connector Type: 100-pin SCSI-II
- Dimensions: 146 mm x 85 mm x 44 mm (W x L x H)
- Mating Cable:
 - ♦ ACL-102100-1: 100-pin SCSI-II cable, 1 M

DIN-100S-01



Terminal Board with One 100-pin SCSI-II Connector and DIN-rail Mounting

- On-board Connector Type: 100-pin SCSI-II female
- Dimensions: 158 mm x 120 mm x 52 mm (W x L x H)
- Mating Cable:
 - ♦ ACL-102100-1: 100-pin SCSI-II cable, 1 M

DIN-68S-01



Terminal Board with One 68-pin SCSI-II Connector and DIN-rail Mounting

- On-board Connector Type: 68-pin SCSI-II female
- Dimensions: 103 mm x 85 mm x 46.2 mm (W x L x H)
- Mating Cables:
 - ♦ ACL-10568-1: 68-pin SCSI-VHDCI cable, 1 M
 - ♦ ACL-10569-1: 68-pin SCSI-II cable, 1 M

DIN-50S-01



Terminal Board with One 50-pin SCSI-II Connector and DIN-rail Mounting

- On-board Connector Type: 50-pin SCSI-II female
- Plastic cover for protection of wiring
- Dimensions: 125 mm x 85 mm x 50 mm (W x L x H)
- Mating Cable:
 - ♦ ACL-10250-1: 50-pin SCSI-II cable, 1 M

Cable Accessories

HSL-4XMO-DM Cable

- For Mitsubishi MR-J2S-A servo amplifiers
- Available for 1 M, 2 M, 3 M



4XMO-DA Cable M

- For Delta A2 servo series
- Available for 3 M



HSL-4XMO-DP Cable

- For Panasonic MINAS A4 servo amplifier with brake control
- Available for 1 M, 1.5 M, 2 M



SCSI-VHDCI 100P Cable

- SCSI-VHDCI 100-pin cable
- Compliant with PCI-8158
- Available for 2 M, 3 M



HSL-4XMO-DY Cable

- For Yaskawa Sigma II/III/IV servo amplifier
- Available for 1 M, 2 M, 3 M



MR-JCCBL M

- Encoder cable (for KFS series)
- Available for 2 M, 5 M



4XMO-DM-J3

- For Mitsubishi MR-J3 servo amplifiers
- Available for 2 M



MR-JHSCBL M

- Encoder cable (for SFS series)
- Available for 2 M, 5 M



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADLINK Technology:](#)

[DIN-814-GP](#)