

# MXC-6000 Series

Powerful Intel® Core™ i7 Processor-based Fanless Expandable Embedded Computer with PCI/PCIe Slots



## Introduction

The Matrix MXC-6000 series of powerful fanless, expandable embedded computers feature the Intel® Core i7 2.0 GHz processor for maximized computing. The MXC-6000 inherits its exceptional fanless and cable-free design from ADLINK's existing Matrix C series.

The MXC-6000 series' Intel® Core i7 2.0 GHz processor and Intel® QM57 chipset deliver a level of performance ideal for image and vision measurement and automation applications. PCI and PCIe slots allow integration of off-the-shelf PCI/PCIe cards for development of configurable application platforms. 16 built-in isolated DIO channels enable standardized industrial control. A DVI-I connector output on the front panel allows direct connection to a LCD panel, and one eSATA port supports storage expansion or hot-swapping SATA drives.

Leveraging a reliable fanless and durable cable-free design, the MXC-6000 series exhibits excellent dependability in harsh environments, where severe temperature variation and vibration may exist. The MXC-6000 series provides an optional hot-pluggable fan module to dissipate heat generated within the system when high power consumption PCI/PCIe cards are installed. This inventive mechanical design retains a cable-free structure which dramatically improves thermal stability when PCI/PCIe cards are installed.

The MXC-6000 also provides a USB 2.0 port internally located on a riser card, enabling heightened reliability for secure applications, with license keys or password encryption on an internal USB dongle dramatically improve system security. Combining a reliable design with computing power and innovative features, the Matrix MXC-6000 series is the optimal choice on which to base any rugged application system.

\*Extending the operating temperature is optional and requires use of an industrial solid-state drive storage device. Heat dissipation from inserted PCI/PCIe cards may affect thermal performance

## Features

- Intel® Core i7-620LE 2.0 GHz processor + Intel® QM57 chipset
- Configurable, providing PCI and PCIe x4 slots
- Rugged, -10°C to 60°C (-14°F to 140°F) fanless operation\*
- Built-in 9 Vdc to 32 Vdc wide-range DC power input
- VGA+DVI-D display by DVI-I connector
- Dual 1000/100/10 Mbps Ethernet ports, 2 RS-232 ports and 2 software-selectable RS-232/422/485 ports
- USB 2.0 port internally on riser card, built-in 16-CH isolated DI and 16-CH isolated DO
- RAID 0, 1 function available through 2 internal SATA-connected HDD or one internal SATA-connected HDD and one external eSATA-connected HDD

## Applications

- Machine Automation / Factory Automation
- Image & Vision Measurement
- Test Instrumentation
- Safety Surveillance

## Software Support

### ■ OS Information

- Windows® XP/XP Embedded/7
- Linux\*
- INtime\*

\*Linux Distribution by Request

\*Custom BIOS is necessary to support INtime\*

### ■ Easy-to-install Hot-pluggable Fan Module



1. Undo the thumbscrew by hand



2. Withdraw the thumbscrew and remove the top cover




3. Replace it by plugging the hot-pluggable fan module cover into the fan connector on CPU board

### ■ A More Reliable Design of Internal USB Port




The Matrix internal USB 2.0 port provides increased application security with connectivity for license keys or password encryption on USB dongle.

### ■ MXC-6000 Series Front Panel



### ■ Inside of the MXC-6000 Series



## Specifications

Model Name	MXC-6101D		MXC-6201D
System Core			
■ Processor	Intel® Core i7-620LE 2.0 GHz CPU		
■ Chipset	Intel® QM57		
■ Video	VGA+DVI display by DVI-I connector <ul style="list-style-type: none"><li>• Analog CRT, supports QXGA (2048 x 1536) resolution</li><li>• DVI-I 1.0 (DVI + VGA) (with external cable for connecting DVI-I connector to DVI-D and VGA device)</li><li>• Optional 48-bit LVDS (by Internal box header)</li></ul>		
■ Memory	2 GB DDR3 800/1066 MHz SODIMM module (Max. capacity 4 GB SODIMM module option)		
I/O Interface			
■ Expansion Slots	2 PCI slots	1 PCI slot and 1 PCIe x4 slot	
■ Ethernet	2 GbE ports (2 Intel® 82574L)		
■ Serial Port	2 software-programmable RS-232/422/485 (COM1 & COM2) 2 RS-232 (COM3 & COM4)		
■ USB	4 USB 2.0 ports (external), 1 USB 2.0 port (internal)		
■ Audio	1 mic-in and 1 line-out		
■ KB/MS	1 PS/2 keyboard and 1 PS/2 mouse		
■ DIO	16-CH isolated DI + 16-CH isolated DO		
■ WDT	Supports a watchdog timer		
Power Supply			
■ DC Input	AT/ATX, built-in 9-32 Vdc wide-range DC power input 3P pluggable connector with latch (GND, V-, V+)		
■ AC Input	Optional 100 W external AC-DC adapter for AC input		
Storage Device			
■ SATA HDD	On-board SATA port for 2.5" HDD/SSD installation Support SATA RAID 0, 1		
■ CompactFlash	1 external type II CompactFlash socket 1 internal type II CompactFlash socket		
■ eSATA	1 eSATA interface connector for external storage expansion		
Mechanical			
■ Optional Fan Module	Optional hot-pluggable fan module for dissipating heat generated by PCI/PCIe card		
■ Dimensions	130 mm (W) x 225 mm (D) x 183 mm (H) (5.1" x 8.9" x 7.2")		
■ Weight	3.5 kg (7.72 lbs)		
■ Mounting	Wall-mount kit		
Environmental			
■ Operating Temperature*	Standard: 0°C to 50°C (32°F to 122°F) Extended temperature option*: -10°C to 60°C (-14°F to 140°F) (w/industrial SSD)		
■ Storage Temperature	-40°C to 85°C (-40°F to 185°F) (excl. HDD/SSD/CF)		
■ Humidity	~95% @ 40°C (104°F) (non-condensing)		
■ Vibration	Operating, 5 Grms, 5-500 Hz, 3 axes (w/ CF or SSD) Operating, 0.5 Grms, 5-500 Hz, 3 axes (w/ HDD)		
■ Shock	Operating, 50 G, Half sine 11 ms duration (w/ CF or SSD)		
■ EMC	CE and FCC Class A		

\*Without PCI/PCIe card installation.

## Ordering Information

Model Name	Description	PCI	PCIe x4	GbE	eSATA	COM	USB	Memory	DIO
MXC-6101D	Intel® Core i7-620LE 2.0 GHz fanless expandable embedded computer	2	0	2	1	4	5	2 GB DDR3	16 DI + 16 DO
MXC-6201D	Intel® Core i7-620LE 2.0 GHz fanless expandable embedded computer	1	1	2	1	4	5	2 GB DDR3	16 DI + 16 DO

## Optional Accessories

MXC-6000 Optional Fan Module	Optional Fan module fan module for the MXC-6000 series
4 GB DDR3 Upgrade	Upgrade to 4 GB DDR3 memory
500 GB HDD Option	Factory-installed 500 GB SATA hard disk drive (0°C to 60°C, 32°F to 140°F)
32/64/128 GB SSD Option	Factory-installed 32/64/128 GB SATA solid-state drive (0°C to 70°C, 32°F to 158°F)
100 W AC-DC Adapter	100 W industrial-grade AC-DC adapter (-20°C to 70°C, -4°F to 158°F)
90 W AC-DC Adapter	90 W commercial grade AC-DC adapter (0°C to 50°C, 32°F to 122°F)
Extended Temperature Option*	Optional Screening to extend the operating temperature of the MXC-6000 series to -10°C to 60°C (-14°F to 140°F)

\*For more options regarding display and COM port cables, please refer to page 1-28.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## ADLINK Technology:

[MXC-6201D/SSD32G-M](#) [MXC-6101D/HDD320G](#) [MXC-6201D/HDD320G](#) [MXC-6201D/M4G/HDD320G](#) [MXC-6101D/M4G](#) [MXC-6201D/M4G](#) [MXC-6201D/Fan](#) [MXC-6101D/Fan](#) [MXC-6101D](#) [MXC-6201D](#) [100W-AC-ADAPTER-MATRIX](#)