



STC-SLAC SERIES


The STC-SLAC Series surge suppressor is specifically designed to protect sensitive electronics that contain both low-voltage control circuit signal lines and 120 volt AC Power. It combines the technologies found in the STC-642 signal line protector and the STC-HSP advanced three-stage hybrid solid state power line protector. The rugged waterproof NEMA 4X polycarbonate enclosure is suited for installation in the most severe environments.

APPLICATIONS

- Water treatment facilities
- Industrial manufacturing plant
- Chemical processing plants
- Wastewater treatment facilities
- Agricultural (farms and processing)
- Fish hatcheries
- Food processing

- Internal replaceable fuse
- Screw terminals for ease in serviceability
- Five year limited warranty

CERTIFICATIONS AND COMPLIANCES

-  Listed
— UL 497B
- RoHS Compliant

FEATURES

- Surge suppression for AC power and low-voltage signal lines
- Series hybrid AC suppressor/filter
- User-replaceable protection modules
- 15 Amps replaceable fuse for AC module
- Test jacks for signal line monitoring
- “Power ON” LED indicator

SELECTION TABLE

Catalog Number	Description
STCSLAC12036	Surge Suppressor (STC-642 signal line protector and the STC-HSP module)
STCHSP121BT1RU	Replacement AC module
STC642036	Replacement signal line module

SOLAHD

For product information:
www.solahd.com
1.800.377.4384



CONSIDER IT SOLVED™

SPECIFICATIONS

Description	AC Power	
Technology	Three-Stage Series Hybrid	
SPD Technology	GDT/PTC/SAD	
Voltage Clamp	325 Vac	
Input Voltage	120 Vac 50/60 Hz	
Output Voltage	15 Amps Max.	
Response Time	<5 nanoseconds	
Maximum Surge Current (8x20 μs)	39 kA	
Parameter	Normal Mode (L-N)	Common Mode (L-G) (N-G)
IEEE 587 CAT A Ring *	172 V	280 V
IEEE 587 CAT B Ring *	205 V	
IEEE 587 CAT B Impulse *	330 V	
Certification	UL 1449, Type 2	
Description	Signal Line	
Technology	Three Stage Series Hybrid	
Peak Surge Current (8x20 μs)	10 kA	
Response Time	<5 nanoseconds	
Voltage Clamp	36 Volts	
Maximum Current	150 mA	
Series Resistance	5 Ohms (typical)	
Certification	UL 497B	

* Measured from zero volts, to 90° Phase angle

SYSTEM DESIGN



SOLAHD

United States: 1.800.377.4384 | Asia/Pacific: + 65.6891.7600 | Australia: + 61.3.9721.0387
 Brazil: São Paulo/SP + 55.11.2122.5777 | Brazil: Camaçari/BA + 55.71.3496.4427 | Canada: + 1.888.765.2226
 China: + 86.21.3418.3888 | Europe: + 33.3.2254.1390 | Mexico/Latin America: + 52.55.5809.5049
 Middle East/Africa/India: + 971.4.811.8100
www.solahd.com

EMERSON

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SolaHD:

[SLAC32036LC](#) [SLAC02036LC](#)