

Surface Mount Multilayer Ceramic Chip Capacitors for High Frequency



FEATURES

- Case size 0402, 0505, 0603, 0805, 1111, 2525, and 3838
- High frequency
- Ultra-stable, high Q dielectric material
- Non-magnetic copper termination "C"
- Lead (Pb)-free terminations code "X"
- Tin / lead termination code "L"
- Surface mount, wet build process
- Reliable Noble Metal Electrode (NME) system
- Made with a combination of design, materials, and tight process control to achieve very high field reliability
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



Available

RoHS*
Available

HALOGEN
FREE
GREEN
(5-2008)
Available

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

LINKS TO ADDITIONAL RESOURCES



Design Tools



S-Parameters



Simulation Tools



Infographics



Videos



Related Documents

APPLICATIONS

- RF and microwave instruments
- Base stations
- Wireless devices
- Broadband communication
- Medical instrumentation and test
- Military devices (radar, communication, etc.)
- Satellite communication

ELECTRICAL SPECIFICATIONS

Note

- Electrical characteristics at 25 °C unless otherwise specified

Operating Temperature:

-55 °C to +125 °C

Capacitance Range:

0402: 0.1 pF to 82 pF

0505: 0.1 pF to 1.0 nF

0603: 0.1 pF to 470 pF

0805: 0.1 pF to 1.0 nF

1111: 0.2 pF to 3.3 nF

2525: 1.0 pF to 3.0 nF

3838: 1.0 pF to 12 nF

Voltage Rating:

0402: 25 V_{DC} to 200 V_{DC}

0505: 50 V_{DC} to 250 V_{DC}

0603: 25 V_{DC} to 250 V_{DC}

0805: 25 V_{DC} to 500 V_{DC}

1111: 50 V_{DC} to 1500 V_{DC}

2525: 300 V_{DC} to 3600 V_{DC}

3838: 300 V_{DC} to 7200 V_{DC}

Temperature Coefficient of Capacitance (TCC):

C0G (D): 0 ppm/°C ± 30 ppm/°C from -55 °C to +125 °C with zero (0) V_{DC} applied

Dissipation Factor (DF):

C0G (D): 0.05 % max. at 1.0 V_{RMS} and 1 MHz
for values ≤ 1000 pF

C0G (D): 0.05 % max. at 1.0 V_{RMS} and 1 kHz
for values > 1000 pF

Aging Rate: 0 % maximum per decade

Insulation Resistance (IR):

at +25 °C and rated voltage 100 000 MΩ minimum or 1000 ΩF, whichever is less

at +125 °C and rated voltage 10 000 MΩ minimum or 100 ΩF, whichever is less

Dielectric Strength Test:

performed per method 103 of EIA-198-2-E.

Applied test voltages:

≤ 250 V_{DC}-rated: min. 200 % of rated voltage

> 250 V_{DC}-rated: min. 150 % of rated voltage
1500 V_{DC} and up: 120 % rated voltage



QUICK REFERENCE DATA

DIELECTRIC	CASE	MAXIMUM VOLTAGE (V)	CAPACITANCE	
			MINIMUM	MAXIMUM
D = HIFREQ	0402	200	0.1 pF	82 pF
	0505	250	0.1 pF	1 nF
	0603	250	0.1 pF	470 pF
	0805	500	0.1 pF	1.0 nF
	1111	1500	0.2 pF	3.3 nF
	2525	3600	1.0 pF	3 nF
	3838	7200	1.0 pF	12 nF

ORDERING INFORMATION


VJ0603	D	101	J	X	A	A	T
CASE CODE	DIELECTRIC	CAPACITANCE NOMINAL CODE	CAPACITANCE TOLERANCE	TERMINATION	DC VOLTAGE RATING ⁽¹⁾	MARKING	PACKAGING ⁽⁴⁾
0402 0505 0603 0805 1111 2525 3838	D = HIFREQ	Expressed in picofarads (pF). The first two digits are significant, the third is a multiplier. An "R" indicates a decimal point. Examples: 1R0 = 1.0 pF	V = ± 0.05 pF B = ± 0.10 pF C = ± 0.25 pF D = ± 0.50 pF F = ± 1 % G = ± 2 % J = ± 5 % K = ± 10 % M = ± 20 % Note Details see "Selection Chart"	X = Ni barrier 100 % tin plate matte finish C = non-magnetic copper barrier 100 % tin plate matte finish E = AgPd ⁽²⁾ L = Ni barrier with tin lead plated finish min. 4 % lead	X = 25 V A = 50 V B = 100 V K = 150 V C = 200 V P = 250 V D = 300 V E = 500 V L = 630 V I = 800 V G = 1000 V R = 1500 V F = 2000 V O = 2500 V H = 3000 V W = 3600 V M = 5000 V S = 7200 V	A = unmarked ⁽³⁾ Q = marked	T = 7" reel / plastic tape C = 7" reel / paper tape O = 7" reel / flamed paper tape J = 7" reel (low quantity) R = 11 1/4" / 13" reel / plastic tape P = 11 1/4" / 13" reel / paper tape I = 11 1/4" / 13" reel / flamed paper tape W = waffle pack Note "I" and "O" is used for "E" termination code

Notes

- (1) DC voltage rating should not be exceeded in application
(2) Termination code "E" is for conductive epoxy assembly - only available for EIA case sizes 0402, 0603, and 0805
(3) Case size 0402 only available with "A"
(4) See "Standard Packaging Quantities" table

ENVIRONMENTAL STATUS

TERMINATION CODE	TERMINATION DESCRIPTION	RoHS COMPLIANT	VISHAY GREEN
C	Non-magnetic copper barrier 100 % tin plated matte finish	Yes	Yes
X	Ni barrier 100 % tin plated matte finish	Yes	Yes
E	AgPd	Yes	Yes
L	Ni barrier tin lead plated with min. 4 % lead	No	No

DIMENSIONS in inches (millimeters)


CASE CODE	STYLE	LENGTH (L)	WIDTH (W)	MAXIMUM THICKNESS (T)	TERMINATIONS PAD (P)	
					MINIMUM	MAXIMUM ⁽¹⁾
0402	VJ0402	0.040 ± 0.004 (1.02 ± 0.10)	0.020 ± 0.004 (0.51 ± 0.10)	0.024 (0.61)	0.004 (0.10)	0.016 (0.41)
0505	VJ0505	0.055 + 0.015 / - 0.010 (1.40 + 0.382 / - 0.254)	0.055 ± 0.015 (1.40 ± 0.38)	0.057 (1.45)	0.004 (0.10)	0.016 (0.41)
0603	VJ0603	0.063 ± 0.006 (1.60 ± 0.15)	0.031 ± 0.005 (0.80 ± 0.12)	0.037 (0.94)	0.010 (0.25)	0.022 (0.55)
0805	VJ0805	0.079 ± 0.008 (2.00 ± 0.20)	0.049 ± 0.008 (1.25 ± 0.20)	0.057 (1.45)	0.010 (0.25)	0.030 (0.76)
1111	VJ1111	0.117 + 0.015 / - 0.010 (2.98 + 0.382 / - 0.254)	0.110 + 0.015 / - 0.020 (2.79 + 0.382 / - 0.509)	0.102 (2.59)	0.012 (0.30)	0.018 ⁽²⁾ (0.46)
2525	VJ2525	0.250 + 0.020 / - 0.025 (6.35 + 0.508 / - 0.63)	0.250 ± 0.015 (6.35 ± 0.381)	0.102 (2.59)	0.010 (0.25)	0.030 (0.76)
3838	VJ3838	0.381 ± 0.015 (9.7 ± 0.40)	0.381 + 0.017 / - 0.015 (9.7 + 0.45 / - 0.40)	0.118 (3.00)	0.010 (0.25)	0.030 (0.76)

Notes

- (1) For Cu termination "C" add 0.01 mm to maximum pad terminations
(2) For Cu termination "C" case size 1111 add 0.17 mm to maximum pad termination



SELECTION CHART						
DIELECTRIC (VISHAY CODE)		C0G (D)				
STYLE		VJ0402				
CASE CODE		0402				
VOLTAGE (V _{DC})		25	50	100	200	TOLERANCE
VOLTAGE CODE		X	A	B	C	
CAP. CODE	CAP.					
0R1	0.1 pF	••	••	••	••	V, B, C, D
0R2	0.2 pF	••	••	••	••	V, B, C, D
0R3	0.3 pF	••	••	••	••	V, B, C, D
0R4	0.4 pF	••	••	••	••	V, B, C, D
0R5	0.5 pF	••	••	••	••	V, B, C, D
0R6	0.6 pF	••	••	••	••	V, B, C, D
0R7	0.7 pF	••	••	••	••	V, B, C, D
0R8	0.8 pF	••	••	••	••	V, B, C, D
0R9	0.9 pF	••	••	••	••	V, B, C, D
1R0	1.0 pF	••	••	••	••	V, B, C, D
1R1	1.1 pF	••	••	••	••	V, B, C, D
1R2	1.2 pF	••	••	••	••	V, B, C, D
1R3	1.3 pF	••	••	••	••	V, B, C, D
1R4	1.4 pF	••	••	••	••	V, B, C, D
1R5	1.5 pF	••	••	••	••	V, B, C, D
1R6	1.6 pF	••	••	••	••	V, B, C, D
1R7	1.7 pF	••	••	••	••	V, B, C, D
1R8	1.8 pF	••	••	••	••	V, B, C, D
1R9	1.9 pF	••	••	••	••	V, B, C, D
2R0	2.0 pF	••	••	••	••	V, B, C, D
2R1	2.1 pF	••	••	••	••	V, B, C, D
2R2	2.2 pF	••	••	••	••	V, B, C, D
2R4	2.4 pF	••	••	••	••	V, B, C, D
2R7	2.7 pF	••	••	••	••	V, B, C, D
3R0	3.0 pF	••	••	••	••	V, B, C, D
3R3	3.3 pF	••	••	••	••	V, B, C, D
3R6	3.6 pF	••	••	••	••	V, B, C, D
3R9	3.9 pF	••	••	••	••	V, B, C, D
4R3	4.3 pF	••	••	••	••	V, B, C, D
4R7	4.7 pF	••	••	••	••	V, B, C, D
5R1	5.1 pF	••	••	••	••	V, B, C, D
5R6	5.6 pF	••	••	••	••	V, B, C, D
6R2	6.2 pF	••	••	••	••	V, B, C, D
6R8	6.8 pF	••	••	••	••	V, B, C, D
7R5	7.5 pF	••	••	••	••	V, B, C, D
8R2	8.2 pF	••	••	••	••	V, B, C, D
9R1	9.1 pF	••	••	••	••	V, B, C, D

Notes

•• RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"

•• Paper carrier

- For soldering conditions see Vishay Soldering Recommendations www.vishay.com/doc?45034



SELECTION CHART						
DIELECTRIC (VISHAY CODE)		C0G (D)				
STYLE		VJ0402				
CASE CODE		0402				
VOLTAGE (V _{DC})		25	50	100	200	TOLERANCE
VOLTAGE CODE		X	A	B	C	
CAP. CODE	CAP.					
100	10 pF	••	••	••	••	F, G, J, K, M
110	11 pF	••	••	••	••	F, G, J, K, M
120	12 pF	••	••	••	••	F, G, J, K, M
130	13 pF	••	••	••	••	F, G, J, K, M
150	15 pF	••	••	••	••	F, G, J, K, M
180	18 pF	••	••	••	••	F, G, J, K, M
200	20 pF	••	••	••	••	F, G, J, K, M
220	22 pF	••	••	••	••	F, G, J, K, M
240	24 pF	••	••	••	••	F, G, J, K, M
270	27 pF	••	••	••	••	F, G, J, K, M
300	30 pF	••	••			F, G, J, K, M
330	33 pF	••	••			F, G, J, K, M
360	36 pF	••	••			F, G, J, K, M
390	39 pF	••	••			F, G, J, K, M
430	43 pF	••	••			F, G, J, K, M
470	47 pF	••	••			F, G, J, K, M
510	51 pF	••	••			F, G, J, K, M
560	56 pF	••	••			F, G, J, K, M
620	62 pF	••				F, G, J, K, M
680	68 pF	••				F, G, J, K, M
750	75 pF	••				F, G, J, K, M
820	82 pF	••				F, G, J, K, M
910	91 pF					
101	100 pF					
111	110 pF					
121	120 pF					

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"
- Paper carrier
- For soldering conditions see Vishay Soldering Recommendations www.vishay.com/doc245034



SELECTION CHART							
DIELECTRIC (VISHAY CODE)		C0G (D)					
STYLE		VJ0505					
CASE CODE		0505					
VOLTAGE (V _{DC})		50	100	150	200	250	TOLERANCE
VOLTAGE CODE		A	B	K	C	P	
CAP. CODE	CAP.						
0R1	0.1 pF	•	•	•	•	•	V, B, C, D
0R2	0.2 pF	•	•	•	•	•	V, B, C, D
0R3	0.3 pF	•	•	•	•	•	V, B, C, D
0R4	0.4 pF	•	•	•	•	•	V, B, C, D
0R5	0.5 pF	•	•	•	•	•	V, B, C, D
0R6	0.6 pF	•	•	•	•	•	V, B, C, D
0R7	0.7 pF	•	•	•	•	•	V, B, C, D
0R8	0.8 pF	•	•	•	•	•	V, B, C, D
0R9	0.9 pF	•	•	•	•	•	V, B, C, D
1R0	1.0 pF	•	•	•	•	•	V, B, C, D
1R1	1.1 pF	•	•	•	•	•	V, B, C, D
1R2	1.2 pF	•	•	•	•	•	V, B, C, D
1R3	1.3 pF	•	•	•	•	•	V, B, C, D
1R4	1.4 pF	•	•	•	•	•	V, B, C, D
1R5	1.5 pF	•	•	•	•	•	V, B, C, D
1R6	1.6 pF	•	•	•	•	•	V, B, C, D
1R7	1.7 pF	•	•	•	•	•	V, B, C, D
1R8	1.8 pF	•	•	•	•	•	V, B, C, D
1R9	1.9 pF	•	•	•	•	•	V, B, C, D
2R0	2.0 pF	•	•	•	•	•	V, B, C, D
2R1	2.1 pF	•	•	•	•	•	V, B, C, D
2R2	2.2 pF	•	•	•	•	•	V, B, C, D
2R4	2.4 pF	•	•	•	•	•	V, B, C, D
2R7	2.7 pF	•	•	•	•	•	V, B, C, D
3R0	3.0 pF	•	•	•	•	•	V, B, C, D
3R3	3.3 pF	•	•	•	•	•	V, B, C, D
3R6	3.6 pF	•	•	•	•	•	V, B, C, D
3R9	3.9 pF	•	•	•	•	•	V, B, C, D
4R3	4.3 pF	•	•	•	•	•	V, B, C, D
4R7	4.7 pF	•	•	•	•	•	V, B, C, D
5R1	5.1 pF	•	•	•	•	•	V, B, C, D
5R6	5.6 pF	•	•	•	•	•	B, C, D
6R2	6.2 pF	•	•	•	•	•	B, C, D
6R8	6.8 pF	•	•	•	•	•	B, C, D
7R5	7.5 pF	•	•	•	•	•	B, C, D
8R2	8.2 pF	•	•	•	•	•	B, C, D
9R1	9.1 pF	•	•	•	•	•	B, C, D
100	10 pF	•	•	•	•	•	F, G, J, K, M
110	11 pF	•	•	•	•	•	F, G, J, K, M
120	12 pF	•	•	•	•	•	F, G, J, K, M
130	13 pF	•	•	•	•	•	F, G, J, K, M
150	15 pF	•	•	•	•	•	F, G, J, K, M
160	16 pF	•	•	•	•	•	F, G, J, K, M
180	18 pF	•	•	•	•	•	F, G, J, K, M

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"
- Plastic carrier tape
- For soldering conditions see Vishay Soldering Recommendations www.vishay.com/doc?45034



SELECTION CHART							
DIELECTRIC (VISHAY CODE)		C0G (D)					
STYLE		VJ0505					
CASE CODE		0505					
VOLTAGE (V _{DC})		50	100	150	200	250	TOLERANCE
VOLTAGE CODE		A	B	K	C	P	
CAP. CODE	CAP.						
200	20 pF	•	•	•	•	•	F, G, J, K, M
220	22 pF	•	•	•	•	•	F, G, J, K, M
240	24 pF	•	•	•	•	•	F, G, J, K, M
270	27 pF	•	•	•	•	•	F, G, J, K, M
300	30 pF	•	•	•	•	•	F, G, J, K, M
330	33 pF	•	•	•	•	•	F, G, J, K, M
360	36 pF	•	•	•	•	•	F, G, J, K, M
390	39 pF	•	•	•	•	•	F, G, J, K, M
430	43 pF	•	•	•	•	•	F, G, J, K, M
470	47 pF	•	•	•	•	•	F, G, J, K, M
510	51 pF	•	•	•	•	•	F, G, J, K, M
560	56 pF	•	•	•	•	•	F, G, J, K, M
620	62 pF	•	•	•	•	•	F, G, J, K, M
680	68 pF	•	•	•	•	•	F, G, J, K, M
750	75 pF	•	•	•	•		F, G, J, K, M
820	82 pF	•	•	•	•		F, G, J, K, M
910	91 pF	•	•	•	•		F, G, J, K, M
101	100 pF	•	•	•	•		F, G, J, K, M
111	110 pF	•	•	•	•		F, G, J, K, M
121	120 pF	•	•	•	•		F, G, J, K, M
131	130 pF	•	•	•	•		F, G, J, K, M
151	150 pF	•	•	•	•		F, G, J, K, M
161	160 pF	•	•	•	•		F, G, J, K, M
181	180 pF	•	•	•	•		F, G, J, K, M
201	200 pF	•	•	•	•		F, G, J, K, M
221	220 pF	•	•	•	•		F, G, J, K, M
241	240 pF	•	•	•	•		F, G, J, K, M
271	270 pF	•	•	•			F, G, J, K, M
301	300 pF	•	•	•			F, G, J, K, M
331	330 pF	•	•	•			F, G, J, K, M
361	360 pF	•	•	•			F, G, J, K, M
391	390 pF	•	•	•			F, G, J, K, M
431	430 pF	•	•	•			F, G, J, K, M
471	470 pF	•	•	•			F, G, J, K, M
511	510 pF	•					F, G, J, K, M
561	560 pF	•					F, G, J, K, M
621	620 pF	•					F, G, J, K, M
681	680 pF	•					F, G, J, K, M
751	750 pF	•					F, G, J, K, M
821	820 pF	•					F, G, J, K, M
911	910 pF	•					F, G, J, K, M
102	1000 pF	•					F, G, J, K, M
112	1100 pF						
122	1200 pF						

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"
- Plastic carrier tape
- For soldering conditions see Vishay Soldering Recommendations www.vishay.com/doc?45034



SELECTION CHART							
DIELECTRIC (VISHAY CODE)		C0G (D)					
STYLE		VJ0603					
CASE CODE		0603					
VOLTAGE (V _{DC})		25	50	100	200	250	TOLERANCE
VOLTAGE CODE		X	A	B	C	P	
CAP. CODE	CAP.						
0R1	0.1 pF	••	••	••	••	••	V, B, C, D
0R2	0.2 pF	••	••	••	••	••	V, B, C, D
0R3	0.3 pF	••	••	••	••	••	V, B, C, D
0R4	0.4 pF	••	••	••	••	••	V, B, C, D
0R5	0.5 pF	••	••	••	••	••	V, B, C, D
0R6	0.6 pF	••	••	••	••	••	V, B, C, D
0R7	0.7 pF	••	••	••	••	••	V, B, C, D
0R8	0.8 pF	••	••	••	••	••	V, B, C, D
0R9	0.9 pF	••	••	••	••	••	V, B, C, D
1R0	1.0 pF	••	••	••	••	••	V, B, C, D
1R1	1.1 pF	••	••	••	••	••	V, B, C, D
1R2	1.2 pF	••	••	••	••	••	V, B, C, D
1R3	1.3 pF	••	••	••	••	••	V, B, C, D
1R4	1.4 pF	••	••	••	••	••	V, B, C, D
1R5	1.5 pF	••	••	••	••	••	V, B, C, D
1R6	1.6 pF	••	••	••	••	••	V, B, C, D
1R7	1.7 pF	••	••	••	••	••	V, B, C, D
1R8	1.8 pF	••	••	••	••	••	V, B, C, D
1R9	1.9 pF	••	••	••	••	••	V, B, C, D
2R0	2.0 pF	••	••	••	••	••	V, B, C, D
2R1	2.1 pF	••	••	••	••	••	V, B, C, D
2R2	2.2 pF	••	••	••	••	••	V, B, C, D
2R4	2.4 pF	••	••	••	••	••	V, B, C, D
2R7	2.7 pF	••	••	••	••	••	V, B, C, D
3R0	3.0 pF	••	••	••	••	••	V, B, C, D
3R3	3.3 pF	••	••	••	••	••	V, B, C, D
3R6	3.6 pF	••	••	••	••	••	V, B, C, D
3R9	3.9 pF	••	••	••	••	••	V, B, C, D
4R3	4.3 pF	••	••	••	••	••	V, B, C, D
4R7	4.7 pF	••	••	••	••	••	V, B, C, D
5R1	5.1 pF	••	••	••	••	••	V, B, C, D
5R6	5.6 pF	••	••	••	••	••	V, B, C, D
6R2	6.2 pF	••	••	••	••	••	V, B, C, D
6R8	6.8 pF	••	••	••	••	••	V, B, C, D
7R5	7.5 pF	••	••	••	••	••	V, B, C, D
8R2	8.2 pF	••	••	••	••	••	V, B, C, D
9R1	9.1 pF	••	••	••	••	••	V, B, C, D
100	10 pF	••	••	••	••	••	F, G, J, K, M
110	11 pF	••	••	••	••	••	F, G, J, K, M
120	12 pF	••	••	••	••	••	F, G, J, K, M
130	13 pF	••	••	••	••	••	F, G, J, K, M
150	15 pF	••	••	••	••	••	F, G, J, K, M
180	18 pF	••	••	••	••	••	F, G, J, K, M
200	20 pF	••	••	••	••	••	F, G, J, K, M
220	22 pF	••	••	••	••	••	F, G, J, K, M

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"
- Paper carrier • Plastic carrier tape
- For case size 0603: Cu termination "C" is only available in plastic carrier tape
- For soldering conditions see Vishay Soldering Recommendations www.vishay.com/doc?45034



SELECTION CHART							
DIELECTRIC (VISHAY CODE)		C0G (D)					
STYLE		VJ0603					
CASE CODE		0603					
VOLTAGE (V _{DC})		25	50	100	200	250	TOLERANCE
VOLTAGE CODE		X	A	B	C	P	
CAP. CODE	CAP.						
240	24 pF	••	••	••	••	••	F, G, J, K, M
270	27 pF	••	••	••	••	••	F, G, J, K, M
300	30 pF	••	••	••	••	••	F, G, J, K, M
330	33 pF	••	••	••	••	••	F, G, J, K, M
360	36 pF	••	••	••	••	••	F, G, J, K, M
390	39 pF	••	••	••	••	••	F, G, J, K, M
430	43 pF	••	••	••	••	••	F, G, J, K, M
470	47 pF	••	••	••	••	••	F, G, J, K, M
510	51 pF	••	••	••	••	••	F, G, J, K, M
560	56 pF	••	••	••	••	••	F, G, J, K, M
620	62 pF	•	•	•	•	•	F, G, J, K, M
680	68 pF	•	•	•	•	•	F, G, J, K, M
750	75 pF	•	•	•	•	•	F, G, J, K, M
820	82 pF	•	•	•	•	•	F, G, J, K, M
910	91 pF	•	•	•	•	•	F, G, J, K, M
101	100 pF	•	•	•	•	•	F, G, J, K, M
111	110 pF	•	•	•			F, G, J, K, M
121	120 pF	•	•	•			F, G, J, K, M
131	130 pF	•	•	•			F, G, J, K, M
151	150 pF	•	•	•			F, G, J, K, M
181	180 pF	•	•				F, G, J, K, M
201	200 pF	•	•				F, G, J, K, M
221	220 pF	•	•				F, G, J, K, M
241	240 pF	•	•				F, G, J, K, M
271	270 pF	•	•				F, G, J, K, M
301	300 pF	•	•				F, G, J, K, M
331	330 pF	•	•				F, G, J, K, M
361	360 pF	•					F, G, J, K, M
391	390 pF	•					F, G, J, K, M
431	430 pF	•					F, G, J, K, M
471	470 pF	•					F, G, J, K, M
511	510 pF						
561	560 pF						
621	620 pF						
681	680 pF						
751	750 pF						
821	820 pF						
911	910 pF						
102	1.0 nF						
112	1.1 nF						
122	1.2 nF						
132	1.3 nF						
152	1.5 nF						
182	1.8 nF						

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"
- Paper carrier • Plastic carrier tape
- For case size 0603: Cu termination "C" is only available in plastic carrier tape
- For soldering conditions see Vishay Soldering Recommendations www.vishay.com/doc?45034



SELECTION CHART								
DIELECTRIC (VISHAY CODE)		COG (D)						
STYLE		VJ0805						
CASE CODE		0805						
VOLTAGE (V _{DC})		25	50	100	200	250	500	TOLERANCE (1)
VOLTAGE CODE		X	A	B	C	P	E	
CAP. CODE	CAP.							
0R1	0.1 pF	•	•	•	•	•		V, B, C, D
0R2	0.2 pF	•	•	•	•	•		V, B, C, D
0R3	0.3 pF	•	•	•	•	•		V, B, C, D
0R4	0.4 pF	•	•	•	•	•		V, B, C, D
0R5	0.5 pF	•	•	•	•	•		V, B, C, D
0R6	0.6 pF	•	•	•	•	•		V, B, C, D
0R7	0.7 pF	•	•	•	•	•		V, B, C, D
0R8	0.8 pF	•	•	•	•	•		V, B, C, D
0R9	0.9 pF	•	•	•	•	•		V, B, C, D
1R0	1.0 pF	•	•	•	•	•	•	V, B, C, D
1R1	1.1 pF	•	•	•	•	•		V, B, C, D
1R2	1.2 pF	•	•	•	•	•	•	V, B, C, D
1R3	1.3 pF	•	•	•	•	•		V, B, C, D
1R4	1.4 pF	•	•	•	•	•		V, B, C, D
1R5	1.5 pF	•	•	•	•	•	•	V, B, C, D
1R6	1.6 pF	•	•	•	•	•		V, B, C, D
1R7	1.7 pF	•	•	•	•	•		V, B, C, D
1R8	1.8 pF	•	•	•	•	•	•	V, B, C, D
1R9	1.9 pF	•	•	•	•	•		V, B, C, D
2R0	2.0 pF	•	•	•	•	•		V, B, C, D
2R1	2.1 pF	•	•	•	•	•		V, B, C, D
2R2	2.2 pF	•	•	•	•	•	•	V, B, C, D
2R4	2.4 pF	•	•	•	•	•		V, B, C, D
2R7	2.7 pF	•	•	•	•	•		V, B, C, D
3R0	3.0 pF	•	•	•	•	•		V, B, C, D
3R3	3.3 pF	•	•	•	•	•	•	V, B, C, D
3R6	3.6 pF	•	•	•	•	•		V, B, C, D
3R9	3.9 pF	•	•	•	•	•	•	V, B, C, D
4R3	4.3 pF	•	•	•	•	•		V, B, C, D
4R7	4.7 pF	•	•	•	•	•	•	V, B, C, D
5R1	5.1 pF	•	•	•	•	•		V, B, C, D
5R6	5.6 pF	•	•	•	•	•	•	V, B, C, D
6R2	6.2 pF	•	•	•	•	•		V, B, C, D
6R8	6.8 pF	•	•	•	•	•	•	V, B, C, D
7R5	7.5 pF	•	•	•	•	•		V, B, C, D
8R2	8.2 pF	•	•	•	•	•	•	V, B, C, D
9R1	9.1 pF	•	•	•	•	•		V, B, C, D

Notes

RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"

- Plastic carrier tape

- For soldering conditions see Vishay Soldering Recommendations www.vishay.com/doc?45034

(1) 500 V, < 10 pF tolerances B, C, D only



SELECTION CHART							
DIELECTRIC (VISHAY CODE)		C0G (D)					
STYLE		VJ0805					
CASE CODE		0805					
VOLTAGE (V _{DC})		25	50	100	200	250	500
VOLTAGE CODE		X	A	B	C	P	E
CAP. CODE	CAP.						
100	10 pF	•	•	•	•	•	•
110	11 pF	•	•	•	•	•	•
120	12 pF	•	•	•	•	•	•
130	13 pF	•	•	•	•	•	•
150	15 pF	•	•	•	•	•	•
180	18 pF	•	•	•	•	•	•
200	20 pF	•	•	•	•	•	•
220	22 pF	•	•	•	•	•	•
240	24 pF	•	•	•	•	•	•
270	27 pF	•	•	•	•	•	•
300	30 pF	•	•	•	•	•	•
330	33 pF	•	•	•	•	•	•
360	36 pF	•	•	•	•	•	•
390	39 pF	•	•	•	•	•	•
430	43 pF	•	•	•	•	•	•
470	47 pF	•	•	•	•	•	•
510	51 pF	•	•	•	•	•	•
560	56 pF	•	•	•	•	•	•
620	62 pF	•	•	•	•	•	•
680	68 pF	•	•	•	•	•	•
750	75 pF	•	•	•	•	•	•
820	82 pF	•	•	•	•	•	•
910	91 pF	•	•	•	•	•	•
101	100 pF	•	•	•	•	•	•
111	110 pF	•	•	•	•	•	•
121	120 pF	•	•	•	•	•	•
131	130 pF	•	•	•	•	•	•
151	150 pF	•	•	•	•	•	•
181	180 pF	•	•	•	•	•	•
201	200 pF	•	•	•	•	•	•
221	220 pF	•	•	•	•	•	•
241	240 pF	•	•	•	•	•	•
271	270 pF	•	•	•	•	•	•
301	300 pF	•	•	•	•	•	•
331	330 pF	•	•	•	•	•	•
361	360 pF	•	•	•	•	•	•
391	390 pF	•	•	•	•	•	•
431	430 pF	•	•	•	•	•	•
471	470 pF	•	•	•	•	•	•
511	510 pF	•	•	•	•	•	•
561	560 pF	•	•	•	•	•	•
621	620 pF	•	•	•	•	•	•
681	680 pF	•	•	•	•	•	•
751	750 pF	•	•	•	•	•	•
821	820 pF	•	•	•	•	•	•
911	910 pF	•	•	•	•	•	•
102	1.0 nF	•	•	•	•	•	•

Notes

RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"

• Plastic carrier tape

- For soldering conditions see Vishay Soldering Recommendations www.vishay.com/doc?45034

(1) 500 V, < 10 pF tolerances B, C, D only



SELECTION CHART										
DIELECTRIC (VISHAY CODE)		C0G (D)								
STYLE		VJ1111								
CASE CODE		1111								
VOLTAGE (V _{DC})		50	100	200	300	500	630	1000	1500	TOLERANCE
VOLTAGE CODE		A	B	C	D	E	L	G	R	
CAP. CODE	CAP.									
0R2	0.2 pF	•	•	•	•	•	•	•	•	V, B, C, D
0R3	0.3 pF	•	•	•	•	•	•	•	•	V, B, C, D
0R4	0.4 pF	•	•	•	•	•	•	•	•	V, B, C, D
0R5	0.5 pF	•	•	•	•	•	•	•	•	V, B, C, D
0R6	0.6 pF	•	•	•	•	•	•	•	•	V, B, C, D
0R7	0.7 pF	•	•	•	•	•	•	•	•	V, B, C, D
0R8	0.8 pF	•	•	•	•	•	•	•	•	V, B, C, D
0R9	0.9 pF	•	•	•	•	•	•	•	•	V, B, C, D
1R0	1.0 pF	•	•	•	•	•	•	•	•	V, B, C, D
1R1	1.1 pF	•	•	•	•	•	•	•	•	V, B, C, D
1R2	1.2 pF	•	•	•	•	•	•	•	•	V, B, C, D
1R3	1.3 pF	•	•	•	•	•	•	•	•	V, B, C, D
1R4	1.4 pF	•	•	•	•	•	•	•	•	V, B, C, D
1R5	1.5 pF	•	•	•	•	•	•	•	•	V, B, C, D
1R6	1.6 pF	•	•	•	•	•	•	•	•	V, B, C, D
1R7	1.7 pF	•	•	•	•	•	•	•	•	V, B, C, D
1R8	1.8 pF	•	•	•	•	•	•	•	•	V, B, C, D
1R9	1.9 pF	•	•	•	•	•	•	•	•	V, B, C, D
2R0	2.0 pF	•	•	•	•	•	•	•	•	V, B, C, D
2R1	2.1 pF	•	•	•	•	•	•	•	•	V, B, C, D
2R2	2.2 pF	•	•	•	•	•	•	•	•	V, B, C, D
2R4	2.4 pF	•	•	•	•	•	•	•	•	V, B, C, D
2R7	2.7 pF	•	•	•	•	•	•	•	•	V, B, C, D
3R0	3.0 pF	•	•	•	•	•	•	•	•	V, B, C, D
3R3	3.3 pF	•	•	•	•	•	•	•	•	V, B, C, D
3R6	3.6 pF	•	•	•	•	•	•	•	•	V, B, C, D
3R9	3.9 pF	•	•	•	•	•	•	•	•	V, B, C, D
4R3	4.3 pF	•	•	•	•	•	•	•	•	V, B, C, D
4R7	4.7 pF	•	•	•	•	•	•	•	•	V, B, C, D
5R1	5.1 pF	•	•	•	•	•	•	•	•	V, B, C, D
5R6	5.6 pF	•	•	•	•	•	•	•	•	B, C, D
6R2	6.2 pF	•	•	•	•	•	•	•	•	B, C, D
6R8	6.8 pF	•	•	•	•	•	•	•	•	B, C, D
7R5	7.5 pF	•	•	•	•	•	•	•	•	B, C, D
8R2	8.2 pF	•	•	•	•	•	•	•	•	B, C, D
9R1	9.1 pF	•	•	•	•	•	•	•	•	B, C, D
100	10 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
110	11 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
120	12 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
130	13 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
150	15 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
160	16 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
180	18 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
200	20 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
220	22 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
240	24 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
270	27 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
300	30 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
330	33 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
360	36 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
390	39 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
430	43 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
470	47 pF	•	•	•	•	•	•	•	•	F, G, J, K, M

Notes

• RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"

- Plastic carrier tape



SELECTION CHART										
DIELECTRIC (VISHAY CODE)		C0G (D)								
STYLE		VJ1111								
CASE CODE		1111								
VOLTAGE (V _{DC})		50	100	200	300	500	630	1000	1500	TOLERANCE
VOLTAGE CODE		A	B	C	D	E	L	G	R	
CAP. CODE	CAP.									
510	51 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
560	56 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
620	62 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
680	68 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
750	75 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
820	82 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
910	91 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
101	100 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
111	110 pF	•	•	•	•	•	•	•	•	F, G, J, K, M
121	120 pF	•	•	•	•	•	•	•		F, G, J, K, M
131	130 pF	•	•	•	•	•	•	•		F, G, J, K, M
151	150 pF	•	•	•	•	•	•	•		F, G, J, K, M
161	160 pF	•	•	•	•	•	•	•		F, G, J, K, M
181	180 pF	•	•	•	•	•	•	•		F, G, J, K, M
201	200 pF	•	•	•	•	•	•	•		F, G, J, K, M
221	220 pF	•	•	•	•	•	•			F, G, J, K, M
241	240 pF	•	•	•	•	•	•			F, G, J, K, M
271	270 pF	•	•	•	•	•	•			F, G, J, K, M
301	300 pF	•	•	•	•	•	•			F, G, J, K, M
331	330 pF	•	•	•	•	•	•			F, G, J, K, M
361	360 pF	•	•	•	•	•	•			F, G, J, K, M
391	390 pF	•	•	•	•	•	•			F, G, J, K, M
431	430 pF	•	•	•	•	•	•			F, G, J, K, M
471	470 pF	•	•	•	•	•	•			F, G, J, K, M
511	510 pF	•	•	•	•					F, G, J, K, M
561	560 pF	•	•	•	•					F, G, J, K, M
621	620 pF	•	•	•	•					F, G, J, K, M
681	680 pF	•	•	•	•					F, G, J, K, M
751	750 pF	•	•	•	•					F, G, J, K, M
821	820 pF	•	•	•	•					F, G, J, K, M
911	910 pF	•	•	•	•					F, G, J, K, M
102	1000 pF	•	•	•	•					F, G, J, K, M
112	1100 pF	•	•	•						F, G, J, K, M
122	1200 pF	•	•	•						F, G, J, K, M
132	1300 pF	•	•	•						F, G, J, K, M
152	1500 pF	•	•	•						F, G, J, K, M
162	1600 pF	•	•	•						F, G, J, K, M
182	1800 pF	•	•							F, G, J, K, M
202	2000 pF	•	•							F, G, J, K, M
222	2200 pF	•	•							F, G, J, K, M
242	2400 pF	•	•							F, G, J, K, M
272	2700 pF	•	•							F, G, J, K, M
302	3000 pF	•	•							F, G, J, K, M
332	3300 pF	•	•							F, G, J, K, M

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"
- Plastic carrier tape



SELECTION CHART												
DIELECTRIC (VISHAY CODE)		C0G (D)										
STYLE		VJ2525										
CASE CODE		2525										
VOLTAGE (V _{DC})		300	500	630	800	1000	1500	2000	2500	3000	3600	TOLERANCE
VOLTAGE CODE		D	E	L	I	G	R	F	O	H	W	
CAP. CODE	CAP.											
1R0	1.0 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
1R1	1.1 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
1R2	1.2 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
1R3	1.3 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
1R4	1.4 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
1R5	1.5 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
1R6	1.6 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
1R7	1.7 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
1R8	1.8 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
1R9	1.9 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
2R0	2.0 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
2R1	2.1 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
2R2	2.2 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
2R4	2.4 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
2R7	2.7 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
3R0	3.0 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
3R3	3.3 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
3R6	3.6 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
3R9	3.9 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
4R3	4.3 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
4R7	4.7 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
5R1	5.1 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
5R6	5.6 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
6R2	6.2 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
6R8	6.8 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
7R5	7.5 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
8R2	8.2 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
9R1	9.1 pF	•	•	•	•	•	•	•	•	•	•	B, C, D
100	10 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
110	11 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
120	12 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
130	13 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
150	15 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
160	16 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
180	18 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
200	20 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
220	22 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
240	24 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
270	27 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
300	30 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
330	33 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
360	36 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
390	39 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M

Notes

• RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"

• Plastic carrier tape



SELECTION CHART												
DIELECTRIC (VISHAY CODE)		C0G (D)										
STYLE		VJ2525										
CASE CODE		2525										
VOLTAGE (V _{DC})		300	500	630	800	1000	1500	2000	2500	3000	3600	TOLERANCE
VOLTAGE CODE		D	E	L	I	G	R	F	O	H	W	
CAP. CODE	CAP.											
430	43 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
470	47 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
510	51 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
560	56 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
620	62 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
680	68 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
750	75 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
820	82 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
910	91 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
101	100 pF	•	•	•	•	•	•	•	•	•	•	F, G, J, K, M
111	110 pF	•	•	•	•	•	•	•	•	•		F, G, J, K, M
121	120 pF	•	•	•	•	•	•	•	•	•		F, G, J, K, M
131	130 pF	•	•	•	•	•	•	•	•	•		F, G, J, K, M
151	150 pF	•	•	•	•	•	•	•	•	•		F, G, J, K, M
161	160 pF	•	•	•	•	•	•	•	•	•		F, G, J, K, M
181	180 pF	•	•	•	•	•	•	•	•	•		F, G, J, K, M
201	200 pF	•	•	•	•	•	•	•	•	•		F, G, J, K, M
221	220 pF	•	•	•	•	•	•	•	•	•		F, G, J, K, M
241	240 pF	•	•	•	•	•	•	•	•	•		F, G, J, K, M
271	270 pF	•	•	•	•	•	•	•	•	•		F, G, J, K, M
301	300 pF	•	•	•	•	•	•	•				F, G, J, K, M
331	330 pF	•	•	•	•	•	•	•				F, G, J, K, M
361	360 pF	•	•	•	•	•	•	•				F, G, J, K, M
391	390 pF	•	•	•	•	•	•	•				F, G, J, K, M
431	430 pF	•	•	•	•	•	•	•				F, G, J, K, M
471	470 pF	•	•	•	•	•	•	•				F, G, J, K, M
511	510 pF	•	•	•	•	•	•					F, G, J, K, M
561	560 pF	•	•	•	•	•	•					F, G, J, K, M
621	620 pF	•	•	•	•	•	•					F, G, J, K, M
681	680 pF	•	•	•	•	•	•					F, G, J, K, M
751	750 pF	•	•	•	•	•	•					F, G, J, K, M
821	820 pF	•	•	•	•	•	•					F, G, J, K, M
911	910 pF	•	•	•	•	•	•					F, G, J, K, M
102	1000 pF	•	•	•	•	•	•					F, G, J, K, M
112	1100 pF	•	•	•	•	•	•					F, G, J, K, M
122	1200 pF	•	•	•	•	•	•					F, G, J, K, M
152	1500 pF	•	•	•	•							F, G, J, K, M
182	1800 pF	•	•	•	•							F, G, J, K, M
222	2000 pF	•	•	•	•							F, G, J, K, M
242	2400 pF	•	•	•								F, G, J, K, M
272	2700 pF	•	•									F, G, J, K, M
302	3000 pF	•	•									F, G, J, K, M

Notes

• RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"

• Plastic carrier tape



SELECTION CHART									
DIELECTRIC (VISHAY CODE)		C0G (D)							
STYLE		VJ3838							
CASE CODE		3838							
VOLTAGE (V _{DC})		300	500	1000	2500	3600	5000	7200	TOLERANCE
VOLTAGE CODE		D	E	G	O	W	M	S	
CAP. CODE	CAP.								
1R0	1.0 pF	•	•	•	•	•	•	•	B, C, D
1R1	1.1 pF	•	•	•	•	•	•	•	B, C, D
1R2	1.2 pF	•	•	•	•	•	•	•	B, C, D
1R3	1.3 pF	•	•	•	•	•	•	•	B, C, D
1R4	1.4 pF	•	•	•	•	•	•	•	B, C, D
1R5	1.5 pF	•	•	•	•	•	•	•	B, C, D
1R6	1.6 pF	•	•	•	•	•	•	•	B, C, D
1R7	1.7 pF	•	•	•	•	•	•	•	B, C, D
1R8	1.8 pF	•	•	•	•	•	•	•	B, C, D
1R9	1.9 pF	•	•	•	•	•	•	•	B, C, D
2R0	2.0 pF	•	•	•	•	•	•	•	B, C, D
2R1	2.1 pF	•	•	•	•	•	•	•	B, C, D
2R2	2.2 pF	•	•	•	•	•	•	•	B, C, D
2R4	2.4 pF	•	•	•	•	•	•	•	B, C, D
2R7	2.7 pF	•	•	•	•	•	•	•	B, C, D
3R0	3.0 pF	•	•	•	•	•	•	•	B, C, D
3R3	3.3 pF	•	•	•	•	•	•	•	B, C, D
3R6	3.6 pF	•	•	•	•	•	•	•	B, C, D
3R9	3.9 pF	•	•	•	•	•	•	•	B, C, D
4R3	4.3 pF	•	•	•	•	•	•	•	B, C, D
4R7	4.7 pF	•	•	•	•	•	•	•	B, C, D
5R1	5.1 pF	•	•	•	•	•	•	•	B, C, D
5R6	5.6 pF	•	•	•	•	•	•	•	B, C, D
6R2	6.2 pF	•	•	•	•	•	•	•	B, C, D
6R8	6.8 pF	•	•	•	•	•	•	•	B, C, D
7R5	7.5 pF	•	•	•	•	•	•	•	B, C, D
8R2	8.2 pF	•	•	•	•	•	•	•	B, C, D
9R1	9.1 pF	•	•	•	•	•	•	•	B, C, D
100	10 pF	•	•	•	•	•	•	•	F, G, J, K, M
110	11 pF	•	•	•	•	•	•	•	F, G, J, K, M
120	12 pF	•	•	•	•	•	•	•	F, G, J, K, M
130	13 pF	•	•	•	•	•	•	•	F, G, J, K, M
150	15 pF	•	•	•	•	•	•	•	F, G, J, K, M
160	16 pF	•	•	•	•	•	•	•	F, G, J, K, M
180	18 pF	•	•	•	•	•	•	•	F, G, J, K, M
200	20 pF	•	•	•	•	•	•	•	F, G, J, K, M
220	22 pF	•	•	•	•	•	•	•	F, G, J, K, M
240	24 pF	•	•	•	•	•	•	•	F, G, J, K, M
270	27 pF	•	•	•	•	•	•	•	F, G, J, K, M
300	30 pF	•	•	•	•	•	•	•	F, G, J, K, M
330	33 pF	•	•	•	•	•	•	•	F, G, J, K, M
360	36 pF	•	•	•	•	•	•	•	F, G, J, K, M
390	39 pF	•	•	•	•	•	•	•	F, G, J, K, M
430	43 pF	•	•	•	•	•	•	•	F, G, J, K, M
470	47 pF	•	•	•	•	•	•	•	F, G, J, K, M
510	51 pF	•	•	•	•	•	•	•	F, G, J, K, M
560	56 pF	•	•	•	•	•	•	•	F, G, J, K, M
620	62 pF	•	•	•	•	•	•	•	F, G, J, K, M
680	68 pF	•	•	•	•	•	•	•	F, G, J, K, M
750	75 pF	•	•	•	•	•	•	•	F, G, J, K, M
820	82 pF	•	•	•	•	•	•	•	F, G, J, K, M
910	91 pF	•	•	•	•	•	•	•	F, G, J, K, M

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"
- Plastic carrier tape







SELECTION CHART								
DIELECTRIC (VISHAY CODE)		C0G (D)						
STYLE		VJ3838						
CASE CODE		3838						
VOLTAGE (V _{DC})		300	500	1000	2500	3600	5000	7200
VOLTAGE CODE		D	E	G	O	W	M	S
CAP. CODE	CAP.							
101	100 pF	•	•	•	•	•	•	•
111	110 pF	•	•	•	•	•	•	
121	120 pF	•	•	•	•	•	•	
131	130 pF	•	•	•	•	•	•	
151	150 pF	•	•	•	•	•	•	
161	160 pF	•	•	•	•	•	•	
181	180 pF	•	•	•	•	•	•	
201	200 pF	•	•	•	•	•		
221	220 pF	•	•	•	•	•		
241	240 pF	•	•	•	•	•		
271	270 pF	•	•	•	•	•		
301	300 pF	•	•	•	•	•		
331	330 pF	•	•	•	•	•		
361	360 pF	•	•	•	•	•		
391	390 pF	•	•	•	•	•		
431	430 pF	•	•	•	•			
471	470 pF	•	•	•	•			
511	510 pF	•	•	•	•			
561	560 pF	•	•	•	•			
621	620 pF	•	•	•	•			
681	680 pF	•	•	•	•			
751	750 pF	•	•	•	•			
821	820 pF	•	•	•				
911	910 pF	•	•	•				
102	1000 pF	•	•	•				
112	1100 pF	•	•	•				
122	1200 pF	•	•	•				
152	1500 pF	•	•	•				
182	1800 pF	•	•	•				
222	2000 pF	•	•	•				
242	2400 pF	•	•	•				
272	2700 pF	•	•	•				
302	3000 pF	•	•	•				
332	3300 pF	•	•	•				
362	3600 pF	•	•	•				
392	3900 pF	•	•	•				
432	4300 pF	•	•	•				
472	4700 pF	•	•	•				
512	5100 pF	•	•	•				
562	5600 pF	•	•					
622	6200 pF	•	•					
682	6800 pF	•	•					
752	7500 pF	•	•					
822	8200 pF	•						
912	9100 pF	•						
103	10 000 pF	•						
113	11 000 pF	•						
123	12 000 pF	•						

Notes

- RoHS-compliant except when supplied with lead (Pb)-containing termination, code "L"
- Plastic carrier tape













EIA SIZE / QUAD SIZE - TYPICAL PARAMETERS











EIA SIZE DIELECTRIC - TYPICAL PARAMETERS









EIA SIZE DIELECTRIC - TYPICAL PARAMETERS


QUAD SIZE DIELECTRIC - TYPICAL PARAMETERS











QUAD SIZE DIELECTRIC - TYPICAL PARAMETERS



QUAD SIZE DIELECTRIC - TYPICAL PARAMETERS



**STANDARD PACKAGING QUANTITIES (1)(2)(3)**

CASE CODE	TAPE SIZE	7" REEL QUANTITIES			11 1/4" AND 13" REEL QUANTITIES		WAFFLE PACK
		PAPER TAPE PACKAGING CODE "C" / "O"	PLASTIC TAPE PACKAGING CODE "T"	LOW QUANTITY "J" (5)	PAPER TAPE PACKAGING CODE "P" / "I"	PLASTIC TAPE PACKAGING CODE "R"	PLASTIC WAFFLE PACK PACKAGING CODE "W"
0402	8 mm	5000	n/a	1000	10 000	n/a	n/a
0603 (4)	8 mm	4000	4000	1000	10 000	10 000	n/a
0805 (4)	8 mm	n/a	3000	1000	n/a	10 000	n/a
0505	8 mm	n/a	3000	1000	n/a	10 000	n/a
1111	8 mm	n/a	2500	1000	n/a	9000	n/a
2525	12 mm	n/a	800	500	n/a	n/a	81
3838	16 mm	n/a	400	100	n/a	n/a	35

Notes

- (1) Vishay Vitramon uses embossed plastic carrier tape
(2) Reference: EIA standard RS 481 - "Taping of Surface Mount Components for Automatic Placement"
(3) n/a = not available
(4) Packaging "C" / "P" / "O" / "I" and "T" / "R" or lower quantities can depend from product thickness
(5) Paper / plastic tape used by availability

STORAGE AND HANDLING CONDITIONS

- (1) Store the components at 5 °C to +40 °C ambient temperature and ≤ 70 % relative humidity conditions.
(2) The product is recommended to be used within a time-frame of 2 years after shipment.
Check solderability in case extended shelf life beyond the expiry date is needed.

Precautions:

- Do not store products in an environment containing corrosive elements, especially where chloride gas, sulfide gas, acid, alkali, salt or the like are present. This may cause corrosion or oxidization of the terminations, which can easily lead to poor soldering.
- Store products on the shelf and avoid exposure to moisture or dust.
- Do not expose products to excessive shock, vibration, direct sunlight and so on.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

VJ0402D120JXCAJ	VJ0402D150JXCAJ	VJ0402D180JXBAJ	VJ0402D1R0BXCAJ	VJ0402D1R2BXCAJ
VJ0402D1R5BXCAJ	VJ0402D1R8BXCAJ	VJ0402D200JXBAJ	VJ0402D220JXBAJ	VJ0402D2R0BXCAJ
VJ0402D390JXAAJ	VJ0402D3R0BXCAJ	VJ0402D3R3BXCAJ	VJ0402D470JXAAJ	VJ0402D4R7CXCAJ
VJ0402D560JXAAJ	VJ0402D5R6CXCAJ	VJ0402D680JXXAJ	VJ0402D6R8CXCAJ	VJ0402D820JXXAJ
VJ0402D8R2CXCAJ	VJ0603D100JXPAJ	VJ0603D101JXCAJ	VJ0603D120JXPAJ	VJ0603D121KXBAJ
VJ0603D150JXPAJ	VJ0603D151KXBAJ	VJ0603D180JXPAJ	VJ0603D181KXAAJ	VJ0603D1R0BXPAJ
VJ0603D1R2BXPAJ	VJ0603D1R5BXPAJ	VJ0603D1R8BXPAJ	VJ0603D200JXPAJ	VJ0603D201KXAAJ
VJ0603D220JXPAJ	VJ0603D221KXAAJ	VJ0603D270JXPAJ	VJ0603D271KXAAJ	VJ0603D2R0BXPAJ
VJ0603D2R2BXPAJ	VJ0603D2R4BXPAJ	VJ0603D2R7BXPAJ	VJ0603D300JXPAJ	VJ0603D301KXAAJ
VJ0603D330JXPAJ	VJ0603D331KXAAJ	VJ0603D390JXPAJ	VJ0603D391KXXAJ	VJ0603D3R0BXPAJ
VJ0603D3R3BXPAJ	VJ0603D3R9CXPAJ	VJ0603D470JXPAJ	VJ0603D471KXXAJ	VJ0603D4R7CXPAJ
VJ0603D560JXCAJ	VJ0603D5R6CXPAJ	VJ0603D680JXCAJ	VJ0603D6R8CXPAJ	VJ0603D820JXCAJ
VJ0603D8R2CXPAJ	VJ0805D101JXPAJ	VJ0805D102KXAAJ	VJ0805D121KXPAJ	VJ0805D122KXXAJ
VJ0805D151KXPAJ	VJ0805D152KXXAJ	VJ0805D181KXPAJ	VJ0805D201KXPAJ	VJ0805D221KXPAJ
VJ0805D241KXPAJ	VJ0805D271KXPAJ	VJ0805D301KXPAJ	VJ0805D331KXPAJ	VJ0805D391KXCAJ
VJ0805D471KXBAJ	VJ0805D561KXBAJ	VJ0805D681KXBAJ	VJ0805D821KXAAJ	VJ0805D1R1BXPAJ
VJ0805D560FXPAJ	VJ0805D1R5BXPAJ	VJ0805D1R2BXPAJ	VJ0805D1R0BXPAJ	VJ0805D241FXPAJ
VJ0805D150JXPAJ	VJ0805D121JXPAJ	VJ0805D201JXPAJ	VJ0402D0R3VXCAJ	VJ0402D2R4BXCAJ
VJ0805D680JXPAJ	VJ0402D4R7BXCAJ	VJ0402D2R7BXCAJ	VJ0805D1R7DXPAJ	VJ0805D2R7DXPAJ
VJ0805D131FXPAJ	VJ0402D3R6DXAAJ	VJ0805D2R7BXPAJ	VJ0805D910FXPAJ	VJ0805D1R4DXPAJ