

Universal Two-Stage HSI Integrated 3-Speed (PSC) Circulator Furnace Control Kit

21M51U-843

Replaces:

White-Rodgers 50M51-242
and All 50M61-XXX's
Two-Stage HSI Systems
with 80V or 120V Ignitor

INCLUDED

HotRod™ Universal
Ignitor Kit – 21D64-2




Replace the Original with the Original.

21M51U-843 simplifies stocking,
installation and ensures peak
system performance.

Easy-Install Kit includes everything you need
for quick and accurate replacement:

- Ignition Control Module — 50M51-843
- HotRod™ Universal Ignitor Kit — 21D64-2
- Installation Instructions and OEM Cross-Reference



Universal Integrated Furnace Module 50M51-843



White-Rodgers™


EMERSON
Climate Technologies

Universal Two-Stage HSI Integrated 3-Speed (PSC) Circulator Furnace Control Kit

Replaces:

White-Rodgers 50M51-242 and All 50M61-XXX's
Two-Stage HSI Systems with 80V or 120V Ignitor

21M51U-843

Features

- 120 VAC Ignitor Output
- 120 VAC Two-Speed Inducer Output
- 120 VAC Humidifier Output
- 120 VAC Electronic Air Cleaner Output
- 120 VAC 3-Speed PSC Circulator Output
- 2-Stage Gas Valve Output
- Fuse Protection – 3 Amp
- Furnace Status LED – Tri-Color (Green, Red and Amber)
- Heat Fan OFF Delay (Dipswitch Selectable)
- Fan ON Delay for Cooling
- Auto Second Stage Delay (Dipswitch Selectable Mode)
- Historical Fault Retrieval by Pushbutton
- YLO, Y, W1, W2, R, G, C, TWIN Terminals
- Pressure Switch Inputs and Monitoring
- Flash Microprocessor with Non-Volatile Memory
- Flame Current Measurement Points

Specifications

Electrical Ratings [@ 77°F (25°C)]

Input Voltage: 24 VAC, 60 Hz (Class II transformer required)
Nom. Input Current @ 24 VAC: 530 mA + MV

Relay Load Ratings

Gas Valve Relays: 1.5 amps @ 24 VAC, 60 Hz
Inducer Relays: 2.2 FLA – 3.5 LRA @ 120 VAC
Circulator Relays: 14.5 FLA – 25.0 LRA @ 120 VAC
Humidifier Load: 1.0 amp max. @ 120 VAC
Electronic Air Cleaner Load: 1.0 amp max. @ 120 VAC
Ignitor Relay: 4.0 amps max. @ 132 VAC, 60 Hz

Flame Current Requirements

Minimum current to insure flame detection: 0.3 µA DC*
Maximum current for non-detection: 0.1 µA DC*
Maximum allowable leakage resistance: 100 M ohms
*Measured with a DC microammeter in the flame probe lead

Operating Temperature Range

-40° to 175°F (-40° to 80°C)

Humidity Range

5% to 93% relative humidity (non-condensing)

Timing Specifications (@ 60 Hz)

Flame Failure Response Time: 2.0 sec. max.

Gases Approved: Natural, Manufactured, Mixed, Liquefied
Petroleum and LP Gas/Air Mixtures are all approved for use.

Dimensions

5.25" W x 8" H x 1.25" D

For Additional Information

Visit www.white-rodgers.com

Timing Specifications

(All times are in seconds unless noted otherwise)

21M51U-843	
Pre-purge	15
Ignitor warm-up	17
Trial for ignition period	4
Ignition activation period	3
Retries	2 times
Valve sequence period	12
Interpurge	60
Post-purge	15
Lockout time	300
Heat delay to fan ON	45
Heat delay to fan OFF*	90/120/150/180
Cool delay to fan ON	5
Cool delay to fan OFF	60
Auto reset	60 minutes
Electronic air cleaner	Yes
Humidifier	Yes
Twin	Yes

* These times will vary depending on option switch position. See OPERATION section for further information.

21M51U-843 Cross Reference Application Data:

Module Model #	Furnace Model	Ignitor	Furnace OEM
18M3401	G60DF(X) or G60UH(X)	21D64-2*	Lennox
20300001	N/A		Goodman
20300003	N/A		
46M9901	G61MP		Lennox
50M51-242	FC9T	Use existing or 21D64-2	Coleman
50M51-242	FL9T		Evcon
50M51-242	PT9A		Luxaire
50M51-242	PT9B		York
50M51-242	PT9C		
50M51-242	PT9D		
50M51-242	GM9T		
50M51-242	FC8T		
50M51-242	FL8T		
50M51-242	LC8T		
50M51-242	LL8T		
50M51-242	PT8A		

Module Model #	Furnace Model	Ignitor	Furnace OEM
50M61-120	G60DF(X) G60UH(X) or G61MP	21D64-2*	Lennox
50M61-288	N/A		Amana
50M61-289	N/A		Goodman
50M61-495	XL80		American Standard
50M61-843	N/A		Trane
83L9301	N/A		White-Rodgers
CNT03077	XL80		Standard
X13650839010	XL80		Lennox
			Trane

Note: The installer may have to modify existing ignitor hole to accommodate the new 21D64-2, with ceramic diameter (0.394").

*21D64-2 Ignitor Note:

In these applications, the existing 80V ignitor must be replaced by the 120V 21D64-2 ignitor.

White-Rodgers™

Saint Louis, Missouri Markham, Ontario
314-553-3600 905-948-3411
www.white-rodgers.com
www.emersonclimate.com

The Emerson logo is a trademark and
a service mark of Emerson Electric Co.


EMERSON™
Climate Technologies

WR-8443-2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[White-Rodgers:](#)

[21M51U-843](#)