

IGBT SIP Module (Fast IGBT)


IMS-2

PRIMARY CHARACTERISTICS

OUTPUT CURRENT IN A TYPICAL 20 kHz MOTOR DRIVE

V_{CES}	600 V
I_{RMS} per phase (3.1 kW total) with $T_C = 90\text{ }^{\circ}\text{C}$	4.6 A _{RMS}
T_J	125 $^{\circ}\text{C}$
Supply voltage	360 V _{DC}
Power factor	0.8
Modulation depth (see fig. 1)	115 %
$V_{CE(on)}$ (typical) at $I_C = 3.9\text{ A}$, 25 $^{\circ}\text{C}$	1.7 V
Speed	8 kHz to 30 kHz
Package	SIP
Circuit configuration	Three phase inverter

FEATURES

- Fully isolated printed circuit board mount package
- Switching-loss rating includes all “tail” losses
- HEXFRED® soft ultrafast diodes
- Optimized for high speed, see fig. 1 for current vs. frequency curve
- UL approved file E78996 
- Designed and qualified for industrial level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

DESCRIPTION

The IGBT technology is the key to Vishay’s Semiconductors advanced line of IMS (Insulated Metal Substrate) power modules. These modules are more efficient than comparable bipolar transistor modules, while at the same time having the simpler gate-drive requirements of the familiar power MOSFET. This superior technology has now been coupled to a state of the art materials system that maximizes power throughput with low thermal resistance. This package is highly suited to motor drive applications and where space is at a premium.

ABSOLUTE MAXIMUM RATINGS

PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS
Collector to emitter voltage	V_{CES}		600	V
Continuous collector current, each IGBT	I_C	$T_C = 25\text{ }^{\circ}\text{C}$	7.2	A
		$T_C = 100\text{ }^{\circ}\text{C}$	3.9	
Pulsed collector current	$I_{CM}^{(1)}$		22	
Clamped inductive load current	$I_{LM}^{(2)}$			
Diode continuous forward current	I_F	$T_C = 100\text{ }^{\circ}\text{C}$	3.4	
Diode maximum forward current	I_{FM}		22	
Gate to emitter voltage	V_{GE}		± 20	V
Isolation voltage	V_{ISOL}	1 minute, any terminal to case	2500	V _{RMS}
Maximum power dissipation, each IGBT	P_D	$T_C = 25\text{ }^{\circ}\text{C}$	23	W
		$T_C = 100\text{ }^{\circ}\text{C}$	9.1	
Operating junction and storage temperature range	T_J, T_{Stg}		-40 to +150	$^{\circ}\text{C}$
Soldering temperature		10 s, (0.063" (1.6 mm) from case)	300	
Mounting torque		6-32 or M3 screw	5 to 7 (0.55 to 0.8)	lbf · in (N · m)

Notes

(1) Repetitive rating; $V_{GE} = 20\text{ V}$, pulse width limited by maximum junction temperature (see fig. 20)

(2) $V_{CC} = 80\%$ (V_{GES}), $V_{GE} = 20\text{ V}$, $L = 10\text{ }\mu\text{H}$, $R_G = 50\text{ }\Omega$ (see fig.19)

**THERMAL AND MECHANICAL SPECIFICATIONS**

PARAMETER	SYMBOL	TYP.	MAX.	UNITS
Junction-to-case, each IGBT, one IGBT in conduction	R_{thJC} (IGBT)	-	5.5	°C/W
Junction-to-case, each diode, one diode on conduction	R_{thJC} (DIODE)	-	9.0	
Case to sink, flat, greased surface	R_{thCS} (MODULE)	0.1	-	
Weight of module		20		g
		0.7		oz.

ELECTRICAL SPECIFICATIONS ($T_J = 25\text{ °C}$ unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Collector to emitter breakdown voltage	$V_{(BR)CES}^{(1)}$	$V_{GE} = 0\text{ V}$, $I_C = 250\text{ }\mu\text{A}$	600	-	-	V
Temperature coefficient of breakdown voltage	$\Delta V_{(BR)CES}/\Delta T_J$	$V_{GE} = 0\text{ V}$, $I_C = 1\text{ mA}$	-	0.63	-	V/°C
Collector to emitter saturation voltage	$V_{CE(on)}$	$I_C = 3.9\text{ A}$	-	1.70	2.2	V
		$I_C = 7.2\text{ A}$	-	1.95	-	
		$I_C = 3.9\text{ A}$, $T_J = 150\text{ °C}$	-	1.70	-	
Gate threshold voltage	$V_{GE(th)}$	$V_{CE} = V_{GE}$, $I_C = 250\text{ }\mu\text{A}$	3.0	-	6.0	mV/°C
Temperature coefficient of threshold voltage	$\Delta V_{GE(th)}/\Delta T_J$		-	-11	-	
Forward transconductance	$g_{fe}^{(2)}$		1.4	4.3	-	S
Zero gate voltage collector current	I_{CES}	$V_{GE} = 0\text{ V}$, $V_{CE} = 600\text{ V}$	-	-	250	μA
		$V_{GE} = 0\text{ V}$, $V_{CE} = 600\text{ V}$, $T_J = 150\text{ °C}$	-	-	2500	
Diode forward voltage drop	V_{FM}	$I_C = 8.0\text{ A}$	-	1.4	1.7	V
		$I_C = 8.0\text{ A}$, $T_J = 150\text{ °C}$	-	1.3	1.6	
Gate to emitter leakage current	I_{GES}	$V_{GE} = \pm 20\text{ V}$	-	-	± 100	nA

Notes

- (1) Pulse width $\leq 80\text{ }\mu\text{s}$; duty factor $\leq 0.1\%$
(2) Pulse width 5.0 μs , single shot

SWITCHING CHARACTERISTICS ($T_J = 25\text{ °C}$ unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNITS
Total gate charge (turn-on)	Q_g	$I_C = 3.9\text{ A}$ $V_{CC} = 400\text{ V}$ $V_{GE} = 15\text{ V}$		-	31	47	nC
Gate to emitter charge (turn-on)	Q_{GE}			-	5.0	7.5	
Gate to collector charge (turn-on)	Q_{gc}			-	13	20	
Turn-on delay time	$t_{d(on)}$	$T_J = 25\text{ °C}$ $I_C = 3.9\text{ A}$, $V_{CC} = 480\text{ V}$ $V_{GE} = 15\text{ V}$, $R_G = 50\text{ }\Omega$ Energy losses include "tail" and diode reverse recovery See fig. 9, 10, 11, 18		-	45	-	ns
Rise time	t_r			-	22	-	
Turn-off delay time	$t_{d(off)}$			-	100	160	
Fall time	t_f			-	120	180	
Turn-on switching loss	E_{on}			-	0.13	-	mJ
Turn-off switching loss	E_{off}			-	0.07	-	
Total switching loss	E_{ts}			-	0.20	0.3	ns
Turn-on delay time	$t_{d(on)}$	$T_J = 150\text{ °C}$ $I_C = 3.9\text{ A}$, $V_{CC} = 480\text{ V}$ $V_{GE} = 15\text{ V}$, $R_G = 50\text{ }\Omega$ Energy losses include "tail" and diode reverse recovery See fig. 9, 10, 11, 18		-	42	-	
Rise time	t_r			-	22	-	
Turn-off delay time	$t_{d(off)}$			-	120	-	
Fall time	t_f			-	250	-	
Total switching loss	E_{ts}			-	0.35	-	mJ
Input capacitance	C_{ies}	$V_{GE} = 0\text{ V}$ $V_{CC} = 30\text{ V}$ $f = 1.0\text{ MHz}$	See fig. 7	-	530	-	pF
Output capacitance	C_{oes}			-	39	-	
Reverse transfer capacitance	C_{res}			-	7.4	-	
Diode reverse recovery time	t_{rr}	$T_J = 25\text{ °C}$	See fig. 14	-	37	55	ns
		$T_J = 125\text{ °C}$		-	55	90	
Diode peak reverse recovery current	I_{rr}	$T_J = 25\text{ °C}$	See fig. 15	-	3.5	5.0	A
		$T_J = 125\text{ °C}$		-	4.5	8.0	
Diode reverse recovery charge	Q_{rr}	$T_J = 25\text{ °C}$	See fig. 16	-	65	138	nC
		$T_J = 125\text{ °C}$		-	124	360	
Diode peak rate of fall of recovery during t_b	$dl_{(rec)M}/dt$	$T_J = 25\text{ °C}$	See fig. 17	-	240	-	A/ μs
		$T_J = 125\text{ °C}$		-	210	-	




Fig. 1 - Typical Load Current vs. Frequency
(Load Current = I_{RMS} of Fundamental)




Fig. 2 - Typical Output Characteristics




Fig. 4 - Maximum Collector Current vs.
Case Temperature




Fig. 3 - Typical Transfer Characteristics




Fig. 5 - Typical Collector to Emitter Voltage vs.
Junction Temperature




Fig. 6 - Maximum Effective Transient Thermal Impedance, Junction to Case




Fig. 7 - Typical Capacitance vs. Collector to Emitter Voltage




Fig. 9 - Typical Switching Losses vs. Gate Resistance




Fig. 8 - Typical Gate Charge vs. Gate to Emitter Voltage




Fig. 10 - Typical Switching Losses vs. Junction Temperature




Fig. 11 - Typical Switching Losses vs. Collector to Emitter Current




Fig. 12 - Turn-Off SOA








Fig. 13 - Maximum Forward Voltage Drop vs. Instantaneous Forward Current


Fig. 14 - Typical Reverse Recovery Time vs. dI_F/dt

Fig. 16 - Typical Stored Charge vs. dI_F/dt

Fig. 15 - Typical Recovery Current vs. dI_F/dt

Fig. 17 - Typical $dI_{(rec)M}/dt$ vs. dI_F/dt




Fig. 18a - Test Circuit for Measurement of I_{LM} , E_{on} , $E_{off(diode)}$, t_{rr} , Q_{rr} , I_{rr} , $t_{d(on)}$, t_r , $t_{d(off)}$, t_f




Fig. 18c - Test Waveforms for Circuit of Fig. 18a, Defining E_{on} , $t_{d(on)}$, t_r




Fig. 18b - Test Waveforms for Circuit of Fig. 18a, Defining E_{off} , $t_{d(off)}$, t_f




Fig. 18d - Test Waveforms for Circuit of Fig. 18a, Defining E_{rec} , t_{rr} , Q_{rr} , I_{rr}




Fig. 18e - Macro Waveforms for Fig. 18a's Test Circuit




Fig. 19 - Clamped Inductive Load Test Circuit





Fig. 20 - Pulsed Collector Current Test Circuit

CIRCUIT CONFIGURATION



LINKS TO RELATED DOCUMENTS

Dimensions

www.vishay.com/doc?95066

DIMENSIONS in millimeters (inches)



- (1) Tolerance unless otherwise specified ± 0.254 mm (0.010")
 (2) Controlling dimension: inch
 (3) Terminal numbers are shown for reference only



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[VS-CPV362M4UPBF](#)