



Product: [11700A2](#)

DataTuff® 5e, 4 Bonded-Pr #24 Sol BC, PO Ins, PVC Jkt, PVC Jkt, SUN RES OIL RES II CMR

[Request Sample](#)

Product Description

Industrial Ethernet Cat 5e, 4 Bonded-Pair 24AWG (Solid) Bare Copper, PO Insulation, PVC Inner Jacket, PVC Outer Jacket, SUN RES OIL RES II CMR

Technical Specifications

Product Overview

Suitable Applications:	heavy oil environment (oil res I & II), outdoor, exposure to abrasion, harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc.
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
24	Solid	BC - Bare Copper	0.02 in	4

Conductor Count:	8
Total Number of Pairs:	4

Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PO - Polyolefin	0.035 in	0.009 in

Bonded-Pair:	Yes
--------------	-----

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Inner Jacket

Material	Nominal Diameter	Ripcord
PVC - Polyvinyl Chloride	0.2 in	Yes

Outer Shield

Material
No Shield

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.285 in	0.035 in	Yes

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
9 Ohm/1000ft	3 %

Capacitance

Max. Capacitance Unbalance	Nom.Mutual Capacitance
66 pF/ft	15 pF/ft

Delay

Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
510 ns/100m	25 ns/100m	70%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance
1 MHz	2 dB/100m	65.3 dB	65.3 dB	63.3 dB	63.3 dB	63.8 dB	60.8 dB	20 dB	100 ± 12 Ohm	105 ± 10 Ohm
4 MHz	4 dB/100m	56.3 dB	56.3 dB	52.3 dB	52.3 dB	51.7 dB	48.7 dB	23 dB	100 ± 12 Ohm	100 ± 10
8 MHz	5.7 dB/100m	51.8 dB	51.8 dB	46.1 dB	46.1 dB	45.7 dB	42.7 dB	24.5 dB	100 ± 12 Ohm	100 ± 10
10 MHz	6.4 dB/100m	50.3 dB	50.3 dB	43.9 dB	43.9 dB	43.8 dB	40.8 dB	25 dB	100 ± 12 Ohm	100 ± 10
16 MHz	8.1 dB/100m	47.3 dB	47.3 dB	39.1 dB	39.1 dB	39.7 dB	36.7 dB	25 dB	100 ± 12 Ohm	100 ± 10
20 MHz	9.2 dB/100m	45.8 dB	45.8 dB	35.2 dB	35.2 dB	37.7 dB	34.7 dB	25 dB	100 ± 12 Ohm	100 ± 10
25 MHz	10.3 dB/100m	44.3 dB	44.3 dB	34.1 dB	34.1 dB	35.8 dB	32.8 dB	24.3 dB	100 ± 15 Ohm	100 ± 10
31.25 MHz	11.6 dB/100m	42.9 dB	42.9 dB	31.3 dB	31.3 dB	33.9 dB	30.9 dB	23.6 dB	100 ± 15 Ohm	100 ± 10
62.5 MHz	16.8 dB/100m	38.4 dB	38.4 dB	21.6 dB	21.6 dB	27.8 dB	24.8 dB	21.5 dB	100 ± 15 Ohm	100 ± 10
100 MHz	21.7 dB/100m	35.3 dB	35.3 dB	17.1 dB	17.1 dB	23.8 dB	20.8 dB	20.1 dB	100 ± 15 Ohm	
155 MHz	27.7 dB/100m	32.5 dB	32.5 dB	4.7 dB	4.7 dB	19.9 dB	16.9 dB	19 dB	100 ± 18 Ohm	
200 MHz	32 dB/100m	30.8 dB	30.8 dB	3 dB	3 dB	17.7 dB	14.7 dB	19 dB	100 ± 20 Ohm	
250 MHz	36.4 dB/100m	29.3 dB	29.3 dB	0 dB	0 dB	15.8 dB	12.8 dB	18 dB	100 ± 20 Ohm	
300 MHz	40.5 dB/100m	28.2 dB	28.2 dB	0 dB	0 dB	14.2 dB	11.2 dB	18 dB	100 ± 20 Ohm	
310 MHz	41.3 dB/100m	27.9 dB	27.9 dB			13.9 dB	10.9 dB	18 dB	100 ± 20 Ohm	
350 MHz	44.3 dB/100m	27.2 dB	27.2 dB			12.9 dB	9.9 dB	17 dB	100 ± 22 Ohm	

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Installation Temperature Range:	+5°C To +75°C
UL Temp Rating:	60°C
Operating Temperature Range:	-10°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	35 lbs/1000ft
Max. Pull Tension:	40 lbs
Min. Bend Radius/Minor Axis:	0.29 in

Standards

NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMR
ISO/IEC Compliance:	Other Standards
CPR Euroclass:	Eca
Data Category:	Category 5e
TIA/EIA Compliance:	NEMA WC-63.1 Category 5e
Third Party Performance Verification:	UL Verified Cat 5e

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1666 Riser
IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
11700A2 0061000	Blue	Reel	1,000 ft	612825107736

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	US Patent #'s 5, 606, 151; 5, 734, 126. Operating temperatures are subject to length de-rating. Cable passes -10C Cold Bend per UL 1581. Outer Shield Separator Material: Polyester.
--------	--

History

Update and Revision:	Revision Number: 0.488 Revision Date: 04-29-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[11700A2 0101000](#) [11700A2 0102000](#) [11700A2 0061000](#)