



Product: [1211A](#)

Instrument Medical Interconnect, #26-4c, TC, PVC, O/A Foil, PVC Jkt, CL2X

Product Description

Computer, Instrument & Medical Interconnect, 26 AWG stranded (7x34) tinned copper conductors, PVC insulation, Duofoil® shield (100% coverage), 26 AWG stranded tinned copper drain wire, PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	for use with Molex SEMMCONN/AMP SDL connectors; computer communications; medical electronics interconnects; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; panel wiring
------------------------	---

Construction Details

Conductor				
Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	26 AWG	7x34	TC - Tinned Copper

Insulation				
Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.048 in mm	White, Yellow, Orange, Green

Outer Shield			
Shield Type	Material	Coverage	Drainwire Type
Tape	Tri-Laminate (Alum+Poly+Alum)	100%	26 AWG (7x34) TC

Outer Jacket		
Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.036 in (0.91 mm)	0.195 in (4.95 mm)
Overall Cable Diameter (Nominal):		0.195 in (4.95 mm)

Electrical Characteristics

Electricals			
Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Velocity of Prop.	Max. Current
44.4 Ohm/1000ft	26 pF/ft (85 pF/m)	60%	1.8 Amps per Conductor at 25°C

Voltage
UL Voltage Rating
300 V

Mechanical Characteristics

Temperature	
UL Temperature	Operating
90°C	-20°C To +90°C

Bend Radius	
Stationary Min.	Installation Min.

1.95 in (49.5 mm)	1.95 in (49.5 mm)
-------------------	-------------------

Max. Pull Tension:	14 lbs (6.4 kg)
Bulk Cable Weight:	21 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	VW-1
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, CL2X
AWM Compliance:	AWM 2464
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	AMP is a registered trademark of AMP, Inc.
--------	--

History

Update and Revision:	Revision Number: 0.474 Revision Date: 01-20-2023
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
1211A 0101000	Black	612825108443	C
1211A 010500	Black	612825108450	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1211A 0101000](#) [1211A 010500](#)