



Product: [1213](#)

Category 5E+ Cable, 4 Pair, U/UTP, CMP

**Product Description**

Category 5E+ Premise Horizontal Cable (350MHz), 4 Pair, 24 AWG Solid Bare Copper Conductors, U/UTP, Plenum-CMP, Flamarrest® PVC-LS Jacket

**Technical Specifications**

**Product Overview**

Suitable Applications:	Premise Horizontal Cable, Ethernet 1000BASE-T, Ethernet 100BASE-TX, Ethernet 10BASE-T, PoE++, PoE+, PoE
Patent:	This product has one or more applicable patents. More information on patents can be found at <a href="https://www.belden.com/patents">https://www.belden.com/patents</a> .

**Construction Details**

**Conductor**

Size	Stranding	Material	No. of Pairs
24 AWG	Solid	BC - Bare Copper	4

**Insulation**

Material	Color Code
PO+FEP - Polyolefin + Fluorinated Ethylene Propylene	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

**Outer Jacket**

Material	Material Trade Name	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	Flamarrest®	0.207 in (5.26 mm)	Yes

Overall Cable Diameter (Nominal):	0.207 in (5.26 mm)
-----------------------------------	--------------------

**Electrical Characteristics**

**Electricals**

Max. Conductor DCR	Max. Capacitance Unbalance
89 Ohm/km (27 Ohm/1000ft)	330 pF/100m

**Delay**

Frequency	Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
100 MHz	537.6 ns/100m	25 ns/100m	72%

**High Frequency**

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted) [Ohm]	Max./Min. Fitted Impedance [Ohm]
1	2.0 dB/100m	70.3	69.3	68.3	67.3	67.8	65.8	20.0	100 ± 15	100 ± 15
4	4.0 dB/100m	61.3	60.3	57.3	56.3	55.8	53.8	23.0	100 ± 15	100 ± 15
8	5.7 dB/100m	56.8	55.8	51.1	50.1	49.7	47.7	24.5	100 ± 15	100 ± 15
10	6.4 dB/100m	55.3	54.3	48.9	47.9	47.8	45.8	25.0	100 ± 15	100 ± 15
16	8.1 dB/100m	52.2	51.2	44.1	43.1	43.7	41.7	25.0	100 ± 15	100 ± 15
20	9.1 dB/100m	50.8	49.8	41.7	40.7	41.8	39.8	25.0	100 ± 15	100 ± 15
25	10.2 dB/100m	49.3	48.3	39.1	38.1	39.8	37.8	24.3	100 ± 15	100 ± 15
31.25	11.4 dB/100m	47.9	46.9	36.4	35.4	37.9	35.9	23.6	100 ± 15	100 ± 15

62.5	16.4 dB/100m	43.4	42.4	27.0	26.0	31.9	29.9	21.5	100 ± 15	100 ± 15
100	21.0 dB/100m	40.3	39.3	19.3	18.3	27.8	25.8	20.1	100 ± 15	100 ± 15
155	26.6 dB/100m	37.4	36.4	10.9	9.9	24.0	22.0	18.8	100 ± 22	100 ± 15
200	30.5 dB/100m	35.8	34.8	5.3	4.3	21.8	19.8	18.0	100 ± 22	100 ± 15
250	34.4 dB/100m	34.3	33.3	-0.1	-1.1	19.8	17.8	17.3	100 ± 32	100 ± 15
300	38.0 dB/100m	33.1	32.1			18.3	16.3	14.4	100 ± 32	100 ± 15
350	41.4 dB/100m	32.1	31.1			16.9	14.9	13.8	100 ± 32	100 ± 15
400	44.6 dB/100m	31.3	30.3			15.8	13.8	13.3	100 ± 32	100 ± 15
450	47.7 dB/100m	30.5	29.5			14.7	12.7	12.8	100 ± 32	100 ± 15

Voltage

UL Voltage Rating
300 V (CMP)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
90°C	-20°C To +75°C	0°C To +50°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
2.25 in (57.2 mm)	2.75 in (69.9 mm)

Max. Pull Tension:	25 lbs (11 kg)
Bulk Cable Weight:	21 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Plenum, Indoor
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), FT6, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
ICEA Compliance:	S-90-661
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3
NEMA Compliance:	NEMA WC-63.1
Data Category:	Category 5e
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 5e
Third Party Performance Verification:	Category 5e
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	1212

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Values above 350 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	--

History

Update and Revision:	Revision Number: 0.565 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1213 010U1000	Black	UnReel	1,000 ft	612825061267	
1213 D151000	Blue	Reel	1,000 ft	612825061274	
1213 D15A1000	Blue	Reel-in-Box	1,000 ft	612825061397	

1213 D15U1000	Blue	UnReel	1,000 ft	612825061298	
1213 D152500	Blue	Reel	2,500 ft	612825061281	
1213 008U1000	Gray	UnReel	1,000 ft	612825061335	
1213 005U1000	Green	UnReel	1,000 ft	612825061304	
1213 003U1000	Orange	UnReel	1,000 ft	612825061311	
1213 012U1000	Pink	UnReel	1,000 ft	612825061328	
1213 007U1000	Purple	UnReel	1,000 ft	612825061342	
1213 0091000	White	Reel	1,000 ft	612825061373	C
1213 009A1000	White	Reel-in-Box	1,000 ft	612825061403	C
1213 009U1000	White	UnReel	1,000 ft	612825061366	
1213 004U1000	Yellow	UnReel	1,000 ft	612825061380	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Belden Wire & Cable:

[1213 D15A1000](#) [1213 D15U1000](#) [1213 D151000](#) [1213 D152500](#) [1213 003U1000](#) [1213 004U1000](#) [1213 005U1000](#)  
[1213 007U1000](#) [1213 008U1000](#) [1213 009A1000](#) [1213 009U1000](#) [1213 0091000](#) [1213 0092500](#) [1213 010U1000](#)  
[1213 012U1000](#)