
www.vishay.com

VS-ETL1506S-M3, VS-ETL1506-1-M3

Vishay Semiconductors

Ultrafast Rectifier, 15 A FRED Pt[®]



VS-ETL1506S-M3

VS-ETL1506-1-M3

PRIMARY CHARACTERISTICS								
I _{F(AV)} 15 A								
V _R	600 V							
V _F at I _F	0.85 V							
t _{rr} (typ.)	60 ns							
T _J max.	175 °C							
Package	D ² PAK (TO-263AB), TO-262AA							
Circuit configuration	Single							

FEATURES

- · State of the art low forward voltage drop
- Ultrafast recovery time
- 175 °C operating junction temperature
- Low leakage current
- Designed and qualified according to JEDEC[®]-JESD 47



- Meets MSL level 1, per J-STD-020, LF maximum peak of 245 °C
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

DESCRIPTION

State of the art, ultralow V_F , soft-switching ultrafast rectifiers optimized for Discontinuous (Critical) Mode (DCM) Power Factor Correction (PFC).

The minimized conduction loss, optimized stored charge and low recovery current minimized the switching losses and reduce over dissipation in the switching element and snubbers.

The device is also intended for use as a freewheeling diode in power supplies and other power switching applications.

APPLICATIONS

AC/DC SMPS 70 W to 400 W

e.g. laptop and printer AC adaptors, desktop PC, TV and monitor, games units, and DVD AC/DC power supplies.

ABSOLUTE MAXIMUM RATINGS				
PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS
Repetitive peak reverse voltage	V _{RRM}		600	V
Average rectified forward current	I _{F(AV)}	T _C = 152 °C	15	٨
Non-repetitive peak surge current	I _{FSM}	T _C = 25 °C	200	A
Operating junction and storage temperatures	T _J , T _{Stg}		-65 to +175	°C

ELECTRICAL SPECIFICATI	LECTRICAL SPECIFICATIONS ($T_J = 25 \text{ °C}$ unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS	
Breakdown voltage, blocking voltage	V_{BR}, V_{R}	I _R = 100 μA	600	-	-		
Forward valtage	V _F	I _F = 15 A - 0.99		0.99	1.07	V	
Forward voltage		I _F = 15 A, T _J = 150 °C	-	0.85	0.91		
Reverse leakage current	1	$V_{R} = V_{R}$ rated	-	0.01	15		
neverse leakage current	I _R	$T_J = 150 \text{ °C}, V_R = V_R \text{ rated}$	-	6	100	μΑ	
Junction capacitance	CT	V _R = 600 V	-	12	-	pF	
Series inductance	L _S	Measured lead to lead 5 mm from package body	-	8.0	-	nH	

Revision: 25-Oct-17 1 Document Number: 96333 For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



VS-ETL1506S-M3, VS-ETL1506-1-M3

Vishay Semiconductors

DYNAMIC RECOVERY CHAR	ACTERIS	STICS (T _J = 25 °C	unless otherwise spe	ecified)			
PARAMETER	SYMBOL	TEST C	ONDITIONS	MIN.	TYP.	MAX.	UNITS
		$I_F = 1 \text{ A}, \ dI_F/dt = 100$	0 A/µs, V _R = 30 V	-	60	110	
Poverse receiver time	+	$I_F = 15 \text{ A}, \text{ d}I_F/\text{d}t = 10$	I _F = 15 A, dI _F /dt = 100 A/μs, V _R = 30 V		185	270	ns
Reverse recovery time	t _{rr}	T _J = 25 °C		-	210	-	115
		T _J = 125 °C		-	290	-	
Peak recovery current	I _{RRM}	T _J = 25 °C	I _F = 15 A dI _F /dt = 200 A/μs V _B = 390 V	-	20	-	А
Feak recovery current		T _J = 125 °C		-	26	-	A
	0	T _J = 25 °C		-	2.2	-	
Reverse recovery charge	Q _{rr}	T _J = 125 °C]	-	4.0	-	μC

THERMAL - MECHANICAL S	PECIFIC	ATIONS				
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Maximum junction and storage temperature range	T _J , T _{Stg}		-65	-	175	°C
Thermal resistance, junction to case	R _{thJC}		-	1.3	1.51	°C/W
Thermal resistance, junction to ambient	R _{thJA}	Typical socket mount	-	-	70	
Thermal resistance, case to heatsink	R _{thCS}	Mounting surface, flat, smooth, and greased	-	0.5	-	
Weight			-	2.0	-	g
weight			-	0.07	-	oz.
Mounting torque			6 (5)	-	12 (10)	kgf · cm (lbf · in)
Marking davias		Case style D ² PAK (TO-263AB)		ETL1	506S	
Marking device		Case style TO-262		ETL1	506-1	




Fig. 1 - Typical Forward Voltage Drop Characteristics




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage



VS-ETL1506S-M3, VS-ETL1506-1-M3

Vishay Semiconductors




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage





Fig. 4 - Max. Thermal Impedance Z_{thJC} Characteristics



Revision: 25-Oct-17

3


Document Number: 96333

24

For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

VS-ETL1506S-M3, VS-ETL1506-1-M3





www.vishay.com

SHAY

Fig. 7 - Typical Reverse Recovery Time vs. dl_F/dt




Fig. 8 - Typical Stored Charge vs. dl_F/dt





Fig. 9 - Reverse Recovery Waveform and Definitions

 Revision:
 25-Oct-17
 4
 Document Number: 96333

 For technical questions within your region:
 DiddesAmericas@vishay.com, DiddesAsia@vishay.com, DiddesEurope@vishay.com

 THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE.
 THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000





Vishay Semiconductors

ORDERING INFORMATION TABLE

Device code	VS-	E	т	L	15	06	S	TRL	-M3	
		2	3	4	5	6	7	8	9	
	1 - 2 - 3 - 4 - 5 - 6 -	E = E = T = L = Cur Volt	nay Sem cuit confi single TO-220 ultrafast rent cod	iguratior t recove le (15 = le (06 =	ry time 15 A) 600 V)	oduct				
	7 - - 8 -	• -1	= D ² PAI = TO-20 one = tu	62AA						
			RL = tap RR = tap		•					<i>.</i> .
	9 -	· -M3	s = halog	gen-free	, RoHS-	complia	ant, and	l termin	ations le	ead (Pt

ORDERING INFORMATI	RDERING INFORMATION (Example)						
PREFERRED P/N	QUANTITY PER TUBE	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION				
VS-ETL1506S-M3	50	1000	Antistatic plastic tube				
VS-ETL1506-1-M3	50	1000	Antistatic plastic tube				
VS-ETL1506STRR-M3	800	800	13" diameter reel				
VS-ETL1506STRL-M3	800	800	13" diameter reel				

LINKS TO RELATED DOCUMENTS							
Dimensions	D ² PAK (TO-263AB)	www.vishay.com/doc?96164					
	TO-262AA	www.vishay.com/doc?96165					
Dat marking information	D ² PAK (TO-263AB)	www.vishay.com/doc?95444					
Part marking information	TO-262AA	www.vishay.com/doc?95443					
Packaging information	D ² PAK (TO-263AB)	www.vishay.com/doc?96424					

5

Vishay Semiconductors

D²PAK

DIMENSIONS in millimeters and inches



ota	ted	90	°C
<u>S</u>	cale	<u>ə:</u> 8	:1

SYMBOL	MILLIM	ETERS	INC	HES	NOTES	
STMBOL	MIN.	MAX.	MIN.	MAX.	NOTES	
А	4.06	4.83	0.160	0.190		
A1	0.00	0.254	0.000	0.010		
b	0.51	0.99	0.020	0.039		
b1	0.51	0.89	0.020	0.035	4	
b2	1.14	1.78	0.045	0.070		
b3	1.14	1.73	0.045	0.068	4	
с	0.38	0.74	0.015	0.029		
c1	0.38	0.58	0.015	0.023	4	
c2	1.14	1.65	0.045	0.065		
D	8.51	9.65	0.335	0.380	2	

SYMBOL		MILLIM	MILLIMETERS		INCHES		
	OTMEDOL	MIN.	MAX.	MIN.	MAX.	NOTES	
	D1	6.86	8.00	0.270	0.315	3	
	E	9.65	10.67	0.380	0.420	2, 3	
	E1	7.90	8.80	0.311	0.346	3	
	е	2.54	2.54 BSC		0.100 BSC		
	Н	14.61	15.88	0.575	0.625		
	L	1.78	2.79	0.070	0.110		
	L1	-	1.65	-	0.066	3	
	L2	1.27	1.78	0.050	0.070		
	L3	0.25	BSC	0.010	BSC		
	L4	4.78	5.28	0.188	0.208		

Notes

⁽¹⁾ Dimensioning and tolerancing per ASME Y14.5 M-1994

(2) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outmost extremes of the plastic body

(3) Thermal pad contour optional within dimension E, L1, D1 and E1

⁽⁴⁾ Dimension b1 and c1 apply to base metal only

(5) Datum A and B to be determined at datum plane H

(6) Controlling dimension: inches

⁽⁷⁾ Outline conforms to JEDEC[®] outline TO-263AB

Revision: 13-Jul-17

1

Document Number: 96164

For technical questions within your region: DiodesAmericas@vishav.com, DiodesAsia@vishav.com, DiodesEurope@vishav.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000




Outline Dimensions




Vishay Semiconductors

TO-262AA

DIMENSIONS in millimeters and inches





F D1 (3) (3) Section A - A Base (4) Plating b1. b3 metal ≰ c1 (4) -(b, b2)-Section B - B and C - C Scale: None





Diodes 1. - Anode (two die)/open (one die) 2., 4. - Cathode 3. - Anode

Lead assignments

CVMPOI	MILLIN	IETERS	INC	INCHES			
SYMBOL	MIN.	MAX.	MIN.	MAX.	NOTES		
А	4.06	4.83	0.160	0.190			
A1	2.03	3.02	0.080	0.119			
b	0.51	0.99	0.020	0.039			
b1	0.51	0.89	0.020	0.035	4		
b2	1.14	1.78	0.045	0.070			
b3	1.14	1.73	0.045	0.068	4		
С	0.38	0.74	0.015	0.029			
c1	0.38	0.58	0.015	0.023	4		
c2	1.14	1.65	0.045	0.065			
D	8.51	9.65	0.335	0.380	2		
D1	6.86	8.00	0.270	0.315	3		
E	9.65	10.67	0.380	0.420	2, 3		
E1	7.90	8.80	0.311	0.346	3		
е	2.54	BSC	0.100) BSC			
L	13.46	14.10	0.530	0.555			
L1	-	1.65	-	0.065	3		
L2	3.56	3.71	0.140	0.146			

 ⁽¹⁾ Dimensioning and tolerancing as per ASME Y14.5M-1994
 ⁽²⁾ Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the second dimensioner of the second dimensis of the second dimensioner of the second dimensioner of the the outmost extremes of the plastic body (3)

Thermal pad contour optional within dimension E, L1, D1 and E1

⁽⁴⁾ Dimension b1 and c1 apply to base metal only (5)

Controlling dimension: inches

(6) Outline conform to JEDEC® TO-262 except A1 (max.), b (min., max.), b1 (min.), b2 (max.), c (min.), c1(min.), c2 (max.), D (min.), E (max.), L1 (max.), L2 (min., max.)

Revision: 30-Nov-17

1



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

VS-ETL1506-1-M3 VS-ETL1506S-M3 VS-ETL1506STRL-M3 VS-ETL1506STRR-M3