


**Product:** [1283S6](#) 

VideoFLEX® Mini Hi-Res, Banana Peel #20-6 coax, CMP



### Product Description

RGB Video Coax, Plenum-CMP, 6-20 AWG tinned copper conductors, foam FEP insulation, Duobond® foil + 95% tinned copper braid shield, color-coded Flamarrest® jackets, Banana Peel construction

### Technical Specifications

#### Product Overview

Suitable Applications:	RGB, VGA, SVGA, XGA, SXGA, UXGA, HDTV, LCD, Plasma, Digital Signage, Component Video, Video Mult, Animation, Special effects. Suitable for use in Plenum spaces
------------------------	---

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
20	Solid	BC - Bare Copper	0.032 in	6

Conductor Count:	6
------------------	---

##### Insulation

Material	Nominal Diameter
FEP - Fluorinated Ethylene Propylene (Foam)	0.133 in

##### Color Chart

Number	Color
1	Red
2	Green
3	Blue
4	White
5	Yellow
6	Brown

##### Inner Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	2	Tinned Copper (TC)		95%

##### Inner Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.196 in

##### Outer Shield Material

Material
No Shield

##### Outer Jacket Material

Material	Nominal Diameter
Banana Peel (No Overall Jacket)	0.588 in

## Construction and Dimensions

### Cabling

Filler
Bonded Spline

## Electrical Characteristics

### Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Inner Shield DCR	Outer Conductor DCR
10 Ohm/1000ft	10 Ohm/1000ft	3.8 Ohm/1000ft	3.8 Ohm/1000ft

### Capacitance

Nom. Capacitance Conductor to Shield
16.2 pF/ft

### Inductance

Nominal Inductance
0.107 $\mu$ H/ft

### Impedance

Nominal Characteristic Impedance
75 Ohm

### Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
5-850 MHz	23 dB
851-3000 MHz	15 dB

### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.3 dB/100ft
3.6 MHz	0.6 dB/100ft
10 MHz	0.9 dB/100ft
71.5 MHz	2.1 dB/100ft
135 MHz	2.7 dB/100ft
270 MHz	3.8 dB/100ft
360 MHz	4.4 dB/100ft
540 MHz	5.5 dB/100ft
720 MHz	6.4 dB/100ft
750 MHz	6.5 dB/100ft
1000 MHz	7.6 dB/100ft
1500 MHz	9.4 dB/100ft
2500 MHz	12.4 dB/100ft
3000 MHz	13.8 dB/100ft

### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.22 ns/ft	83%

### Voltage

UL Voltage Rating
300 V RMS

## Temperature Range

Non-UL Temp Rating:	75°C
UL Temp Rating:	60°C
Operating Temp Range:	-20°C To +75°C

## Mechanical Characteristics

Bulk Cable Weight:	196 lbs/1000ft
Max. Pull Tension:	216 lbs

Min Bend Radius/Minor Axis:	6.5 in
-----------------------------	--------

## Standards

NEC/(UL) Compliance:	CMP
CEC/C(UL) Compliance:	CMP
RG Type:	59/U Type
Series Type:	59

## Applicable Environmental and Other Programs

Environmental Space:	Indoor - Plenum
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-06-01
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Aerial:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	No

## Flammability, LSOH, Toxicity Testing

UL Flammability:	NFPA 262
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

## Part Number

### Variants

Item #	Color	Putup Type	Length	UPC
1283S6 000250	None	Reel	250 ft	612825110873
1283S6 000500	None	Reel	500 ft	612825110880
1283S6 0001000	None	Reel	1,000 ft	612825110866

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## History

Update and Revision:	Revision Number: 0.268 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1283S6 000500](#) [1283S6 0001000](#) [1283S6 000250](#)