


Vishay Semiconductors

High Speed Infrared Emitting Diode, 940 nm, GaAlAs, MQW



DESCRIPTION

VSLB3948 is a high speed infrared emitting diode in GaAlAs,

FEATURES

Package type: leaded

• Package form: T-1, clear epoxy

• Dimensions: Ø 3 mm

· High speed

High radiant power

· Low forward voltage

· Suitable for high pulse current operation

• Angle of half intensity: $\varphi = \pm 22^{\circ}$

• Peak wavelength: $\lambda_p = 940 \text{ nm}$

· Good spectral matching to Si photodetectors

· Material categorization: for definitions of compliance please see www.vishav.com/doc?99912





HALOGEN FREE

GREEN

MQW technology, molded in a clear plastic package.

APPLICATIONS

· Infrared remote control units

PRODUCT SUMMARY					
COMPONENT	I _e (mW/sr)	φ (deg)	λ _p (nm)	t _r (ns)	
VSLB3948	65	± 22	940	15	

Note

Test conditions see table "Basic Characteristics"

ORDERING INFORMATION					
ORDERING CODE	PACKAGING	REMARKS	PACKAGE FORM		
VSLB3948	Bulk	MOQ: 5000 pcs, 5000 pcs/bulk	T-1		


Note

• MOQ: minimum order quantity

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
Reverse voltage		V _R	5	V	
Forward current		I _F	100	mA	
Peak forward current	$t_p/T = 0.1$, $t_p = 100 \mu s$	I _{FM}	500	mA	
Surge forward current	t _p = 100 μs	I _{FSM}	1	Α	
Power dissipation		P _V	160	mW	
Junction temperature		Tj	100	°C	
Operating temperature range		T _{amb}	-25 to +85	°C	
Storage temperature range		T _{stg}	-40 to +100	°C	
Soldering temperature	t ≤ 5 s, 2 mm from case	T _{sd}	260	°C	
Thermal resistance junction/ambient	J-STD-051, leads 7 mm, soldered on PCB	R _{thJA}	300	K/W	



Vishay Semiconductors








Fig. 2 - Forward Current Limit vs. Ambient Temperature

PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Forward voltage	$I_F = 100 \text{ mA}, t_p = 20 \text{ ms}$	V _F	1.22	1.42	1.62	V
Temperature coefficient of V _F	I _F = 1 mA	TK _{VF}		-1.5		mV/K
Reverse current	V _R = 5 V	I _R			10	μΑ
Junction capacitance	$V_R = 0 \text{ V, f} = 1 \text{ MHz,}$ $E = 0 \text{ mW/cm}^2$	CJ		21		pF
Radiant intensity	$I_F = 100 \text{ mA}, t_p = 20 \text{ ms}$	l _e	32	65	110	mW/sr
Radiant power	$I_F = 100 \text{ mA}, t_p = 20 \text{ ms}$	фе		40		mW
Temperature coefficient of radiant	I _F = 1 mA	TKφ _e		-1.1		%/K
power	I _F = 100 mA	TKφ _e		-0.51		%/K
Angle of half intensity		φ		± 22		deg
Peak wavelength	I _F = 30 mA	λρ		940		nm
Spectral bandwidth	I _F = 30 mA	Δλ		30		nm
Temperature coefficient of Ip	I _F = 30 mA	TK _{λp}		0.25		nm
Rise time	I _F = 100 mA, 20 % to 80 %	t _r		15		ns
Fall time	I _F = 100 mA, 20 % to 80 %	t _f		15		ns
Virtual source diameter		d		2		mm



BASIC CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 3 - Forward Current vs. Forward Voltage




Fig. 4 - Relative Forward Voltage vs. Ambient Temperature




Fig. 5 - Radiant Intensity vs. Forward Current




Fig. 6 - Relative Radiant Power vs. Wavelength




Fig. 7 - Relative Radiant Intensity vs. Ambient Temperature






Fig. 8 - Relative Radiant Intensity vs. Angular Displacement




Vishay Semiconductors

PACKAGE DIMENSIONS in millimeters







technical drawings according to DIN specifications

Drawing-No.: 6.544-5255.01-4

Issue: 9; 28.07.14



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay: VSLB3948