


Ultra Precision Resistor 1-2-3 Network

RoHS
COMPLIANT

DSCC Specification 87026

COMPOSITION OF TYPE NUMBER

Example: R₁≠R₂

SM 1X 10K00 B A

① ② ③ ④ ⑤ ⑥

Example: R₁=R₂


SLD 2X 1K000 / 10K00 B Q

① ② ③ ④ ⑤ ⑥


- ① Type
- ② Number of Values
- ③ TCR Absolute
- ④ Nominal Resistance Values
- ⑤ Resistance Tolerance (Absolute)
- ⑥ Resistance Tolerance (Matching)

Resistance value, in ohm, is expressed by a series of five characters, four of which represent significant digits. The fifth R or K is a dual-purpose letter that designates both the value range (R for ohmic; K for kilo-ohm) and the location of decimal point.

CONFIGURATION (DIMENSIONS IN mm)



Type	SM
L	7.7±0.2
L ₁	1.0 max.
W	8.1±0.2
W ₁	7.8±0.2
W ₂	0.3 max.
T	2.6±0.2
F	2.54±0.25
l	10±3
d	φ0.65±0.05



Type	SLD
L	7.5±0.5
W	7.5±0.5
T	2.2±0.5
F	2.54±0.25
l	5±1
t	0.3±0.05
a	1.0±0.05
b	0.65±0.05
c	0.4±0.05

TCR, RESISTANCE RANGE, TOLERANCE, RATED POWER

Type	TCR (ppm/°C) -55°C to +125°C		Resistance Range/ Element (Ω)**	Resistance Tolerance (%)		Rated Power/ Package (W)
	Absolute*	Tracking		Absolute*	Matching*	
SM	0±5 (X) 0±2.5 (Y)	See Table 1	50 to 30k	±0.02 (Q) ±0.05 (A) ±0.1 (B)	±0.01 (T) ±0.02 (Q) ±0.05 (A) ±0.1 (B)	0.3 at 125°C
SLD	0±5 (X) 0±2.5 (Y)	See Table 1	50 to 100	±0.1 (B) ±0.5 (D)	±0.05 (A) ±0.1 (B)	0.25 at 70°C
			100 to 30k	±0.05 (A) ±0.1 (B)	±0.02 (Q) ±0.05 (A) ±0.1 (B)	

* Symbols parenthesized are for type number composition.


** -25°C to +125°C for SLD type.

*** Please contact us for the availability.


TABLE 1.
TCR TRACKING IS SUBJECT TO RESISTANCE RATIO

Resistance Ratio	TCR Tracking (ppm/°C)
Resistance Ratio = 1	±0.5
1 < Resistance Ratio ≤ 10	±1
10 < Resistance Ratio ≤ 100	±2
100 < Resistance Ratio	±3

POWER DERATING CURVE



FREQUENCY CHARACTERISTICS




PERFORMANCE – SM					
Parameters	Test Condition	ALPHA Specification		ALPHA Typical Test Data	
		ΔR	$\Delta Ratio$	ΔR	$\Delta Ratio$
Maximum Rated Operating Temperature		125°C			
Working Temperature Range		-65°C to +150°C			
Thermal Shock Overload	-65°C/30 min. \leftrightarrow +150°C/30 min., 5 cycles Rated Voltage x 2.5, 5 sec.	$\pm 0.02\%$ $\pm 0.02\%$	$\pm 0.01\%$ $\pm 0.01\%$	$\pm 0.005\%$ $\pm 0.0025\%$	$\pm 0.0025\%$ $\pm 0.001\%$
Solderability	245°C, 5 sec.	over 95% coverage		over 95% coverage	
Resistance to Solvents	① Isopropyl Alcohol + Mineral Spirits ② Water + Butyl Cellosolve + Monoethanolamine	no damage		no damage	
Low Temperature Storage and Operation	-65°C, No Load, 24 hrs. \rightarrow Rated Voltage, 45 min. 0.908 kg (2 pounds), 10 sec.	$\pm 0.05\%$ $\pm 0.02\%$	$\pm 0.02\%$ $\pm 0.01\%$	$\pm 0.0025\%$ $\pm 0.0025\%$	$\pm 0.001\%$ $\pm 0.001\%$
Terminal Strength		over 10,000 M Ω		over 10,000 M Ω	
Dielectric Withstanding Voltage	Atmo. Pres.: AC 300V, 1 min. Baro. Pres. 8 mHg; AC 200V, 1min. DC 500V, 2 min.	$\pm 0.02\%$	$\pm 0.01\%$	$\pm 0.0025\%$	$\pm 0.001\%$
Insulation Resistance		over 10,000 M Ω		over 10,000 M Ω	
Resistance to Soldering Heat	350°C, 3 sec.	$\pm 0.02\%$	$\pm 0.01\%$	$\pm 0.0025\%$	$\pm 0.001\%$
Moisture Resistance	+65°C to -10°C, 90% RH to 98% RH, Rated Voltage, 10 cycles (240 hrs.)	$\pm 0.05\%$	$\pm 0.02\%$	$\pm 0.02\%$	$\pm 0.01\%$
Shock	100G, 6 ms, Sawtooth Wave, X, Y, Z, each 10 shocks	$\pm 0.01\%$	$\pm 0.005\%$	$\pm 0.0025\%$	$\pm 0.001\%$
Vibration, High Frequency	20G, 10 Hz to 2,000 Hz to 10 Hz, 20 min., X, Y, Z, each 2.5 hrs.	$\pm 0.02\%$	$\pm 0.01\%$	$\pm 0.0025\%$	$\pm 0.001\%$
Life	125°C, Rated Power, 1.5 hr. – ON, 0.5 hr. – OFF, 2,000 hrs.	$\pm 0.05\%$	$\pm 0.02\%$	$\pm 0.015\%$	$\pm 0.005\%$
Storage Life	15°C to 35°C, 15% RH to 75% RH, No Load, 10,000 hrs.	$\pm 0.005\%$	$\pm 0.0025\%$	$\pm 0.0025\%$	$\pm 0.0015\%$
High Temperature Exposure	150°C, No Load, 2,000 hrs.	$\pm 0.05\%$	$\pm 0.02\%$	$\pm 0.015\%$	$\pm 0.005\%$
Current Noise		-32 dB		-42 dB	
Voltage Coefficient		0.0005%/V		0.00003%/V	
Thermal EMF		1.0 $\mu V/^{\circ}C$		1.0 $\mu V/^{\circ}C$	

PERFORMANCE – SLD					
Parameters	Test Condition	ALPHA Specification		ALPHA Typical Test Data	
		ΔR	$\Delta Ratio$	ΔR	$\Delta Ratio$
Maximum Rated Operating Temperature		70°C			
Working Temperature Range		-25°C to +125°C			
Thermal Cycling Overload	-25°C/30 min., Room Temperature/5 min., 125°C/30 min., 5 cycles Rated Voltage x 2.5, 5 sec.	$\pm 0.05\%$ $\pm 0.05\%$	$\pm 0.01\%$ $\pm 0.01\%$	$\pm 0.01\%$ $\pm 0.0025\%$	$\pm 0.005\%$ $\pm 0.001\%$
Solderability	235°C, 2 sec.	over 75% coverage		over 75% coverage	
Resistance to Solvents	Isopropyl Alcohol	no damage		no damage	
Low Temperature Operation	-25°C, No Load, 2 hrs. 0.908 kg (2 pounds), 10 sec.	$\pm 0.05\%$ $\pm 0.05\%$	$\pm 0.01\%$ $\pm 0.01\%$	$\pm 0.0025\%$ $\pm 0.0025\%$	$\pm 0.001\%$ $\pm 0.001\%$
Terminal Strength		over 10,000 M Ω		over 10,000 M Ω	
Dielectric Withstanding Voltage	Atmo. Pres.: AC 300V, 1 min. DC 100V, 1 min.	$\pm 0.03\%$	$\pm 0.01\%$	$\pm 0.0025\%$	$\pm 0.001\%$
Insulation Resistance		over 10,000 M Ω		over 10,000 M Ω	
Resistance to Soldering Heat	350°C, 3 sec.	$\pm 0.03\%$	$\pm 0.01\%$	$\pm 0.0025\%$	$\pm 0.001\%$
Moisture Resistance	+65°C to -10°C, 90% RH to 98% RH, Rated Voltage, 10 cycles (240 hrs.)	$\pm 0.1\%$	$\pm 0.05\%$	$\pm 0.03\%$	$\pm 0.01\%$
Shock	50G, 11 ms, Half-Sine Wave, X, Y, Z, each 3 shocks	$\pm 0.03\%$	$\pm 0.01\%$	$\pm 0.005\%$	$\pm 0.001\%$
Vibration	20G, 10 Hz to 55 Hz to 10 Hz, 1 min., X, Y, Z, each 2 hrs.	$\pm 0.03\%$	$\pm 0.01\%$	$\pm 0.005\%$	$\pm 0.001\%$
Life (Rated Load)	70°C, Rated Power, 1.5 hr. – ON, 0.5 hr. – OFF, 1,000 hrs.	$\pm 0.1\%$	$\pm 0.05\%$	$\pm 0.01\%$	$\pm 0.005\%$
Life (Moisture Load)	40°C 90% RH to 95% RH, Rated Power 1.5 hrs – ON, 0.5 hr. – OFF, 1,000 hrs.	$\pm 0.05\%$	$\pm 0.01\%$	$\pm 0.01\%$	$\pm 0.005\%$
Storage Life	15°C to 35°C, 15% RH to 75% RH, No Load, 10,000 hrs	$\pm 0.02\%$	$\pm 0.01\%$	$\pm 0.005\%$	$\pm 0.0025\%$
High Temperature Exposure	125°C, No Load, 1,000 hrs.	$\pm 0.05\%$	$\pm 0.01\%$	$\pm 0.01\%$	$\pm 0.005\%$

EXAMPLE OF APPLICATION

An application of type SM/SLD (input/feedback resistors for amplifiers) Because the input and the feedback resistors are incorporated into one single element, amplification is not affected by temperature range.



Disclaimer

ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase.

To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at vpgsensors.com.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay Precision Group:

[SLD1X10K00DB](#) [SLD1X10K00BQ](#) [SLD1X10K00FB](#) [SLD1X1K000AB](#) [SLD1X20K00FB](#) [SLD1X2K000AQ](#)
[SM2Y5K000/20K00BA](#) [SM2Y6K000/14K00BA](#) [SM2X5K000/13K90BB](#) [SM2X5K000/13K90FB](#) [SM2X9K000/1K000FA](#)
[SM2Y14K00/6K00BA](#) [SM2Y18K00/2K00BA](#) [SM2Y2K000/18K00BA](#) [SM2X10K00/2K048FQ](#) [SM2X2K000/20K00QT](#)
[SM2X2K000/3K000BQ](#) [SM2X2K000/3K000QT](#) [SM2X2K000/4K000QT](#) [SM2X30K00/992R0FQ](#) [SM1Y10K00BQ](#)
[SM1Y13K00BA](#) [SM1Y25K00AT](#) [SM1Y2K000QT](#) [SM1Y30K00AT](#) [SM1Y5K000BA](#) [SM1X30K00AA](#) [SM1X30K00BB](#)
[SM1X4K700BA](#) [SM1X5K000QT](#) [SM1Y10K00BA](#) [SM1Y10K00BB](#) [SM1X10K00BA](#) [SM1X10K00FB](#) [SM1X10K00FQ](#)
[SM1X15K00QT](#) [SM1X20K00BQ](#) [SM1X2K000BA](#) [SLD2Y1K000/13K00BB](#) [SLD2Y1K000/9K000AQ](#)
[SLD2Y2K000/4K500BA](#) [SLD2Y2K400/200R0BB](#) [SLD2Y2K400/450R0BB](#) [SLD2Y612R0/30K00BB](#)
[SLD2X1K000/9K000BQ](#) [SLD2X2K000/18K00AQ](#) [SLD2X2K000/20K00BA](#) [SLD2X2K000/8K000BA](#)
[SLD2X3K600/3K622BB](#) [SLD2Y130R0/30K00QQ](#) [SLD2X1K00/10K018AQ](#) [SLD2X1K000/10K00BA](#)
[SLD2X1K000/12K00AA](#) [SLD2X1K000/12K00AB](#) [SLD2X1K000/12K00BB](#) [SLD2X1K000/20K00BA](#) [SLD1Y20K00BQ](#)
[SLD1Y2K000BA](#) [SLD1Y5K000BA](#) [SLD1Y5K000BB](#) [SLD2X10K00/25K00BB](#) [SLD2X10K00/30K00BB](#)
[SLD1X2K000BQ](#) [SLD1X30K00AQ](#) [SLD1X30K00BA](#) [SLD1Y10K00BA](#) [SLD1Y200R0BA](#) [SLD1Y20K00BA](#)