


## 1477A Multi-Conductor - 300V Power-Limited Tray Cable



For more Information  
please call

1-800-Belden1

**General Description:**

18 AWG pairs stranded (7x26) bare copper conductors, twisted pairs, individually shielded plus an overall Beldfoil (100% coverage), PVC insulation, PVC jacket.

**Physical Characteristics (Overall)****Conductor**

AWG:

# Conductors	# Pairs	AWG	Stranding	Conductor Material
	12	18	7x26	BC - Bare Copper
1		22	7x30	BC - Bare Copper

Total Number of Conductors: 25

**Insulation**

Insulation Material:

Insulation Material
PVC - Polyvinyl Chloride

**Inner Shield**

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
20

Inner Shield Drain Wire Stranding: 7x28

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

**Outer Shield**

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
18	7x26	TC - Tinned Copper

**Outer Jacket**

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.064

Outer Jacket Ripcord: Yes

**Overall Cable**

Overall Nominal Diameter: 0.739 in.

**Pair**

Pair Color Code Chart:

Number	Color
1	Black & White and Numbered 1
2	Black & White and Numbered 2

**1477A Multi-Conductor - 300V Power-Limited Tray Cable**

3	Black & White and Numbered 3
4	Black & White and Numbered 4
5	Black & White and Numbered 5
6	Black & White and Numbered 6
7	Black & White and Numbered 7
8	Black & White and Numbered 8
9	Black & White and Numbered 9
10	Black & White and Numbered 10
11	Black & White and Numbered 11
12	Black & White and Numbered 12
Communication	Orange

**Mechanical Characteristics (Overall)**

<b>Operating Temperature Range:</b>	-30°C To +105°C
<b>Bulk Cable Weight:</b>	328 lbs/1000 ft.
<b>Max. Recommended Pulling Tension:</b>	779 lbs.
<b>Min. Bend Radius/Minor Axis:</b>	7.250 in.

**Applicable Specifications and Agency Compliance (Overall)****Applicable Standards & Environmental Programs**

<b>NEC/(UL) Specification:</b>	CMG, ITC-ER, PLTC-ER
<b>CEC/C(UL) Specification:</b>	CMG
<b>EU Directive 2011/65/EU (ROHS II):</b>	Yes
<b>EU CE Mark:</b>	Yes
<b>EU Directive 2000/53/EC (ELV):</b>	Yes
<b>EU Directive 2002/95/EC (RoHS):</b>	Yes
<b>EU RoHS Compliance Date (mm/dd/yyyy):</b>	04/01/2005
<b>EU Directive 2002/96/EC (WEEE):</b>	Yes
<b>EU Directive 2003/11/EC (BFR):</b>	Yes
<b>CA Prop 65 (CJ for Wire &amp; Cable):</b>	Yes
<b>MII Order #39 (China RoHS):</b>	Yes

**Flame Test**

<b>UL Flame Test:</b>	UL1685 FT4 Loading
<b>CSA Flame Test:</b>	FT4
<b>IEEE Flame Test:</b>	1202

**Suitability**

<b>Suitability - Indoor:</b>	Yes
<b>Suitability - Outdoor:</b>	Yes
<b>Suitability - Burial:</b>	Yes
<b>Sunlight Resistance:</b>	Yes

**Plenum/Non-Plenum**

<b>Plenum (Y/N):</b>	No
----------------------	----

**Surface Printing (Overall)**

<b>Surface Printing:</b>	BELDEN 1477A E34972 12PR18 1C22 SHIELDED (UL) CMG 105C OR PLTC OR ITC SUN RES DIR BUR AWM 2464 80C 300V OR C(UL) CMG----FT4 IEEE1202 (2 FT, 7 DIGIT SEQUENTIAL NUMBER) FEET
--------------------------	---

## 1477A Multi-Conductor - 300V Power-Limited Tray Cable

## Electrical Characteristics (Overall)

## Nom. Conductor DC Resistance:

Description	DCR @ 20°C (Ohm/1000 ft)
18 AWG	5.86
22 AWG	14.7

## Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
4.1

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 10.300 Ohm/1000 ft

## Max. Operating Voltage - UL:

Voltage
300 V RMS

## Max. Recommended Current:

Current
2.5 Amps per conductor @ 25°C

## Notes (Overall)

**Notes:** Alternate color coding available upon request.

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1477A 0061000	1,000 FT	342.000 LB	BLUE, LIGHT	C	12FS PR #18 + 1 #22 PVC FS PVC
1477A 0105000	5,000 FT	1,570.000 LB	BLACK	C Z	12 FS PR #18 +1 #22 PVC FS PVC

**Notes:**

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 4      Revision Date: 05-17-2015

© 2019 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1477A 0061000](#) [1477A 0105000](#)