

SPECIFICATIONS

1504

DESCRIPTION: 0-12VDC, 500mA Power Supply
INPUT VOLTAGE: 120VAC, 60Hz
ENVIRONMENTAL TEMPERATURE: 25°C

0-12VDC:	Min.	Max.
Output Voltage Range	0.1V	12V
Minimum Output Voltage		100mV
Maximum Output Voltage	12V	13.5V
Output Current	0.4A, typical	

VOLTAGE REGULATION:

Load (0-100% load)	400mV
Line (100-130VAC Variation)	200mV
Ripple & Noise	100mVp-p

12VAC:

Output Voltage No Load	12.5V	15V
Output Voltage Full Load	11.5V	
Output Current	0.5A, typical	

No Load Input current	50mA
Full Load Input Current (All rated load)	200mA
Fuse 1	1A, typical
Fuse 2	0.5A, typical

Dimensions (W X D X H): 101 mm x 140 mm x 83 mm

Weight: 0.90 kgs

Description:

This power supply gives you two outputs, 12VAC and a 0-12VDC. By offering two different outputs you can choose from either AC voltage or DC voltage.

Operation:

Plug model 1504 into an AC outlet. Turn power switch on. Adjust voltage with control knob. Connect to either 12VAC (constant) or 12VDC (variable).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[B&K Precision:](#)

[1504](#)