



Product: [1594A](#)

Category 5e Indoor/Outdoor Cable, 4 Pair, U/UTP, CMR/CMX

Product Description

Category 5e Premise Horizontal Cable (200MHz), Indoor/Outdoor, 4 Pair, 24 AWG Solid Bare Copper Conductors, U/UTP, Riser-CMR/CMX Outdoor, UV Resistant PVC Jacket

Technical Specifications

Product Overview

Suitable Applications:	Indoor/Outdoor, Premise Horizontal Cable, Ethernet 1000BASE-T, PoE++, PoE+, PoE
------------------------	---

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs
24 AWG	Solid	BC - Bare Copper	4

Insulation

Material	Color Code
PO - Polyolefin	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Outer Jacket

Material	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.220 in (5.59 mm)	Yes

Overall Cable Diameter (Nominal):	0.220 in (5.59 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
93.8 Ohm/km (28.6 Ohm/1000ft)	330 pF/100m

Delay

Frequency	Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.
100 MHz	537.6 ns/100m	45 ns/100m	68%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted) [Ohm]	Max./Min. Fitted Impedance [Ohm]
1	2.0 dB/100m	65.3	62.3	63.3	60.3	63.8	60.8	20.0	100 ± 15	100 ± 15
4	4.1 dB/100m	56.3	53.3	52.2	49.2	51.7	48.7	23.0	100 ± 15	100 ± 15
8	5.8 dB/100m	51.8	48.8	46.0	43.0	45.7	42.7	24.5	100 ± 15	100 ± 15
10	6.5 dB/100m	50.3	47.3	43.8	40.8	43.8	40.8	25.0	100 ± 15	100 ± 15
16	8.2 dB/100m	47.3	44.2	39.0	36.0	39.7	36.7	25.0	100 ± 15	100 ± 15
20	9.3 dB/100m	45.8	42.8	36.5	33.5	37.7	34.7	25.0	100 ± 15	100 ± 15
25	10.4 dB/100m	44.3	41.3	33.9	30.9	35.8	32.8	24.3	100 ± 15	100 ± 15
31.25	11.7 dB/100m	42.9	39.9	31.2	28.2	33.9	30.9	23.6	100 ± 15	100 ± 15
62.5	17.0 dB/100m	38.4	35.4	21.4	18.4	27.8	24.8	21.5	100 ± 15	100 ± 15

100	22.0 dB/100m	35.3	32.3	13.3	10.3	23.8	20.8	20.1	100 ± 15	100 ± 15
155	28.1 dB/100m	32.5	29.4	4.4	1.4	19.9	16.9	15.8	100 ± 25	100 ± 15
200	32.4 dB/100m	30.8	27.8			17.7	14.7	15.0	100 ± 25	100 ± 15

Voltage

UL Voltage Rating
300 V (CMR), 300 V (CMX-Outdoor)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
90°C	-40°C To +75°C	-25°C To +75°C	-40°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
1.0 in (25 mm)	2.25 in (57.2 mm)

Max. Pull Tension:	25 lbs (11 kg)
Bulk Cable Weight:	23 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, Aerial - When supported by messenger wire
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Reaction to Fire:	UL 1666 Riser, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CMR, CMX-Outdoor
CEC / C(UL) Compliance:	CMX-Outdoor
ICEA Compliance:	S-90-661, S-56-434, S-99-689, S-100-685
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3
NEMA Compliance:	NEMA WC-63.1
Data Category:	Category 5e
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 5e
Third Party Performance Verification:	Category 5e
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	1585A
Non-Plenum Number:	1583A

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	---

History

Update and Revision:	Revision Number: 0.552 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
1594A 008U1000	Gray	UnReel	1,000 ft	612825118756
1594A 1GFU1000	Ivory	UnReel	1,000 ft	612825118770
1594A 009U1000	White	UnReel	1,000 ft	612825118763

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1594A 008U1000](#)