



Feature -

small size
bi-color LED illuminated available
right angle and vertical PCB terminal
SPDT, DPDT, lock / non-lock function

Application -

consumer products
computer products
instrumentation
communication equipments

► **SPECIFICATIONS**

SWITCH SPECIFICATIONS	
POLE - POSITION	1P2T, 2P2T LOCK / NON-LOCK Action with LED
CONTACT RATING	30 VDC, 0.1A / 5 VDC, 0.1mA
CONTACT RESISTANCE	50 mΩ MAX. 1.5 V DC; 100 mA, by Method of Voltage DROP
INSULATION RESISTANCE	100 MΩ MIN. 500 V DC
DIELECTRIC STRENGTH	Breakdown is not Allowable; 500 V AC for 1 Minute
OPERATING FORCE	250 ± 100 gf
OPERATING LIFE	50,000 cycles
OPERATING TEMPERATURE RANGE	-20°C ~ 70°C
TOTAL TRAVEL	TRAVEL - 0.7 ± 0.3 mm FULL TRAVEL - 1.5 ± 0.3 mm

LED SPECIFICATIONS		Value / LED Color					
	Unit						
		Blue	Green	Red	White	Yellow	
FORWARD CURRENT	If	mA	10	20	20	2	20
REVERSE VOLTAGE	Vr	V	5.0	5.0	5.0	5.0	5.0
REVERSE CURRENT	Ir	μA	10	10	10	10	10
FORWARD VOLTAGE	Vf	V	@ 10mA 3.0-4.0	2.1-2.5	2.0-2.5	@ 2mA 2.8-4.0	2.0-2.5
LUMINOUS INTENSITY	Iv	mcd	@ 10mA 200	800	1800	@ 2mA 12	1800

■ Physical and electrical information of LED will be provided upon customer's request on switches.

► **HOW TO ORDER**


PS004	-	L	2	2	N	P	X	X	X		U	G	X	X																																																																																											
		<table><tr><td colspan="2">OPERATION</td></tr><tr><td>N</td><td>NON-LOCK (std.)</td></tr><tr><td>L</td><td>LOCK TYPE</td></tr><tr><td>T</td><td>TACTILE</td></tr></table>		OPERATION		N	NON-LOCK (std.)	L	LOCK TYPE	T	TACTILE	<table><tr><td colspan="2">POSITION</td></tr><tr><td>2</td><td>2 POSITION (std.)</td></tr></table>		POSITION		2	2 POSITION (std.)			<table><tr><td colspan="2">TERMINAL</td></tr><tr><td>P</td><td>P.C.B TYPE (std.)</td></tr><tr><td>R</td><td>RIGHT ANGLE TYPE</td></tr><tr><td>R1</td><td>RIGHT ANGLE TYPE 1</td></tr><tr><td>R2</td><td>RIGHT ANGLE TYPE 2</td></tr><tr><td>R3</td><td>RIGHT ANGLE TYPE 3</td></tr><tr><td>R4</td><td>RIGHT ANGLE TYPE 4</td></tr></table>		TERMINAL		P	P.C.B TYPE (std.)	R	RIGHT ANGLE TYPE	R1	RIGHT ANGLE TYPE 1	R2	RIGHT ANGLE TYPE 2	R3	RIGHT ANGLE TYPE 3	R4	RIGHT ANGLE TYPE 4			<table><tr><td colspan="2">HOUSING COLOR</td></tr><tr><td>K</td><td>BLACK (std.)</td></tr><tr><td>G</td><td>GRAY</td></tr><tr><td>W</td><td>WHITE</td></tr><tr><td>X</td><td>WITHOUT</td></tr></table>		HOUSING COLOR		K	BLACK (std.)	G	GRAY	W	WHITE	X	WITHOUT			<table><tr><td colspan="2">CAP SYMBOL</td></tr><tr><td colspan="2">Please refer to appendix 1(knob)</td></tr><tr><td colspan="2">For example</td></tr><tr><td>K3</td><td> PK3:Printing</td></tr><tr><td>E1</td><td> K3:Laser carving</td></tr><tr><td></td><td> PE1:Printing</td></tr><tr><td>☐</td><td>E1:Laser carving</td></tr><tr><td></td><td>WITHOUT</td></tr></table>		CAP SYMBOL		Please refer to appendix 1(knob)		For example		K3	 PK3:Printing	E1	 K3:Laser carving		 PE1:Printing	☐	E1:Laser carving		WITHOUT			<table><tr><td colspan="2">LED COLOR</td></tr><tr><td>B</td><td>BLUE</td></tr><tr><td>G</td><td>GREEN</td></tr><tr><td>R</td><td>RED</td></tr><tr><td>W</td><td>WHITE</td></tr><tr><td>Y</td><td>YELLOW</td></tr><tr><td>X</td><td>WITHOUT</td></tr></table>		LED COLOR		B	BLUE	G	GREEN	R	RED	W	WHITE	Y	YELLOW	X	WITHOUT			<table><tr><td colspan="2">LED COLOR</td></tr><tr><td>B</td><td>BLUE</td></tr><tr><td>G</td><td>GREEN</td></tr><tr><td>R</td><td>RED</td></tr><tr><td>W</td><td>WHITE</td></tr><tr><td>Y</td><td>YELLOW</td></tr><tr><td>X</td><td>WITHOUT</td></tr></table>		LED COLOR		B	BLUE	G	GREEN	R	RED	W	WHITE	Y	YELLOW	X	WITHOUT
OPERATION																																																																																																									
N	NON-LOCK (std.)																																																																																																								
L	LOCK TYPE																																																																																																								
T	TACTILE																																																																																																								
POSITION																																																																																																									
2	2 POSITION (std.)																																																																																																								
TERMINAL																																																																																																									
P	P.C.B TYPE (std.)																																																																																																								
R	RIGHT ANGLE TYPE																																																																																																								
R1	RIGHT ANGLE TYPE 1																																																																																																								
R2	RIGHT ANGLE TYPE 2																																																																																																								
R3	RIGHT ANGLE TYPE 3																																																																																																								
R4	RIGHT ANGLE TYPE 4																																																																																																								
HOUSING COLOR																																																																																																									
K	BLACK (std.)																																																																																																								
G	GRAY																																																																																																								
W	WHITE																																																																																																								
X	WITHOUT																																																																																																								
CAP SYMBOL																																																																																																									
Please refer to appendix 1(knob)																																																																																																									
For example																																																																																																									
K3	 PK3:Printing																																																																																																								
E1	 K3:Laser carving																																																																																																								
	 PE1:Printing																																																																																																								
☐	E1:Laser carving																																																																																																								
	WITHOUT																																																																																																								
LED COLOR																																																																																																									
B	BLUE																																																																																																								
G	GREEN																																																																																																								
R	RED																																																																																																								
W	WHITE																																																																																																								
Y	YELLOW																																																																																																								
X	WITHOUT																																																																																																								
LED COLOR																																																																																																									
B	BLUE																																																																																																								
G	GREEN																																																																																																								
R	RED																																																																																																								
W	WHITE																																																																																																								
Y	YELLOW																																																																																																								
X	WITHOUT																																																																																																								
		<table><tr><td colspan="2">POLE</td></tr><tr><td>2</td><td>2 POLE (std.)</td></tr><tr><td>1</td><td>1 POLE</td></tr></table>		POLE		2	2 POLE (std.)	1	1 POLE	<table><tr><td colspan="2">TIMING</td></tr><tr><td>N</td><td>NON - SHORTING (std.)</td></tr></table>		TIMING		N	NON - SHORTING (std.)	<table><tr><td colspan="2">FRAME</td></tr><tr><td>X</td><td>WITHOUT</td></tr><tr><td>S1</td><td>SQUARE</td></tr><tr><td>S2</td><td>SQUARE</td></tr><tr><td>S2H</td><td>SQUARE</td></tr><tr><td>S3</td><td>SQUARE</td></tr><tr><td>R1</td><td>ROUND</td></tr><tr><td>R1A</td><td>ROUND</td></tr><tr><td>R2</td><td>ROUND</td></tr><tr><td>R2.1</td><td>ROUND</td></tr><tr><td>R2H</td><td>ROUND</td></tr><tr><td>R2A</td><td>ROUND H=6.2</td></tr><tr><td>R2B</td><td>ROUND H=7.2</td></tr><tr><td>R2C</td><td>ROUND</td></tr><tr><td>R2D</td><td>ROUND</td></tr><tr><td>R3</td><td>ROUND</td></tr></table>		FRAME		X	WITHOUT	S1	SQUARE	S2	SQUARE	S2H	SQUARE	S3	SQUARE	R1	ROUND	R1A	ROUND	R2	ROUND	R2.1	ROUND	R2H	ROUND	R2A	ROUND H=6.2	R2B	ROUND H=7.2	R2C	ROUND	R2D	ROUND	R3	ROUND	<table><tr><td colspan="2">CAP COLOR</td></tr><tr><td>T</td><td>Transparent (std.)</td></tr><tr><td>X</td><td>WITHOUT</td></tr><tr><td>N</td><td>GREEN</td></tr><tr><td>R</td><td>RED</td></tr><tr><td>Y</td><td>YELLOW</td></tr><tr><td>B</td><td>BLUE</td></tr><tr><td>S</td><td>SILVER</td></tr></table>		CAP COLOR		T	Transparent (std.)	X	WITHOUT	N	GREEN	R	RED	Y	YELLOW	B	BLUE	S	SILVER	<table><tr><td colspan="2">LED BRIGHTNESS</td></tr><tr><td>U</td><td>ULTRA (std.)</td></tr><tr><td>R</td><td>REGULAR</td></tr><tr><td>X</td><td>WITHOUT</td></tr></table>		LED BRIGHTNESS		U	ULTRA (std.)	R	REGULAR	X	WITHOUT	<table><tr><td colspan="2">LED BRIGHTNESS</td></tr><tr><td>U</td><td>ULTRA (std.)</td></tr><tr><td>R</td><td>REGULAR</td></tr><tr><td>X</td><td>WITHOUT</td></tr></table>		LED BRIGHTNESS		U	ULTRA (std.)	R	REGULAR	X	WITHOUT																		
POLE																																																																																																									
2	2 POLE (std.)																																																																																																								
1	1 POLE																																																																																																								
TIMING																																																																																																									
N	NON - SHORTING (std.)																																																																																																								
FRAME																																																																																																									
X	WITHOUT																																																																																																								
S1	SQUARE																																																																																																								
S2	SQUARE																																																																																																								
S2H	SQUARE																																																																																																								
S3	SQUARE																																																																																																								
R1	ROUND																																																																																																								
R1A	ROUND																																																																																																								
R2	ROUND																																																																																																								
R2.1	ROUND																																																																																																								
R2H	ROUND																																																																																																								
R2A	ROUND H=6.2																																																																																																								
R2B	ROUND H=7.2																																																																																																								
R2C	ROUND																																																																																																								
R2D	ROUND																																																																																																								
R3	ROUND																																																																																																								
CAP COLOR																																																																																																									
T	Transparent (std.)																																																																																																								
X	WITHOUT																																																																																																								
N	GREEN																																																																																																								
R	RED																																																																																																								
Y	YELLOW																																																																																																								
B	BLUE																																																																																																								
S	SILVER																																																																																																								
LED BRIGHTNESS																																																																																																									
U	ULTRA (std.)																																																																																																								
R	REGULAR																																																																																																								
X	WITHOUT																																																																																																								
LED BRIGHTNESS																																																																																																									
U	ULTRA (std.)																																																																																																								
R	REGULAR																																																																																																								
X	WITHOUT																																																																																																								






► DIMENSION


PS004-L22NPXXX□□□□




PS004-L22NPS1KT□□□□




PS004-N22NPS2KT□□□□




PS004-N22NPS2HKK□□□□




PS004-L22NPS3XT□□□□




PS004-L22NPR1AXT□□□□



PS004-L22NPR1KT□□□□




PS004-N22NPR2KT□□□□




► DIMENSION


PS004-L22NPR2.1KT□□□□




PS004-N22NPR2HKK□□□□




PS004-N22NPR3KT□□□□




PS004-L22NPR2ABT□□□□




PS004-L22NPR2BBT□□□□




PS004-L22NPR2CBT□□□□




PS004-L22NPR2DBT□□□□




PS004-N22NRXXX□□□□




PS004-N22NRS1XT□□□□




PS004-N22NRS1KT□□□□




PS004-N22NR1S1XT□□□□





PS004-N22NR2S1KT□□□



PS004-N22NR3S1KT□□□□




PS004-N22NR4S1XT□□□□



STANDARD TYPE



RIGHT ANGLE TYPE



- FRAME : PA + GF
- ACTUATOR : PA + GF
- BASE : PA + GF
- TERMINAL : BRASS ; SILVER PLATING
- SPRING : STAINLESS STEEL

	0	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19
A	0	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19
B	A	B	C	D	E	F	G	H	I	J	CH5	CH6	DSK	PIP	C-KEY	CUT	TAKE	REC	ENG	PROG
C	K	L	M	N	O	P	Q	R	S	T	REPLAY	RET1	RET2	KEY ON	AUTO TAKE					
D	U	V	W	X	Y	Z	POWER	ON OFF	ON	OFF		USER A	USER B	USER C	USER D	USER E	USER F	USER G	USER H	USER I
E	OK		Auto	Enter	Start	STOP	OPEN	CLOSE	Exit	Move	USER J									
F	SET	Reset	Light	Alarm	Menu	Next	Back	Delete	Motor	Save										
G	Up	Down	Right	Left	Test	End	Insert	Lock	Print	+/-										
H	ESC	BC.	HOME	Health	D-LED 2	OC GENIE	VIDEO INPUT	clr CMOS	Green Power	Save OK										
I	B/R +	Undo Cancel	T/L -	F1	F2	F3	F4	F5	F6	F7										
J	F8	F9	F10	F11	F12	F13	F14	IN 1	IN 2	IN 3										
K	IN 4	IN 5	IN 6																	
L	+	-	x	+	=	↑	→	▲	▶	▶										
M																				
N	↑	→	▲	◀	▶	◀	▶	◀	▶	◀										
O																				
P																				
Q	ME3	ME4	BGND 3D DVE1	BGND 3D DVE2	BUS COLOR	ME BUTTON LINK	*	INSERT	WIPE											
R	⏮	ALL		VP		COPY		RECORD MODE	↑											
S			MUTE																	
T			group																	
U			chair																	
V			OC			CLEAR	CROSS WIND	AMMO TEMP	BARO PRESS	AIR TEMP										
W	BORE-SIGHT	CANT	LEAD	RANGE	MRS	ZERO	TEST	UD	LR											
X	ID	Disp	MF	GALL		BAND	SETUP	MODE	LINK	FUNC.										
Y	SHIFT					DEL														
Z				RUN	2D	3D	CH1	CH2	CH3	CH4										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Well Buying:

[PS004-L22NPR2DBKH5UBXX-1](#) [PS004-L22NPS3XTURXX](#) [PS004-N22NR1S1XTUGXX](#) [PS004-N22NR2S1KTURXX](#)
[PS004-L22NPR1AXTUGXX](#) [PS004-L22NPR1AXTURXX](#) [PS004-L22NPR1AXTUYXX](#) [PS004-L22NPS1KTUGXX](#)
[PS004-L22NPS1KTURXX](#) [PS004-L22NPS1KTUYXX](#) [PS004-N22NPR1AXBUBXX](#) [PS004-N22NPR1KTUGXX](#) [PS004-](#)
[N22NPR1AXTURUG](#) [PS004-N22NPR1AXRURXX](#) [PS004-N22NPR1AXTUYXX](#) [PS004-N22NPS1KTUGXX](#) [PS004-](#)
[N22NPS1KTURXX](#) [PS004-N22NPS1KTUYXX](#) [PS004-L12NRR1XTUBXX](#)