



Product: [1694F](#)

75 Ohm SDI Coax, RG-6, 19 AWG Str BC, Double 95% TC Braid, PVC Jkt, CM, Flexible

Product Description

75 Ohm SDI Coax, RG-6, 19 AWG (7x27) Bare Copper Conductor, PE Insulation, Double 95% Tinned Copper Braid Shield, PVC Jacket, CM, Flexible

Technical Specifications

Product Overview

Suitable Applications:	Digital Video, 6 Gb/s UHDTV, HD-SDI 1080p
------------------------	---

Construction Details

RG Type:	6
----------	---

Conductor

Element	Size	Stranding	Nom. Diameter	Material
Coax(es)	19 AWG	7x27	0.041 in	BC - Bare Copper

Insulation

Element	Material	Nom. Insulation Diameter	Color Code
Coax(es)	PE - Polyethylene (Foam)	0.180 in (4.57 mm)	White

Outer Shield

Layer	Outer Shield Type	Material	Coverage
1	Braid	Tinned Copper (TC)	95%
2	Braid	Tinned Copper (TC)	95%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.276 in (7.01 mm)

Overall Cable Diameter (Nominal):	0.276 in (7.01 mm)
-----------------------------------	--------------------

Electrical Characteristics

Return Loss (RL)

Frequency	Min. Return Loss
5 - 850 MHz	20 dB
850 - 6000 MHz	15 dB

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.24 dB/100ft
3.58 MHz	0.45 dB/100ft
5 MHz	0.54 dB/100ft
6 MHz	0.55 dB/100ft
7 MHz	0.62 dB/100ft
10 MHz	0.72 dB/100ft
12 MHz	0.83 dB/100ft
25 MHz	1.18 dB/100ft

55 MHz	1.76 dB/100ft
67.5 MHz	1.9 dB/100ft
71.5 MHz	2.0 dB/100ft
88.5 MHz	2.2 dB/100ft
100 MHz	2.4 dB/100ft
135 MHz	2.8 dB/100ft
143 MHz	2.9 dB/100ft
180 MHz	3.3 dB/100ft
270 MHz	4.0 dB/100ft
360 MHz	4.7 dB/100ft
540 MHz	5.9 dB/100ft
720 MHz	6.9 dB/100ft
750 MHz	7.1 dB/100ft
1000 MHz	6.3 dB/100ft
1500 MHz	7.8 dB/100ft
2000 MHz	12.5 dB/100ft
2250 MHz	13.4 dB/100ft
3000 MHz	15.9 dB/100ft
4500 MHz	20.6 dB/100ft
6000 MHz	28.7 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
8.5 Ohm/1000ft	1.7 Ohm/1000ft (5.6 Ohm/km)	17.0 pF/ft (55.8 pF/m)	75 Ohm	80%

Voltage

UL Voltage Rating
300 V (CM)

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C	-35°C to +75°C

Bend Radius

Installation Min.
2.75 in (69.9 mm)

Max. Pull Tension:	90 lbs (41 kg)
Bulk Cable Weight:	50 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1685 - UL Loading
NEC / UL Compliance:	CM
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.527 Revision Date: 07-03-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
1694F B591000	Black, Matte	Reel	1,000 ft	612825356196	C
1694F B59N1000	Black, Matte	Reel w/Small Barrel	1,000 ft		
1694F B595000	Black, Matte	Reel	5,000 ft	612825439813	
1694F G7X1000	Blue, Matte	Reel	1,000 ft	612825356110	C
1694F G7X5000	Blue, Matte	Reel	5,000 ft	612825439851	

1694F G7W1000	Green, Matte	Reel	1,000 ft	612825356127	C
1694F G7W5000	Green, Matte	Reel	5,000 ft	612825439837	
1694F G8L1000	Orange, Matte	Reel	1,000 ft	612825356097	C
1694F G8L5000	Orange, Matte	Reel	5,000 ft	612825439899	
1694F G7V1000	Red, Matte	Reel	1,000 ft	612825356134	C
1694F G7V5000	Red, Matte	Reel	5,000 ft	612825440468	
1694F Z4B1000	Violet	Reel	1,000 ft	612825358176	C
1694F Z4B5000	Violet	Reel	5,000 ft	612825439912	
1694F G7Y1000	White, Matte	Reel	1,000 ft	612825356103	C
1694F G7Y5000	White, Matte	Reel	5,000 ft	612825439882	
1694F G8M1000	Yellow, Matte	Reel	1,000 ft	612825356080	C
1694F G8M5000	Yellow, Matte	Reel	5,000 ft	612825439905	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1694F B591000](#) [1694F G7W1000](#) [1694F G7X1000](#) [1694F G8L1000](#) [1694F G7V1000](#) [1694F Z4B1000](#) [1694F](#)
[G8M1000](#) [1694F G7Y1000](#)