


Feature -


with screw mount installation
 wire and PCB terminal











Application -

consumer products
 computer products
 instrumentation
 communication equipments

SPECIFICATIONS

SWITCH SPECIFICATIONS	
POLE - POSITION	SPST , Momentary and Lock Type are Available
CONTACT RATING	120 V AC or 28 V DC , 1 A
CONTACT RESISTANCE	30 mΩ MAX. 1.5 V DC ; 100 mA , by Method of Voltage DROP
INSULATION RESISTANCE	100 MΩ MIN. 500 V DC
DIELECTRIC STRENGTH	Breakdown is not Allowable ; 500 V AC for 1 Minute
OPERATING FORCE	650 ± 150 gf
OPERATING LIFE	10,000 cycles
OPERATING TEMPERATURE RANGE	-20°C ~ 70°C
TOTAL TRAVEL	3.3 ± 0.3 mm

HOW TO ORDER


▶ DIMENSION			
RP - MWNS		RP - PBNS	RP - SPL
			
▶ FRAME TYPE			▶ P.C.B LAYOUT
S TYPE	P TYPE	M TYPE	RP - □P□□  RP - □B□□ 
			
▶ TERMINAL TYPE			
W TYPE	P TYPE	B TYPE	
			
▶ CIRCUIT		▶ MATERIAL	
		■ FRAME : BRASS NICKEL PLATED ■ ACTUATOR : POM ■ BASE FRAME : PA66 ■ TERMINAL : BRONZE SILVER PLATING	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Well Buying:](#)

[RP-MWLL](#) [RP-MWNL](#) [RP-MWNS](#) [RP-PBLS](#) [RP-PBNS](#) [RP-PPLS](#) [RP-SBLS](#) [RP-SBNS](#) [RP-SPLS](#) [RP-SPNS](#) [RP-SWLL](#) [RP-SWLS](#) [RP-SWNS](#)