








DIMENSION	TOLERANCE
BELOW 10 mm	± 0.3
10-100 mm	± 0.5
ABOVE 100 mm	± 0.8
ANGLE	± 3°




P.C.B LAYOUT



1. RATING : 12 V DC , 50 mA
2. TRAVEL : 0.25 ± 0.1mm
3. OPERATING FORCE : 160 ± 50 gf
4. CONTACT RESISTANCE : 100 mΩ MAX.
5. LIFE : 80,000 CYCLES
6. LEAD FREE

CIRCUIT DIAGRAM



△				DATE	2010/10/5	UNIT	mm	MODE	TACT SWITCH
△				APPROVAL	KAVEN	SCALE	1 : 1	PART	TC010-N21AAAA
△				CONFIRM	ALAN	VIEW	☯	2D FILE NAME	TC010-N21AAAA
	DATE	APPROVAL	DESIGN	ENGINEERING CHANGE DESCRIPTION					
				DESIGN	HEEGU	VER.	01	3D FILE NAME	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Well Buying:](#)

[TC010-N21AAAA](#)