

WASB-2400-20-SMAM Datasheet

Single-Band 2.4 GHz Dipole Antenna

Revision 1.2 Aug 17, 2021

Copyright © *2021 Wi2Wi, Inc.* 1879 Lundy Ave, Suite 218, San Jose, CA 95131, United States Email: <u>sales@wi2wi.com</u> | Phone: 1-408-416-4200 | Fax: 1-608-831-3343



Disclaimers

Wi2Wi, Inc. PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE MANAGING DIRECTOR OF Wi2Wi, Inc.

The definitions used herein are:

a) Life support devices or systems are devices which (1) are intended for surgical implant into the body, or (2) support or sustain life and whose failure to perform when properly used in accordance with the instructions for use provided in the labeling can reasonably be expected to result in a significant injury to the user. b) A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Wi2Wi does not assume responsibility for use of any of the circuitry described, no circuit patent licenses are implied and Wi2Wi reserves the right at any time to change without notice said circuitry and specifications.

The content of this document is to be treated as strictly confidential and is not to be disclosed, reproduced or used, except as authorized in writing by Wi2Wi, Inc.



1. Overview

WASB-2400-20-SMAM is a single-band, omni-directional, multi-position, dipole antenna with an SMA Plug (SMA Male port); hence it requires a connector cable with RP SMA Plug (SMA Female port).

Omni-directional antennas radiate equally well in all directions and are best used to spread a signal uniformly over some area. The dBi rating of an antenna specifies the amount of gain the antenna has in a particular direction. An antenna gain of 0dBi specifies an antenna that radiates all power uniformly over a sphere. For a dipole antenna, the radiation pattern is toroidal; and signal transmission and reception is best on the broad side of the antenna (i.e. horizontally placed from the antenna). The higher the gain of a dipole antenna, the stronger the signal is in the horizontal directions and the weaker the signal will be in the vertical (elevated) directions. Hence a high gain dipole antenna may not be ideal for a multi-story building, but it will be good to disperse a signal omni-directionally across a single floor. This antenna is designed for Wireless Communications.



Figure 3: WASB-2400-20-SMAM at 90°





Figure 4: WASB-2400-20-SMAM showing SMA Plug (SMA Male) connector

2. Specification

Antenna Type	:	Dipole
Frequency	:	2.4GHz – 2.5GHz
Polarization	:	Linear Vertical
Gain Factor	:	2 dBi
VSWR	:	≤ 1.5 : 1
Impedance	:	50 Ω
Operating Temperature	:	-40°C to +85°C
Antenna's Port	:	SMA Plug (SMA Male)
Mating Connector Type	:	RP SMA Plug (SMA Female)
Weight	:	13 grams
Size	:	105mm (Len) x 10mm (Dia)
Antenna Color	:	Matte Black



3. Performance Graphs



Figure 5: Reflection Coefficient vs Frequency



Figure 6: VSWR vs Frequency



4. Radiation Patterns







Figure 8: E-PLANE Radiation Pattern

WASB-2400-20-SMAM



5. Mechanical Drawing



Figure 9: Antenna Drawing with Dimensions



6. Part Ordering

Part Order Number	Description
WASB-2400-20-SMAM	Dipole Antenna, Single-Band 2.4 GHz, SMA-Male
	Gain = 2 dBi (2.4 GHz)
WADB-2458-23-SMAM	Dipole Antenna, Dual-Band 2.4/5 GHz, SMA-Male
	Gain = 2 dBi (2.4 GHz) / 3 dBi (5 GHz)
WACC-MHF4-SMAF-100-113	Antenna Connector Cable, MHF4-Female, SMA-Female
	Length = 100 mm, Diameter = 1.13 mm

7. Revision History

Revision	Revision Date	Originator	Changes
1.0	07/12/2017	Wi2Wi	Initial version Datasheet
1.1	10/13/2017	Wi2Wi	Added graphs
1.2	08/17/2021	Wi2Wi	Added Temperature Information

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Wi2Wi: WASB-2400-20-SMAM