

2021



PROFESSIONAL TORQUE CONTROL



COMPLETE TORQUE CONTROL PROGRAM




Wiha TorqueFix Wing Handles & Blades

DESCRIPTION	Page
 TorqueFix Handle	4
 Hex Metric Blades	4
 TORX Blades	4
 TORXPlus Blades	4

Wiha Torque QuickCheck

DESCRIPTION	Page
 Torque QuickCheck	4

Wiha TorqueControl Tools

DESCRIPTION	Page
 TorqueFix Handle	5
 TorqueVario Handle	5
 TorqueVario Handle (Newton Meter Scale)	5
 Standard Blades Slotted, Phillips, Torx®, TorxPlus®, Hex	6
 MicroBits Slotted, Phillips, Torx®, Security Torx® Hex, Security Hex, Pentalobe & Nut Setters	9
 TorqueControl Sets	10-11

Wiha TorqueControl Blades & Bits

DESCRIPTION	Page
 Standard Blades Slotted, Phillips, Torx®, TorxPlus®, Hex	6
 MicroBits Slotted, Phillips, Torx®, Security Torx® Hex, Security Hex, Pentalobe & Nut Setters	9

Wiha EasyTorque Handles

DESCRIPTION	Page
 EasyTorque Handles	7
 EasyTorque TORX	7
 EasyTorque TORXPlus	7

Wiha iTorque Handles & Sets

DESCRIPTION	Page
 iTorque Handles	8
 iTorque Sets	8

Wiha TorqueControl Accessories

DESCRIPTION	Page
 TorqueControl Adapters	6-7
 Torque Cable Key	7


Wiha Torque SlimLine Insulated Tools

DESCRIPTION	Page
 TorqueVario Handle	12
 Insulated Blade Holder	12
 Insulated SlimLine Blades Slotted, Phillips, Terminal, TORX, Square	13
 Ins. Torque SlimLine Sets	14
 Ins TorqueRatchet	15

Wiha TorqueControl T-handle Tools

	DESCRIPTION	Page
	T-handle Torque Tools	15
	Blades	15

Wiha TorqueControl ESD Safe Tools

DESCRIPTION		Page
	TorqueVario Handle	16
	ESD Safe Blades	16
	ESD Safe Set TorqueVario	16

Notes:

TorqueVario-S ESD was developed for use in anti-static environments and TorqueVario-S ESD provides safety when working with electronic components. All Wiha TorqueVario-S models have an integrated window scale that displays the torque value - a completely new design, which eliminates false readings. The torque value is continuously adjustable by using the provided adjustment tool (TorqueSetter) this prevents the setting from being altered unintentionally.

Wiha TorqueFix Wing Keys Handles & Blades

- Audible Click At Torque
- Replaceable Blades
- +/- 6% Repeatability
- Extremely Compact
- Quick Turning Zone



Low profile
for easy access

Small &
Compact

Very slim blade diameter for
hard to reach screws

Torque tool for very tight
machine assembly spaces



EN ISO 6798,
BS EN 26789, ASME
B107.14M

+/- 6% Accuracy

Includes Calibration
Certificate



283 TorqueFix Wing Handles

Audible & perceptible click when torque setting
has been attained.

Item					
No.	Nm	mm	Inch	pkg.	lbs.
28349	0.5	68	2.7	1	.28
28351	0.6	68	2.7	1	.28
28352	0.9	68	2.7	1	.28
28353	1.1	68	2.7	1	.28
28354	1.2	68	2.7	1	.28
28355	1.4	68	2.7	1	.28
28356	2.0	68	2.7	1	.28
28357	2.5	68	2.7	1	.28
28358	3.0	68	2.7	1	.28
28359	3.8	68	2.7	1	.28
28360	4.0	68	2.7	1	.28



283 Hex Metric Blades For TorqueFix

Wing Handles CVM steel, through-hardened,
titanium silver.

Item					
No.	Size	Nm	Inch	mm	lbs.
28361	1.5	0.9	3.0	75	.03
28362	2.0	1.8	3.0	75	.03
28363	2.5	3.8	3.0	75	.03
28364	3.0	5.5	3.0	75	.03
28365	4.0	8.0	3.0	75	.03



283 TORX® Blades For TorqueFix

Wing Handles CVM steel, through-hardened,
titanium silver.

Item					
No.	Size	Nm	Inch	pkg.	lbs.
28374	T6	0.6	3.0	1	.03
28375	T7	0.9	3.0	1	.03
28376	T8	1.3	3.0	1	.03
28377	T9	2.5	3.0	1	.03
28378	T10	3.8	3.0	1	.03
28379	T15	5.5	3.0	1	.03
28380	T20	8.0	3.0	1	.03
28381	T25	8.0	3.0	1	.03



283 TORXPlus® Blades For TorqueFix

Wing Handles CVM steel, through-hardened,
titanium silver.

Item					
No.	Size	Nm	Inch	pkg.	lbs.
28382	IP6	0.8	3.0	1	.03
28383	IP7	1.3	3.0	1	.03
28384	IP8	2.0	3.0	1	.03
28385	IP9	3.0	3.0	1	.03
28386	IP10	4.5	3.0	1	.03
28387	IP15	6.6	3.0	1	.03
28388	IP20	8.0	3.0	1	.03
28389	IP25	8.0	3.0	1	.03



Loosening
torque approx.
+30% greater
than tightening
torque

3.9" OAL w/Blade

Wiha Torque QuickCheck

Quickly and easily test the iTorque® and
TorqueVario® handles to check the precision
of the set torque value before each use.
Only suitable for all Wiha torque handles
which can be configured to a check value
of 2.8 Nm.



28897 Torque QuickCheck

Includes Torque checker, adapter blades
and 2 batteries

Item			
No.	Nm	pkg.	lbs.
28897	2.8	1	1.49

Wiha torque screwdriver is inserted into Torque
QuickCheck along with the enclosed adapter
blades to verify how precise the torque tool is.
The LED light then clearly indicates the result in
traffic light colors.



Wiha Adjustable TorqueControl Tools

Wiha TorqueControl Screwdrivers

- **TorqueFix** factory preset torque
- **TorqueVario** adjustable torque drivers

molded cushion grip two component handles allow for maximum achievable torque to be reached with comfort.

Precise repeatability!

All TorqueFix & TorqueVario tools are tested and comply with:

- **EN ISO 6789**
- **BS EN 26789**
- **ASME B107.14M**

Each tool has unique serial number and certificate of calibration

Whether it's TorqueVario-S or TorqueFix - Wiha has a torque screwdriver to cover almost every application



+/-6% accuracy tolerance
Certificate of calibration



285 TorqueFix, With Wiha-SoftFinish®

Handle Fixed Torque value pre-set. Tested in accordance with EN ISO 6789, BS EN 26789, ASME B107.14M, tolerance +/- 6%. Audible & perceptible click when pre-set torque has been attained. Automatically resets for next torque cycle; 50% greater reverse torque.

Item No.	Pre-Sets						
	oz.	lbs.	Nm	mm	Inch	lbs.	pkg.
28503	80	5	0.56	112	4.4	.16	1
28505	120	7.5	0.84	112	4.4	.15	1
28507	160	10	1.12	119	4.7	.28	1
28509	200	12.5	1.41	119	4.7	.27	1
28511	240	15	1.69	119	4.7	.27	1
28513	320	20	2.25	119	4.7	.28	1
28515	400	25	2.82	126	4.9	.37	1
28517	480	30	3.39	126	4.9	.37	1
28518	560	35	3.95	126	4.9	.37	1
28519	640	40	4.52	126	4.9	.37	1
28521	800	50	5.65	132	5.2	.52	1
28523	960	60	6.78	132	5.2	.52	1

Direct Reading Scale



4mm Bit Holder

+/-6% accuracy tolerance Certificate of calibration

285 Adjustable TorqueVario With Direct

Reading Scale EN ISO 6789, BS EN 26789, ASME B107.14M. Ergonomic molded multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible and perceptible click when the torque setting has been attained, automatically resets for next torque cycle.

Item No.	Range			
	Inch lbs.	Increments	mm	lbs.
28501*	15 - 80(in/oz)	2.5 In.oz.	127	.22
28502	5 - 10	.5 In.lbs.	127	.41
28506	10 - 50	2 In.lbs.	138	.59

* 28501 +/- 10% (This unit only)*

Item No.	Range			
	Inch lbs.	Increments	mm	lbs.
28404	5 - 18	1 In.lbs.	131	.50
28408	18 - 62	2 In.lbs.	142	.74

Direct Reading Scale



1/4" Bit Holder

Item No.	Range			
	Inch lbs.	Increments	mm	
28410*	15 - 80(in/oz)	2.5 In.oz.	127	
28411	5 - 10	.5 In.lbs.	127	
28412	10 - 50	2 In.lbs.	138	
28413	5 - 18	.5 In.lbs.	131	
28414	18 - 62	2 In.lbs.	142	

+/-6% accuracy tolerance Certificate of calibration

* 28410 +/- 10% (This unit only)



+/-6% accuracy tolerance
Certificate of calibration

285 Adjustable TorqueVario-S Handle - In

Newton Meter Scale EN ISO 6789, BS EN 26789, ASME B107.14M. Ergo molded multi-component handle, light & compact. Handle sizes proportioned to optimize torque range. Audible & perceptible click when the torque setting has been attained, automatically resets for next torque cycle.

Item No.	Newton Meter Scale	Increments	mm	lbs.
28550*	0.1 - 0.6Nm	.05 Nm	127	.35
28551	0.4 - 1.0Nm	.05 Nm	127	.35
28552	0.5 - 2.0Nm	.10 Nm	131	.45
28553	0.8 - 5.0Nm	.20 Nm	138	.55
28655	2.0 - 7.0Nm	.25 Nm	142	.70

* +/- 10% (This unit only)


+/-6% accuracy tolerance
Certificate of calibration



1/4" Bit Holder

Item No.	Range			
	Inch lbs.	Increments	mm	
28415*	0.1 - 0.6Nm	.05 Nm	127	
28416	0.4 - 1.0Nm	.05 Nm	127	
28417	0.5 - 2.0Nm	.10 Nm	131	
28418	0.8 - 5.0Nm	.20 Nm	138	
28419	2.0 - 7.0Nm	.25 Nm	142	

* +/- 10% (This unit only)



All TorqueVario models include Torque setting adjustment tool

Wiha TorqueControl Blades - For Easy Torque, TorqueFix & TorqueVario Handles



285 Slotted Interchangeable Blades For TorqueFix & TorqueVario Slotted tip blades on narrow 5/32 Hex shafts. High alloy chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

Item					Max.	
No.	mm	Inch	mm	lbs.	Nm	pkg.
28534	1.5	.059	175	.07	0.15	1
28535	2.0	.078	175	.07	0.4	1
28536	2.5	.098	175	.07	0.4	1
28537	3.0	.118	175	.07	0.6	1
28538	3.5	.139	175	.07	1.1	1
28539	4.0	.157	175	.07	2.5	1



285 Phillips Interchangeable Blades For TorqueFix & TorqueVario Phillips tip blades on narrow 5/32 Hex shafts. High alloy chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

Item					Max.	
No.	Size	mm	mm	lbs.	Nm	pkg.
28540	000	175	4.0	.07	0.4	1
28541	00	175	4.0	.07	0.4	1
28542	0	175	4.0	.07	0.9	1
28543	1	175	4.0	.07	3.8	1
28544	2	175	4.0	.07	5.5	1



285 TORX® Interchangeable Blades For TorqueFix & TorqueVario TORX® tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item					Max.	
No.	Size	mm	mm	lbs.	Nm	pkg.
28561	T5	175	4.0	.07	0.4	1
28562	T6	175	4.0	.07	0.6	1
28563	T7	175	4.0	.07	0.9	1
28564	T8	175	4.0	.07	1.3	1
28565	T9	175	4.0	.07	2.5	1
28566	T10	175	4.0	.07	3.8	1
28567	T15	175	4.0	.07	5.5	1
28568	T20	175	4.0	.07	8.0	1
28569	T25	175	4.0	.07	8.0	1



285 Hex Inch Interchangeable Blades For TorqueFix & TorqueVario Hex tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item					Max.	
No.	Inch	mm	lbs.	Nm	pkg.	
28555	.050	175	.07	.4	1	
28556	1/16	175	.07	.9	1	
28557	5/64	175	.07	1.8	1	
28558	3/32	175	.07	1.8	1	
28559	7/64	175	.07	3.8	1	
28560	1/8	175	.07	5.5	1	
28587	9/64	175	.07	8.0	1	
28588	5/32	175	.07	8.0	1	



285 Hex Metric Interchangeable Blades For TorqueFix & TorqueVario Hex tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item					Max.	
No.	mm	mm	lbs.	Nm	pkg.	
28545	1.5	175	.07	0.9	1	
28546	2.0	175	.07	1.8	1	
28547	2.5	175	.07	3.8	1	
28548	3.0	175	.07	5.5	1	
28549	4.0	175	.07	8.0	1	



285 TORXPlus® Blades For TorqueFix & TorqueVario TORXPlus® tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item					Max.	
No.	Size	mm	mm	lbs.	Nm	pkg.
28571	IP5	175	4.0	.07	0.5	1
28572	IP6	175	4.0	.07	0.8	1
28573	IP7	175	4.0	.07	1.3	1
28574	IP8	175	4.0	.07	2.0	1
28575	IP9	175	4.0	.07	3.0	1
28576	IP10	175	4.0	.07	4.5	1
28577	IP15	175	4.0	.07	6.6	1
28578	IP20	175	4.0	.07	8.0	1
28579	IP25	175	4.0	.07	8.0	1



285 MagicSpring TORX® Interchangeable Blades For TorqueFix & TorqueVario blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item					Max.	
No.	Size	mm	mm	lbs.	Nm	pkg.
28512	T6	175	4.0	.07	0.6	1
28527	T7	175	4.0	.07	0.9	1
28528	T8	175	4.0	.07	1.3	1
28529	T9	175	4.0	.07	2.5	1
28530	T10	175	4.0	.07	3.8	1
28531	T15	175	4.0	.07	5.5	1
28532	T20	175	4.0	.07	8.0	1
28533	T25	175	4.0	.07	8.0	1



286 MagicSpring TORXPlus® Interchangeable Blades For TorqueFix & TorqueVario blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item					Max.	
No.	Size	mm	mm	lbs.	Nm	pkg.
28611	IP6	175	4.0	.07	0.8	1
28612	IP7	175	4.0	.07	1.3	1
28613	IP8	175	4.0	.07	2.0	1
28614	IP9	175	4.0	.07	3.0	1
28616	IP10	175	4.0	.07	4.5	1
28617	IP15	175	4.0	.07	6.6	1
28618	IP20	175	4.0	.07	8.0	1
28619	IP25	175	4.0	.07	8.0	1

*None of the blades featured on this page will function in a TorqueVario Insulated Handle

Wiha TorqueControl Adapters



28882 ESD Safe Bit Holder Adapter For 1/4" Drive Bits

Shaft CVM steel, hardened, corrosion protected. (Not for use in Insulated handles)

Item					Max.	
No.	Size	mm	mm	lbs.	pkg.	
28882	1/4	162	4.0	.09	1	

Wiha Torque Cable Keys

Torque handles recommended
#28552 & #28504



286 Torque Cable Key For Threaded Hex Connectors

For torque controlled fastening of cable plug connectors with Hex heads. Used with Wiha-TorqueControl Screwdrivers.

Item No.	Size	mm	mm	mm	Max Nm	lbs.	pkg.
28620	8mm	4.0	78	218	1.0	.06	1
28622	9mm	4.0	78	218	1.0	.06	1
28627	13mm	4.0	78	218	1.5	.06	1
28629	14mm	4.0	78	218	1.5	.06	1
28633	18mm	4.0	78	218	1.5	.06	1



easyTorque Control Handles

“easy” Torque

- Audible Click At Torque
- Replaceable Blades
- +/- 10% Repeatability
- Improve Productivity
- Reduces Waste
- Controls Costs
- Save Time!

Each tool
factory
preset



Economical
Torque Control
for tooling
assembly and
repair

Torque accuracy
of +/- 10% to
5000 cycles

Reverse torque is 50% greater for
easy removal using same tool

Uses 285 Series
interchangeable blades on pg. 6



292 easyTorque Screwdriver Handle

easyTorque value pre-set. Release accuracy +/- 10%. SoftFinish cushion grip handle for good power transfer.

Item	Pre-Sets					
No.	Inch/lbs.	Nm	mm	Inch	lbs.	pkg.
29205	4.4	0.5	130	5.1	.20	1
29206	5.3	0.6	130	5.1	.20	1
29209	8.0	0.9	130	5.1	.20	1
29211	9.7	1.1	130	5.1	.20	1
29212	10.6	1.2	130	5.1	.20	1
29214	12.4	1.4	130	5.1	.20	1
29220	17.7	2.0	130	5.1	.20	1
29225	22.1	2.5	130	5.1	.20	1
29230	26.6	3.0	130	5.1	.20	1
29238	33.6	3.8	130	5.1	.20	1
29241	35.4	4.0	130	5.1	.20	1
29245	39.8	4.5	130	5.1	.20	1
29251	44.2	5.0	130	5.1	.20	1

* No Calibration Certificates



292 easyTorque Screwdriver Handle With TORX® Blades

easyTorque value pre-set. Release accuracy +/- 10%. Internal mechanism clicks when torque value has been attained. Cushion grip comfortable handle for good power transfer.

Item		Pre-Sets			
No.	Size	Inch/lbs.	Nm	lbs.	pkg.
29232	T5	4.4	0.5	.24	1
29233	T6	5.3	0.6	.24	1
29234	T7	8.0	0.9	.24	1
29236	T8	10.6	1.2	.25	1
29237	T9	12.4	1.4	.25	1
29239	T10	17.7	2.0	.26	1
29242	T15	26.6	3.0	.26	1
29243	T20	35.4	4.0	.26	1
29244	T25	44.2	5.0	.28	1

* No Calibration Certificates



292 easyTorque Screwdriver Handle With TORXPlus® Blades

easyTorque value pre-set. Release accuracy +/- 10%. Internal mechanism clicks when torque value has been attained. Cushion grip comfortable handle for good power transfer.

Item		Pre-Sets			
No.	Size	Inch/lbs.	Nm	lbs.	pkg.
29246	IP5	4.4	0.5	.24	1
29247	IP6	5.3	0.6	.24	1
29248	IP7	8.0	0.9	.24	1
29249	IP8	10.6	1.2	.25	1
29252	IP9	12.4	1.4	.25	1
29253	IP10	17.7	2.0	.26	1
29254	IP15	26.6	3.0	.26	1
29255	IP20	35.4	4.0	.26	1
29256	IP25	44.2	5.0	.28	1

* No Calibration Certificates

Wiha TorqueControl Adapters

Adapters For TorqueFix™ & TorqueVario™



28581 Bit Holder Adapter For 1/4" Drive Bits Shaft CVM steel, hardened, corrosion protected. (Not for use in Insulated handles)

Item No.	Size	mm	mm	lbs.	pkg.
28581	1/4	149	4.0	.09	1



28582 Square Drive Adapter For 1/4" Sockets Shaft CVM steel, hardened, corrosion protected. (Not for use in Insulated handles)

Item No.	Size	mm	mm	lbs.	pkg.
28582	1/4	145	4.0	.08	1



28583 Adapter Blade For 4mm MicroBits Shaft CVM steel, hardened, corrosion protected. (Not for use in Insulated handles)

Item No.	Size	mm	mm	lbs.	pkg.
28583	4.0	149	4.0	.09	1

Wiha TorqueControl Adjustable iTorque

iTorque Screwdrivers

- Metric (Nm) & Inch (In-lbs / oz)
- Built in click counter
- Auto shut off
- Fast adjusting
- Cycle Counter
- Accurate +/- 6%



With Certificate of Calibration Included



4mm bit holder included

288 iTorque Screwdriver Handles

EN ISO 6789, BS EN 26789, ASME B107.14M. Handle reads Nm & Inch/lbs. with built in click counter. Fast adjusting. Accurate +/- 6% Each iTorque handle includes a 4mm bit holder.

Item No.	Adjustable Maximum Torque	mm	Inch	lbs.
28886	60-210(in/oz.) 40-150(Ncm)	134	5.3	.44
28887	7-26 in/lbs. 0.8-3.0 Nm	134	5.3	.44
28889	9-45 in/lbs. 1.0-6.0 Nm	134	5.3	.44

1/4" bit holder included

288 iTorque Screwdriver Handles

Each iTorque handle includes a 1/4" bit holder.

Item No.	Adjustable Maximum Torque	mm	Inch	lbs.
28883	60-210(in/oz.) 40-150(Ncm)	134	5.3	.44
28884	7-26 in/lbs. 0.8-3.0 Nm	134	5.3	.44
28885	9-45 in/lbs. 1.0-6.0 Nm	134	5.3	.44



Quick Adjusting



Digital Display



Push Button Start
Push Button Conversion



Fast Conversion
Nm to In/lbs.

With Certificate of Calibration



52 Pc. Set

28891 52 Piece iTorque Bit Set, In Metal Storage Box Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable iTorque handle 60-210 in/oz. 40-150 Ncm, 50 insert bits & 1/4" bit holder.

Item	Slotted: 4.5, 5.5, 6.5, 8.0mm
No.	Phillips: #0, #1, #2, #3
28891	TORX®: T6, T7, T8, T9, T10, T15, T20, T25, T27, T3
lbs.	Hex Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 2.56 9/64, 5/32, 3/16"
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm
	Pozidriv: #0, #1, #2, #3
	Torq Set: #4, #5, #6, #8
	Square: #1, #2, #3
	Triwing: #0, #1, #2, #3, #4
	iTorque Handle Range 60 - 210 Inch/oz.
	28581 - 1/4" Bit Holder

With Certificate of Calibration



52 Pc. Set

28892 52 Piece iTorque Bit Set, In Metal Storage Box Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable iTorque handle 7-26 in/lbs. 0.8-3.0 Nm, 50 insert bits & 1/4" bit holder.

Item	Slotted: 4.5, 5.5, 6.5, 8.0mm
No.	Phillips: #0, #1, #2, #3
28892	TORX®: T6, T7, T8, T9, T10, T15, T20, T25, T27, T3
lbs.	Hex Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 2.57 9/64, 5/32, 3/16"
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm
	Pozidriv: #0, #1, #2, #3
	Torq Set: #4, #5, #6, #8
	Square: #1, #2, #3
	Triwing: #0, #1, #2, #3, #4
	iTorque Handle Range 7 - 26 Inch/lbs.
	28581 - 1/4" Bit Holder

With Certificate of Calibration



52 Pc. Set

28896 52 Piece iTorque Bit Set, In Metal Storage Box Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable iTorque handle 9-50 in/lbs. 1.0-6.0 Nm, 50 insert bits & 1/4" bit holder.

Item	Slotted: 4.5, 5.5, 6.5, 8.0mm
No.	Phillips: #0, #1, #2, #3
28896	TORX®: T6, T7, T8, T9, T10, T15, T20, T25, T27, T3
lbs.	Hex Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 2.61 9/64, 5/32, 3/16"
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm
	Pozidriv: #0, #1, #2, #3
	Torq Set: #4, #5, #6, #8
	Square: #1, #2, #3
	Triwing: #0, #1, #2, #3, #4
	iTorque Handle Range 9 - 45 Inch/lbs.
	28581 - 1/4" Bit Holder

Wiha SYSTEM 4 Micro Bits



750 SYSTEM 4 Slotted Bits High alloy CVM steel, hardened, on 4 mm hex stock.

Item				
No.	mm	mm	Inch	lbs.
75008	0.8	28	1.1	.01
75012	1.2	28	1.1	.01
75015	1.5	28	1.1	.01
75018	1.8	28	1.1	.01
75020	2.0	28	1.1	.01
75025	2.5	28	1.1	.01
75030	3.0	28	1.1	.01
75035	3.5	28	1.1	.01
75040	4.0	28	1.1	.01



751 SYSTEM 4 Phillips Bits High alloy CVM steel, hardened, on 4 mm hex stock.

Item				
No.	Size	mm	Inch	lbs.
75105	000	28	1.1	.01
75110	00	28	1.1	.01
75115	0	28	1.1	.01
75120	1	28	1.1	.01



753 SYSTEM 4 Hex Inch Bits High alloy CVM steel, hardened, on 4 mm hex stock.

Item				
No.	Inch	mm	Inch	lbs.
75307	.028	28	1.1	.01
75309	.035	28	1.1	.01
75313	.050	28	1.1	.01
75350	1/16	28	1.1	.01
75352	5/64	28	1.1	.01
75354	3/32	28	1.1	.01
75356	7/64	28	1.1	.01
75358	1/8	28	1.1	.01
75360	9/64	28	1.1	.01
75340	5/32	28	1.1	.01



757 SYSTEM 4 TORX® Bits High alloy CVM steel, hardened, on 4 mm stock.

Item				
No.	Size	mm	Inch	lbs.
75701	T1	28	1.1	.01
75702	T2	28	1.1	.01
75703	T3	28	1.1	.01
75704	T4	28	1.1	.01
75705	T5	28	1.1	.01
75706	T6	28	1.1	.01
75707	T7	28	1.1	.01
75708	T8	28	1.1	.01
75709	T9	28	1.1	.01
75710	T10	28	1.1	.01
75715	T15	28	1.1	.01
75720	T20	28	1.1	.01



753 SYSTEM 4 Hex Metric Bits High alloy CVM steel, hardened, on 4 mm hex stock.

Item				
No.	mm	mm	Inch	lbs.
75307	0.7	28	1.1	.01
75309	0.9	28	1.1	.01
75313	1.3	28	1.1	.01
75315	1.5	28	1.1	.01
75320	2.0	28	1.1	.01
75325	2.5	28	1.1	.01
75330	3.0	28	1.1	.01
75340	4.0	28	1.1	.01



757 SYSTEM 4 Pentalobe Bits High alloy CVM steel, hardened, on 4 mm stock.

Item				
No.	Size	mm	Inch	lbs.
75743	PL1	28	1.1	.01
75744	PL2	28	1.1	.01
75745	PL3	28	1.1	.01
75746	PL4	28	1.1	.01
75747	PL5	28	1.1	.01
75748	PL6	28	1.1	.01



753 SYSTEM 4 Metric & Inch Nut Setters CVM steel, hardened, on 4 mm hex stock.

Item No.				
Metric	mm	mm	Inch	lbs.
75820	2.0	30	1.2	.01
75821	2.5	30	1.2	.01
75822	3.0	30	1.2	.01
75823	3.5	30	1.2	.01
75824	4.0	30	1.2	.01
75825	4.5	30	1.2	.01
75826	5.0	30	1.2	.01
75827	5.5	30	1.2	.01
Inch	Inch	mm	Inch	lbs.
75810	5/64	30	1.2	.01
75811	3/32	30	1.2	.01
75812	7/64	30	1.2	.01
75813	1/8	30	1.2	.01
75814	9/64	30	1.2	.01
75815	5/32	30	1.2	.01
75816	3/16	30	1.2	.01
75817	7/32	30	1.2	.01

1/4" Drive Micro Bit Tool Adapters



75802 Micro Bit To 1/4" Drive Insert Bit Adapter uses magnets to hold 4mm Micro Bits

Item				
No.	Size	mm	mm	lbs.
75802	4.0	25	4.0	.01



75803 Long Micro Bit To 1/4" Drive Insert Bit Adapter uses spring clip non-magnetic to hold 4mm Micro Bits

Item				
No.	Size	mm	mm	lbs.
75803	4.0	38	4.0	.02

Wiha Adjustable TorqueControl Tool Sets In Durable Storage Cases



53 Pc. Set



With Certificate of Calibration

28595 53 Piece TorqueVario-S Bit Set, In Storage Box Set includes ergonomic multi-component adjustable TorqueVario-S handle, 50 Insert bits, 1/4" Bit holder and Torque adjustment tool.

Item	Slotted: 4.5, 5.5, 6.5, 8.0mm
No.	Phillips: #0, #1, #2, #3
28595	TORX®: T6, T7, T8, T9, T10, T15, T20, T25, T27, T30
lbs.	Hex Inch: 1/16, 5/64, 3/32, 7/64, 2.04 1/8, 9/64, 5/32, 3/16"
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm
	Pozidriv®: #0, #1, #2, #3
	Torq Set: #4, #5, #6, #8
	Square: #1, #2, #3
	Tri-Wing: #0, #1, #2, #3, #4
	28506 - Handle Range 10-50 In/lbs.
	28581 - 1/4" Bit Holder



59 Pc. Set



With Certificate of Calibration

28589 59 Piece TorqueVario-S Bit Set, In Storage Box Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. Set includes 3 ergonomic multi-component adjustable TorqueVario-S handles, 39 Insert bits, 15 Sockets, 1/4" Bit holder, 1/4" Hex to 1/4" Square adapter and Torque adjustment tool.

Item	Slotted: 4.5, 5.5, 6.0mm
No.	Phillips: #0, #1, #2
28589	TORX®: T5, T6, T7, T8, T9, T10, T15, T20, T25, T30
lbs.	Hex Inch: .050, 1/16, 5/64, 3/32, 2.73 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm
	Pozidriv®: #1, #2
	Square: #1, #2, #3
	Inch Sockets: 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 3/8"
	Metric Sockets: 4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0mm
	3 Handles: 15 - 80 In/oz., 5 - 10 & 10 - 50 In/lbs.
	1/4" Bit Holder
	1/4" Hex to 1/4" Square adapter



59 Pc. Set



With Certificate of Calibration

28689 59 Piece Torque Newton Meter Bit Set, In Storage Box Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. Set includes 3 ergonomic multi-component adjustable Torque Nm handles, 39 Insert bits, 15 Sockets, 1/4" Bit holder, 1/4" Hex to 1/4" Square adapter and Torque adjustment tool.

Item	Slotted: 4.5, 5.5, 6.0mm
No.	Phillips: #0, #1, #2
28689	TORX®: T5, T6, T7, T8, T9, T10, T15, T20, T25, T30
lbs.	Hex Inch: .050, 1/16, 5/64, 3/32, 2.73 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm
	Pozidriv®: #1, #2
	Square: #1, #2, #3
	Inch Sockets: 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 3/8"
	Metric Sockets: 4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0mm
	3 Handles: 0.1-0.6 Nm, 0.4-1.0 Nm & 1.0-5.0 Nm
	1/4" Bit Holder
	1/4" Hex to 1/4" Square adapter



Wiha Adjustable TorqueControl Tool Sets In Durable Storage Box



With Certificate of Calibration

28590 24 Pc. TorqueVario-S Micro-Bit Set

Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder & Torque adjustment tool. Packed in a compact durable storage box.

Item	Slotted: 1.5, 2.0, 3.0, 4.0mm
No.	Phillips: #00, #0, #1
28590	TORX®: T6, T7, T8, T9, T10, T15
	Hex Inch: .050, 1/16, 5/64, 3/32,
lbs.	7/64, 1/8, 9/64, 5/32
1.35	28404 - Handle Range 5 - 18 In/lbs.



With Certificate of Calibration

28593 24 Pc. TorqueVario-S Micro-Bit Set

Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder & Torque adjustment tool. Packed in a compact durable storage box.

Item	Slotted: 1.5, 2.0, 3.0, 4.0mm
No.	Phillips: #00, #0, #1
28593	TORX®: T6, T7, T8, T9, T10, T15
	Hex Inch: .050, 1/16, 5/64, 3/32,
lbs.	7/64, 1/8, 9/64, 5/32
1.35	28501 - Handle Range 15-80 In/oz.
	(+/- 10%)

Wiha TorqueControl Sets In Durable Canvas Pouch



28596 8 Piece TorqueControl Set With Slotted & Phillips Blades Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 6 blades & Torque adjustment tool. Packed in a durable canvas pouch.

Item No.	
28596	Slotted: 2.5, 3.0, 3.5, 4.0mm
	Phillips: #0, #1
lbs.	1.0 28404 - Handle Range 5 - 18 In/lbs.

With Certificate of Calibration



28600 20 Piece TorqueControl Set With Slotted, Phillips, TORX®, Hex Inch Blades Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 18 blades & Torque adjustment tool. Packed in a durable canvas pouch.

Item No.	
28600	Slotted: 2.5, 3.5, 4.0mm
	Phillips: #0, #1, #2
	TORX®: T7, T8, T9, T10, T15, T20
lbs.	Hex: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
1.38	28506 - Handle Range 10 - 50 In/lbs.

With Certificate of Calibration



28597 8 Pc. TorqueControl Set With TORX® Blades Certified to EN ISO 6789, BS EN 26789, ASME B107.14M

Item	lbs. 1.01
No.	TORX®: T7, T8, T9, T10, T15, T20
28597	28506 - Handle Range 10 - 50 In/lbs.

With Certificate of Calibration



28598 8 Piece TorqueControl Set With TORXPlus® Blades Certified to EN ISO 6789, BS EN 26789, ASME B107.14M

Item	TORXPlus®	lbs. 1.00
No.	IP7, IP8, IP9, IP10, IP15, IP20	
28598	28506 - Handle Range 10 - 50 In/lbs.	

With Certificate of Calibration



28599 14 Piece TorqueControl Set With TORX® & TORXPlus® Blades Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. Set includes Ergonomic multi-component adjustable TorqueVario-S handle, 12 blades & Torque adjustment tool. Packed in a durable canvas pouch.

Item	TORXPlus®:	lbs. 1.25
No.	IP7, IP8, IP9, IP10, IP15, IP20	
28599	TORX®: T7, T8, T9, T10, T15, T20	
	28506 - Handle Range 10 - 50 In/lbs.	

With Certificate of Calibration



Wiha Insulated TorqueControl Tools



- * Includes Certificate
- * Includes SlimLine blade holder #28350
- * Requires SlimLine Blades

1000Volt

287 Insulated TorqueVario-S, With Window Scale Insulation up to 1000Volt. EN/IEC, EN ISO, BS EN, ASME & CSA, +/- 6% Accuracy. Ergonomic multi-component handle, light & compact. Handle sizes proportioned to optimize torque range. Audible & perceptible click when torque setting has been attained. In Plastic Tube Holder

Item No.	Range	Inch lbs.	Increments	mm	lbs.	pkg.
28750	5 - 18	.5 In/lbs	126-131	.56	1	
28751	10 - 50	2 In/lbs	133-138	.74	1	
28752	18 - 62	2 In/lbs	137-142	.84	1	

287 Insulated TorqueVario-S Handle - In Newton Meter Scale

Item No.	Range	Nm	mm	lbs.	pkg.
28740	0.5 - 2.0	131	.64	1	
28741	0.8 - 5.0	138	.56	1	
28742	2.0 - 7.0	142	.84	1	

Each TorqueVario handle has unique serial number & certificate of calibration



Wiha Insulated TorqueControl Tools

Includes Certificate



1000Volt

287 Insulated TorqueVario-S, With Window Scale Insulation up to 1000Volt EN ISO, BS EN, ASME, VDE, ASTM & NFPA70E standards, +/- 6% Accuracy. Handle sizes proportioned to optimize torque range. Audible and perceptible click when torque setting has been attained. (Requires Insulated Blade Holder #28350-Not Included)

Item No.	Range	Inch lbs.	Increments	mm	lbs.	pkg.
28724	5 - 18	.5 In/lbs	131	.43	1	
28726	10 - 50	2 In/lbs	138	.40	1	
28727	18 - 62	2 In/lbs	142	.69	1	

Each TorqueVario handle has unique serial number and certificate of calibration

287 Insulated TorqueVario-S Handle - In Newton Meter Scale (Requires Insulated Blade Holder #28350-Not Included)

Item No.	Range	Nm	mm	lbs.	pkg.
28734	0.5 - 2.0	131	.45	1	
28736	0.8 - 5.0	138	.45	1 (2 Nm Increment)	
28738	2.0 - 7.0	142	.72	1	

Wiha Insulated SlimLine Torque Blade Holder

1000Volt



28350 Insulated SlimLine Torque Blade Holder CVM steel. Through hardened black finish. ClicFix quick release holder securely locks blades.

Item No.	OAL	OAL	Inch	lbs.	pkg.
28350	6.0	170	6.75	.06	1

1000Volt



28316 Insulated SlimLine Torque Blade Holder CVM steel. Through hardened black finish. Blade holder holds blades securely.

Item No.	OAL	OAL	Inch	lbs.	pkg.
28316	6.0	70	2.75	.02	1

Wiha Insulated SlimLine Torque Socket Adapters



1000Volt

28311 Insulated SlimLine Torque Socket Adapters CVM steel. For 1/4" drive sockets

Item No.	OAL	OAL	Inch	lbs.	pkg.
28311	6.0	57	2.25	.03	1

1000Volt



28700 Insulated SlimLine Torque Socket Adapters CVM steel. For 1/4" drive sockets

Item No.	OAL	OAL	Inch	lbs.	pkg.
28700	6.0	176	7.0	.06	1

Wiha Insulated Easy TorqueControl Adapters

Meets VDE, EN/IEC, ASTM, CSA, NFPA specifications



1000Volt

283 Insulated Easy-TorqueControl

Adapters Ideal for torque sensitive terminations. For use with SlimLine blades.

Repeatable accuracy to +/- 10%

Item No.	Range	Nm	In/lbs	mm	Inch	lbs.	pkg.
28366	0.8 - 7.0	60	2.38	.13	1		
28367	2.0 - 17.7	60	2.38	.13	1		
28368	2.5 - 23.1	60	2.38	.13	1		
28369	2.8 - 24.7	60	2.38	.13	1		
28371	4.0 - 35.4	60	2.38	.13	1		

Wiha Insulated SlimLine Blades

Insulation Test Standards:

Insulation according to EN/IEC 60900,
ASTM F-1505, VDE 0682/part 201,
DIN 7437, NFPA70E &
CSA specification



Insulation does
not exceed screw
head diameter

Integrated Slim
Insulation molded
directly onto blade

 **1000 Volt Rated**
10,000 Volt Tested

High quality CV steel,
through-hardened

**Wiha
SlimTECHNOLOGY**
Achieves blade
diameters up to 33%
narrower utilizing
integrated insulation



283 Insulated Slotted SlimLine Blades

SlimLine blades have up to 33% narrower
insulation diameter than standard insulated tools.

Item No.	mm	Inch	Slim Dia.	Max Dia.	Nm	lbs.	Inch/ lbs.	Pkg.
28307	2.5	3/32	4.0	0.4	3.5	.02	1	
28308	3.0	1/8	4.0	0.6	5.3	.02	1	
28310	3.5	9/64	4.0	2.5	22.1	.02	1	
28309	4.0	5/32	4.0	2.5	22.1	.02	1	
28312	5.5	7/32	6.0	3.8	33.6	.02	1	
28315	6.5	1/4	6.0	5.5	48.6	.02	1	

283 Insulated Phillips SlimLine Blades

SlimLine blades have up to 33% narrower
insulation diameter than standard insulated tools.

Item No.	Size	Slim Dia.	Max Dia.	Nm	lbs.	Inch/ lbs.	Pkg.
28317	1	4.0	3.8	33.7	.02	1	
28319	2	6.0	5.5	48.8	.02	1	

283 Insulated Pozidriv® SlimLine Blades

SlimLine blades have up to 33% narrower
insulation diameter than standard insulated tools.

Item No.	Size	Slim Dia.	Max Dia.	Nm	lbs.	Inch/ lbs.	Pkg.
28330	1	4.0	3.8	33.7	.02	1	
28331	2	6.0	5.5	48.8	.02	1	

283 Insulated Xeno Slotted/Pozidriv®

SlimLine Blades Up to 33% narrower
insulation diameter than standard insulated tools.

Item No.	Size	Slim Dia.	Max Dia.	Nm	lbs.	Inch/ lbs.	Pkg.
28320	1	4.0	3.8	33.6	.02	1	
28321	2	6.0	5.5	48.7	.02	1	

283 Insulated Xeno Slotted/Phillips

SlimLine Blades Up to 33% narrower insulation
diameter than standard insulated tools.

Item No.	Size	Slim Dia.	Max Dia.	Nm	lbs.	Inch/ lbs.	Pkg.
28327	1	4.0	3.8	33.6	.02	1	
28329	2	6.0	5.5	48.7	.02	1	

283 Insulated Square SlimLine Blades

Up to 33% narrower insulation diameter than
standard insulated tools.

Item No.	Size	Slim Dia.	Max Dia.	Nm	lbs.	Inch/ lbs.	Pkg.
28346	1	4.0	3.8	33.6	.02	1	
28347	2	6.0	5.5	48.7	.02	1	

283 Insulated TORX® SlimLine Blades

Up to 33% narrower insulation diameter than
standard insulated tools.

Item No.	Size	Slim Dia.	Max Dia.	Nm	lbs.	Inch/ lbs.	Pkg.
28325	T6	4.0	.6	5.31	.02	1	
28326	T7	4.0	.9	7.9	.02	1	
28339	T8	4.0	1.3	11.5	.02	1	
28344	T9	4.0	1.3	11.5	.02	1	
28340	T10	4.0	3.8	33.6	.02	1	
28341	T15	6.0	5.5	48.7	.02	1	
28342	T20	6.0	5.5	48.7	.02	1	
28343	T25	6.0	5.5	48.7	.02	1	

283 Insulated Hex Metric SlimLine

Blades Up to 33% narrower insulation
diameter than standard insulated tools.

Item No.	Size	Slim Dia.	Max Dia.	Nm	lbs.	Inch/ lbs.	Pkg.
28332	1.5	4.0	0.9	7.9	.02	1	
28333	2.0	4.0	1.8	15.9	.02	1	
28334	2.5	4.0	3.8	33.6	.02	1	
28335	3.0	4.0	5.5	48.7	.02	1	
28336	4.0	6.0	5.5	48.7	.02	1	
28337	5.0	6.0	5.5	48.7	.02	1	
28338	6.0	6.0	5.5	48.7	.02	1	

28372 7 Piece SlimLine Blade Set

High quality CV steel, through hardened,
black finish.

Item No.	Slotted: 2.5, 3.5, 5.5mm	Phillips: #1, #2	Square: #1, #2
28372			

28373 7 Piece SlimLine Blade Set

High quality CV steel, through hardened,
black finish.

Item No.	Slotted: 2.5, 3.5, 5.5mm	Phillips: #1, #2	Xeno Slit/Ph: #1, #2
28373			



28348 12 Piece Insulated SlimLine

Blade Set With Belt Holder Up to 33%
narrower insulation diameter than standard
insulated tools. SlimLine blade holder holds
12 SlimLine blades.

Item No.	Slotted: 4.0, 5.5mm	Phillips: #1, #2	Hex: 2.5, 3.0, 4.0mm	TORX®: T15, T20, T25	Square: #1, #2
28348					



Insulated Torque & SlimLine Tool Sets

1000Volt



28791 8 Piece Insulated TorqueControl Set With Slotted & Phillips SlimLine Blades Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. Set includes Insulated multi-component adjustable TorqueVario-S handle, 5 SlimLine blades, SlimLine blade holder & Torque adjustment tool.

Item No.

28791 SlimLine Slotted: 3.0, 4.0, 5.5mm
 SlimLine Phillips: #1, #2
 lbs. 28726 - Handle Range 10-50 Inch/lbs.
 .87 SlimLine Blade Holder

With Certificate of Calibration



28795 12 Pc. Insulated TorqueControl Set With SlimLine Blades Certified to EN ISO, BS EN, ASME. Set includes Insulated multi-component adjustable TorqueVario-S Nm handle, SlimLine Blade Holder Handle, 8 SlimLine blades, SlimLine blade holder & Torque adjustment tool.

Item No.

28795 SlimLine Slotted: 4.0, 5.5, 6.5mm
 SlimLine Phillips: #1, 2
 SlimLine Pozidriv®: #1, 2
 SlimLine Terminal Xeno SI/Pz: #2
 28736 - Handle Range 0.8 - 5.0 Nm
 SlimLine Blade Holder Handle
 SlimLine Blade Holder
 lbs. 1.32

With Certificate of Calibration



28789 11 Pc. Insulated TorqueControl Set With SlimLine Blades Certified to EN ISO, BS EN, ASME. Set includes Insulated multi-component adjustable TorqueVario-S 10-50 In/lbs. handle, 8 SlimLine blades, SlimLine blade holder & Torque adjustment tool. In Clamshell

Item Slotted: 4.0, 6.5mm

No. Phillips: #1, 2

28789 Square: #1, 2

Terminal Xeno SI/Pz: #1, 2

lbs. Torque Handle Range 10-50 In/lbs.

1.32 SlimLine Blade Holder 6.75" OAL

With Certificate of Calibration

1000Volt



28792 16 Piece Insulated TorqueControl Set With SlimLine Blades Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. Set includes Insulated multi-component adjustable TorqueVario-S handle, 13 SlimLine blades, SlimLine blade holder & Torque adjustment tool.

Item No.

28792 SlimLine Slotted: 4.0, 5.5, 6.5mm
 SlimLine Phillips: #1, #2
 lbs. SlimLine Terminal Xeno: #1, 2
 1.27 SlimLine TORX®: T8, T10, T15, T20
 SlimLine Square: #1, #2
 28727 - Handle Range 18-62 Inch/lbs.
 SlimLine Blade Holder

With Certificate of Calibration



28781 20 Piece Insulated TorqueControl Set With SlimLine Blades Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. Set includes Insulated multi-component adjustable TorqueVario-S handle, SoftFinish® SlimLine blade handle, PicoFinish® SlimLine blade holder, 15 SlimLine blades, SlimLine blade holder & Torque adjustment tool. In Clamshell

Item Slotted: 2.5, 3.5, 4.0, 6.5mm

No. Phillips: #1, 2 (qty. 2 of #2)

28781 Terminal Xeno SI/Ph: #1, 2

TORX®: T10, T15, T20, T25

lbs. Square: #1, 2

1.61 Handle Range 10-50 In/lbs.

SlimLine SoftFinish® Blade Holder

PicoFinish® SlimLine Holder

SlimLine Blade Holder 6.75" OAL

Wiha Insulated Torque Ratchet Wrenches



#30138



#30114

1000Volt

301 Insulated Torque Ratchet

Wrenches, 1/4, 3/8, 1/2" Drives Insulated to EN/IEC 60900:2004, ASTM F1505-10, CSA Standards Visible reading scale for easy reading and adjustment. Locking endcap Torque adjuster for easy adjustment. Accuracy +/- 10%. Dual scale reading Ft. lbs. / Nm.

Item No.	OAL	OAL			
	Inch	mm	Inch	Nm	lbs.
30114	1/4"	210	8.25	5-25	1.02
30138	3/8"	370	14.5	5-50	2.72
30152	1/2"	530	21.0	40-220	3.64



1000Volt

30190 16 Pc. Inch Insulated 3/8" Drive Ratcheting Torque Wrench & Socket Set

CV steel, forged, oil-hardened sockets.

Item No. 3/8" Drive Sockets:

30190	1/4, 9/32, 5/16, 11/32, 3/8, 7/16
	1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8"
lbs.	3/8" x 125mm Extension Bar
8.80	3/8" x 250mm Extension Bar
	3/8" Drive Ratcheting Torque Wrench - 5-50 Nm

*Sockets must be used with insulated ratchets & extensions



1000Volt

30192 16 Pc. Metric Insulated 3/8" Drive Ratcheting Torque Wrench & Socket Set

Item No. 3/8" Drive Sockets:

30192	8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20mm
lbs.	3/8" x 125mm Extension Bar
8.80	3/8" x 250mm Extension Bar
	3/8" Drive Ratcheting Torque Wrench - 5-50 Nm

*Sockets must be used with insulated ratchets & extensions

T-handle TorqueControl Handles



Accuracy Ergonomic multi-component handle, light & compact

Includes Calibration Certificate

289 TorqueFix T-handle EN ISO 6789, BS EN 26789, ASME B107.14M, +/- 6%

Item No.	Torque In-lbs.	Torque Nm	mm x mm	lbs.	pkg.
28931	53.1	6	56 x 120	.81	1
28933	70.8	8	56 x 120	.82	1
28935	88.5	10	56 x 120	.79	1
28937	106.2	12	56 x 120	.79	1
28938	110.6	12.5	56 x 120	.80	1
28939	123.9	14	56 x 120	.80	1

Each TorqueFix T-handle has unique serial number and certificate of calibration



Includes Calibration Certificate

28940 Adjustable TorqueVario STplus T-handle EN ISO 6789, BS EN 26789, ASME B107.14M, +/- 6%

Item No.	Torque Nm	Torque In-lbs.	mm x mm	lbs.	pkg.
28940	5-14	44.3-123.9	56 x 120	.81	1

* (1 Nm 8.8507) (Scale is shown in Nm only)

T-handle TorqueControl Blades



289 TORX® Interchangeable Blades For TorqueFix T-Handle TORX® tip blades on 6mm Hex shafts. High alloy CVM steel, hardened, hard chromed.

Item No.	Size	mm	Inch	mm	lbs.	pkg.
28903	T15	130	5.1	6.0	.10	1
28904	T20	130	5.1	6.0	.10	1
28905	T25	130	5.1	6.0	.11	1
28906	T27	130	5.1	6.0	.11	1
28907	T30	130	5.1	6.0	.11	1
28908	T40	130	5.1	6.0	.11	1



289 TORXPlus® Interchangeable Blades For TorqueFix T-Handle TORXPlus® tip blades on 6mm Hex shafts. High alloy CVM steel, hardened, hard chromed.

Item No.	Size	mm	Inch	mm	lbs.	pkg.
28910	IP15	130	5.1	6.0	.10	1
28911	IP20	130	5.1	6.0	.10	1
28912	IP25	130	5.1	6.0	.11	1
28913	IP27	130	5.1	6.0	.11	1
28914	IP30	130	5.1	6.0	.11	1



289 Hex Metric Interchangeable Blades For TorqueFix T-Handle Hex tip blades on 6mm Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item No.	Size	mm	Inch	mm	lbs.	pkg.
28916	3.0	130	5.1	.11	.11	1
28917	4.0	130	5.1	.11	.11	1
28918	5.0	130	5.1	.11	.11	1
28919	6.0	130	5.1	.11	.11	1

Wiha T-handle TorqueControl Adapters



289 TorqueFix Adapter For 1/4" & 3/8" Sockets Shaft CVM steel, hardened, corrosion protected.

Item No.	Size	mm	Inch	mm	lbs.	pkg.
28926	1/4	100	3.9	6.0	.12	1



28925 TorqueFix Quick Release Bit Holder Shaft CVM steel, hardened, corrosion protected.

Item No.	Size	mm	Inch	mm	lbs.	pkg.
28925	1/4	125	4.9	6.0	.15	1

ESD Safe Adjustable TorqueControl Tools



28591 24 Piece ESD Safe Adjustable TorqueVario-S Bit Set

Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder and Torque adjustment tool, packed in a compact durable storage box.

Item No.	Slotted: 1.5, 2.0, 3.0, 4.0mm
	Phillips: #00, #0, #1
28591	TORX®: T6, T7, T8, T9, T10, T15
	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
1.57	28524 - Handle ESD Safe
	Range 5 - 10 Inch lbs.



28895 24 Piece ESD Safe Adjustable TorqueVario-S Bit Set

Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder and Torque adjustment tool, packed in a compact durable storage box.

Item No.	Slotted: 0.8, 1.2, 1.5, 2.0mm
28895	Phillips: #000, #00, #0
	TORX®: T1, T2, T3, T4, T5, T6
1.30	Hex Metric: 0.7, 0.9, 1.3mm
	Pentalobe: PL1, PL2, PL3, PL4
	28500 - Handle ESD Safe
	.04 - .46Nm (+/-10%)



285 ESD Safe TorqueVario-S, With Window Scale

EN ISO 6789, BS EN 26789, ASME B107.14M, +/- 6% Accuracy. Ergonomic multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible & perceptible click when torque setting has been attained. With Certificate of accuracy. Pkg. 1

Item No.	Range	Increments	mm	lbs.
28522*	15 - 80 (in/oz)	2.5 In.oz.	122-127	.33
28524	5 - 10	.2 In.lbs.	122-127	.34

Item No.	Range	Increments	mm	lbs.
28426	5 - 18	.5 In.lbs.	126-131	.46

Each TorqueVario handle has unique serial number and certificate of calibration



28890 24 Piece TorqueVario-S ESD Safe Micro-Bit Set

Certified to EN ISO 6789, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder and Torque adjustment tool.

Item No.	Slotted: 1.5, 2.0, 3.0, 4.0mm
28890	Phillips: #00, #0, #1
	TORX®: T6, T7, T8, T9, T10, T15
1.35	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
	28522 - ESD Safe Handle Range
	15-80 Inch/oz.

ESD Safe TorqueControl Tools



285 ESD Safe TorqueVario-S Newton Meter, With Window Scale

EN ISO 6789, BS EN 26789, ASME B107.14M, +/- 10% Accuracy. Ergonomic multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible & perceptible click when torque setting has been attained. With Certificate of accuracy.

Item No.	Range	mm	Inch	lbs.	pkg.
28500	.04 - .46	124	4.875"	.35	1

ESD TorqueVario handle has unique serial number and certificate of calibration



288 ESD Safe Pentalobe IPR Interchangeable Blades For TorqueVario-S Newton Meter

Handle tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, hard chromed.

Item No.	Size	mm	mm	lbs.	pkg.
28818	PL1	175	4.0	.07	1



28882 ESD Safe Bit Holder Adapter For 1/4" Drive Bits

Shaft CVM steel, hardened, corrosion protected. (Not for use in Insulated handles)

Item No.	Size	mm	mm	lbs.	pkg.
28882	1/4	162	4.0	.09	1

Maximum Recommended Torque For Wiha Torque Blades

Tip Size	Style	Maximum Torque	
T5	TORX	.4 Nm	3.5 in.lbs
T6	TORX	.6 Nm	5.31 in.lbs
T7	TORX	.9 Nm	7.9 in.lbs
T8	TORX	1.3 Nm	11.5 in.lbs
T9	TORX	2.5 Nm	22.1 in.lbs
T10	TORX	3.8 Nm	33.6 in.lbs
T15	TORX	5.5 Nm	48.7 in.lbs
T20	TORX	8.0 Nm	70.8 in.lbs
T25	TORX	8.0 Nm	70.8 in.lbs
IP5	TORX Plus	.5 Nm	4.4 in.lbs
IP6	TORX Plus	.8 Nm	7.0 in.lbs
IP7	TORX Plus	1.3 Nm	11.5 in.lbs
IP8	TORX Plus	2.0 Nm	17.7 in.lbs
IP9	TORX Plus	3.0 Nm	26.5 in.lbs
IP10	TORX Plus	4.5 Nm	39.8 in.lbs
IP15	TORX Plus	6.6 Nm	58.4 in.lbs
IP20	TORX Plus	8.0 Nm	70.8 in.lbs
IP25	TORX Plus	8.0 Nm	70.8 in.lbs
1.5	Slotted	.15 Nm	1.3 in.lbs
2.0	Slotted	.4 Nm	3.5 in.lbs
2.5	Slotted	.4 Nm	3.5 in.lbs
3.0	Slotted	.6 Nm	5.31 in.lbs
3.5	Slotted	1.1 Nm	9.7 in.lbs
4.0	Slotted	2.5 Nm	22.1 in.lbs
#000	Phillips	.4 Nm	3.5 in.lbs
#00	Phillips	.4 Nm	3.5 in.lbs
#0	Phillips	.9 Nm	7.9 in.lbs
#1	Phillips	3.8 Nm	33.6 in.lbs
#2	Phillips	5.5 Nm	48.6 in.lbs
1.5	Hex Metric	.9 Nm	7.9 in.lbs
2.0	Hex Metric	1.8 Nm	15.9 in.lbs
2.5	Hex Metric	3.8 Nm	33.6 in.lbs
3.0	Hex Metric	5.5 Nm	48.6 in.lbs
4.0	Hex Metric	8.0 Nm	70.8 in.lbs
.050	Hex Inch	.4 Nm	3.5 in.lbs
1/16	Hex Inch	.9 Nm	7.9 in.lbs
5/64	Hex Inch	1.8 Nm	15.9 in.lbs
3/32	Hex Inch	1.8 Nm	15.9 in.lbs
7/64	Hex Inch	3.8 Nm	33.6 in.lbs
1/8	Hex Inch	5.5 Nm	48.6 in.lbs
9/64	Hex Inch	8.0 Nm	70.8 in.lbs
5/32	Hex Inch	8.0 Nm	70.8 in.lbs

Numerical Index by Item Number

Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page
28307 13	28359 4	28501 5	28553 5	28616 6
28308 13	28360 4	28502 5	28555 6	28617 6
28309 13	28361 4	28503 5	28556 6	28618 6
28310 13	28362 4	28505 5	28557 6	28619 6
28311 12	28363 4	28506 5	28558 6	28620 7
28312 13	28364 4	28507 5	28559 6	28622 7
28315 13	28365 4	28509 5	28560 6	28627 7
28316 12	28366 12	28511 5	28561 6	28629 7
28317 13	28367 12	28512 6	28562 6	28633 7
28319 13	28368 12	28513 5	28563 6	28655 5
28320 13	28369 12	28515 5	28564 6	28689 10
28321 13	28371 12	28517 5	28565 6	28700 12
28325 13	28372 13	28518 5	28566 6	28724 12
28326 13	28373 13	28519 5	28567 6	28726 12
28327 13	28374 4	28521 5	28568 6	28727 12
28329 13	28375 4	28522 16	28569 6	28734 12
28330 13	28376 4	28523 5	28571 6	28736 12
28331 13	28377 4	28524 16	28572 6	28738 12
28332 13	28378 4	28527 6	28573 6	28740 12
28333 13	28379 4	28528 6	28574 6	28741 12
28334 13	28380 4	28529 6	28575 6	28742 12
28335 13	28381 4	28530 6	28576 6	28750 12
28336 13	28382 4	28531 6	28577 6	28751 12
28337 13	28383 4	28532 6	28578 6	28752 12
28338 13	28384 4	28533 6	28579 6	28781 14
28339 13	28385 4	28534 6	28581 7	28789 14
28340 13	28386 4	28535 6	28582 7	28791 14
28341 13	28387 4	28536 6	28583 7	28792 14
28342 13	28388 4	28537 6	28587 6	28795 14
28343 13	28389 4	28538 6	28588 6	28818 16
28344 13	28404 5	28539 6	28589 10	28882 6,16
28346 13	28408 5	28540 6	28590 11	28883 8
28347 13	28410 5	28541 6	28591 16	28884 8
28348 13	28411 5	28542 6	28593 11	28885 8
28349 4	28412 5	28543 6	28595 16	28886 8
28350 12	28413 5	28544 6	28596 11	28887 8
28351 4	28414 5	28545 6	28597 11	28889 8
28352 4	28415 5	28546 6	28598 11	28890 16
28353 4	28416 5	28547 6	28599 11	28891 8
28354 4	28417 5	28548 6	28600 11	28892 8
28355 4	28418 5	28549 6	28611 6	28895 14
28356 4	28419 5	28550 5	28612 6	28896 8
28357 4	28426 16	28551 5	28613 6	28897 4
28358 4	28500 16	28552 5	28614 6	28903 15

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
28904	15	29246	7	75703	9				
28905	15	29247	7	75704	9				
28906	15	29248	7	75705	9				
28907	15	29249	7	75706	9				
28908	15	29251	7	75707	9				
28910	15	29252	7	75708	9				
28911	15	29253	7	75709	9				
28912	15	29254	7	75710	9				
28913	15	29255	7	75715	9				
28914	15	29256	7	75720	9				
28916	15	30114	15	75743	9				
28917	15	30138	15	75744	9				
28918	15	30152	15	75745	9				
28919	15	30190	15	75746	9				
28925	15	30192	15	75747	9				
28926	15	75008	9	75748	9				
28931	15	75012	9	75802	9				
28933	15	75015	9	75803	9				
28935	15	75018	9	75810	9				
28937	15	75020	9	75811	9				
28938	15	75025	9	75812	9				
28939	15	75030	9	75813	9				
28940	15	75035	9	75814	9				
29205	7	75040	9	75815	9				
29206	7	75105	9	75816	9				
29209	7	75110	9	75817	9				
29211	7	75115	9	75820	9				
29212	7	75120	9	75821	9				
29214	7	75307	9	75822	9				
29220	7	75309	9	75823	9				
29225	7	75313	9	75824	9				
29230	7	75315	9	75825	9				
29232	7	75320	9	75826	9				
29233	7	75325	9	75827	9				
29234	7	75330	9						
29236	7	75340	9						
29237	7	75350	9						
29238	7	75352	9						
29239	7	75354	9						
29241	7	75356	9						
29242	7	75358	9						
29243	7	75360	9						
29244	7	75701	9						
29245	7	75702	9						



Prop 65 WARNING: Cancer and reproductive harm. For more information, go to www.P65Warnings.ca.gov/



PROFESSIONAL TORQUE CONTROL



(800) 494-6104
fax: (800) 494-7456
cservice@wihatools.com
www.wihatools.com

Catalog Item No. 99001
version - 1/1/2021

Subject to change
without notice

©2021 Willi Hahn Corporation

®Torx is a registered trademark of
Acument Intellectual Properties LLC.



Wiha Quality Tools

1348 Dundas Circle
Monticello, MN 55362
tel: 763.295.6591
fax: 763.295.6598

Wiha Tools Canada Ltd.

www.wihatools.ca
Brampton, ONT L6T 4X4
tel: 866.494.0096 or 763.295.6591
fax: 763.295.6598



To:



99007.w0 - Merchandise Catalog




99977 Pliers/Crimpers Catalog



99004 Automotive Catalog



99919 Insulated Catalog



99945 ESD Catalog



99951 Bits Catalog



99002 Screwdrivers Catalog



99914 TORX Catalog



99934 Hex Tools Catalog

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Wiha:

<u>28504</u>	<u>28502</u>	<u>28508</u>	<u>28506</u>	<u>28940</u>	<u>28505</u>	<u>28503</u>	<u>28509</u>	<u>28517</u>	<u>28519</u>	<u>28507</u>	<u>28638</u>	<u>28512</u>	<u>28511</u>	<u>28513</u>
<u>28518</u>	<u>28544</u>	<u>28501</u>	<u>28515</u>	<u>28308</u>	<u>28312</u>	<u>28315</u>	<u>28317</u>	<u>28319</u>	<u>28339</u>	<u>28340</u>	<u>28341</u>	<u>28342</u>	<u>28346</u>	<u>28347</u>
<u>29242</u>	<u>29244</u>	<u>29246</u>	<u>29248</u>	<u>29249</u>	<u>29256</u>	<u>28891</u>	<u>29205</u>	<u>29206</u>	<u>29212</u>	<u>29230</u>	<u>29232</u>	<u>29233</u>	<u>29238</u>	<u>29251</u>
<u>29253</u>	<u>29211</u>	<u>29234</u>	<u>28500</u>	<u>28321</u>	<u>28330</u>	<u>28332</u>	<u>28335</u>	<u>28336</u>	<u>28338</u>	<u>28343</u>	<u>28351</u>	<u>28354</u>	<u>28355</u>	<u>28356</u>
<u>28358</u>	<u>28359</u>	<u>28361</u>	<u>28382</u>	<u>28383</u>	<u>28887</u>	<u>28895</u>	<u>28689</u>	<u>28370</u>	<u>39251</u>	<u>39256</u>	<u>39257</u>	<u>39258</u>	<u>28738</u>	<u>28309</u>
<u>28327</u>	<u>28329</u>	<u>28350</u>	<u>28726</u>	<u>28727</u>	<u>28736</u>	<u>28734</u>	<u>28737</u>	<u>29239</u>	<u>29241</u>	<u>29245</u>	<u>29247</u>	<u>29252</u>	<u>29254</u>	<u>29255</u>
<u>28892</u>	<u>29209</u>	<u>29225</u>	<u>29236</u>	<u>29237</u>	<u>28893</u>	<u>29243</u>	<u>29214</u>	<u>28818</u>	<u>29220</u>					