




Product: [1852F](#)



Audio Snake Cable, #24-24pr, TC, Indiv. Shielded, CMG

Product Description

Digital Audio Snake Cable, CMG-Rated, 24-24 AWG tinned copper pairs, Datalene® insulation, individually shielded with Beldfoil, numbered/color-coded PVC jackets, flexible PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Multi-channel interconnect between audio equipment such as microphones, speakers, amplifiers, mixing consoles; Live events or studio sound; Analog audio
------------------------	--

Physical Characteristics (Overall)

Conductor				
AWG	Stranding	Material	Nominal Diameter	No. of Pairs
24	7x32	TC - Tinned Copper	0.024 in	24
Conductor Count:		48		
Total Number of Pairs:		24		

Insulation			
Material	Material Trade Name	Nominal Diameter	Nominal Wall Thickness
PE - Polyethylene (Foam)	Datalene®	0.068 in	0.022 in

Color Chart	
Number	Color
1	Brown and Numbered 1
2	Red and Numbered 2
3	Orange and Numbered 3
4	Yellow and Numbered 4
5	Green and Numbered 5
6	Blue and Numbered 6
7	Purple and Numbered 7
8	Gray and Numbered 8
9	White and Numbered 9
10	Black and Numbered 10
11	Tan and Numbered 11
12	Pink and Numbered 12
13	Gray/Brown Stripe and Numbered 13
14	Gray/Red Stripe and Numbered 14
15	Gray/Orange Stripe and Numbered 15
16	Gray/Yellow Stripe and Numbered 16
17	Gray/Green Stripe and Numbered 17
18	Gray/Blue Stripe and Numbered 18
19	Gray/Purple Stripe and Numbered 19
20	Gray/Gray Stripe and Numbered 20
21	Gray/White Stripe and Numbered 21
22	Gray/Black Stripe and Numbered 22
23	Gray/Tan Stripe and Numbered 23

24	Gray/Pink Stripe and Numbered 24
----	----------------------------------

Color Chart 2

Number	Color
1	Red & Black
2	Red & Black
3	Red & Black
4	Red & Black
5	Red & Black
6	Red & Black
7	Red & Black
8	Red & Black
9	Red & Black
10	Red & Black
11	Red & Black
12	Red & Black
13	Red & Black
14	Red & Black
15	Red & Black
16	Red & Black
17	Red & Black
18	Red & Black
19	Red & Black
20	Red & Black
21	Red & Black
22	Red & Black
23	Red & Black
24	Red & Black

Inner Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire Diameter	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	0.024 in	24	Stranded

Table Notes:	Indiv. Foil tapes bonded to inner jacket
--------------	--

Inner Jacket

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.167 in	0.014 in

Outer Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire Diameter	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	0.060 in	16	Stranded

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	1.21 in	0.100 in	Yes
	1.210 in		

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance
23.7 Ohm/1000ft	23.7 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
12 pF/ft	26 pF/ft

Inductance

Nominal Inductance
0.18 µH/ft

Impedance

Nominal Characteristic Impedance

110 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
0.384 MHz	0.29 dB/100ft
0.706 MHz	0.71 dB/100ft
0.768 MHz	0.77 dB/100ft
1.024 MHz	0.94 dB/100ft
1.411 MHz	1.1 dB/100ft
1.536 MHz	1.1 dB/100ft
2.048 MHz	1.3 dB/100ft
2.822 MHz	1.4 dB/100ft
3.072 MHz	1.4 dB/100ft
4.096 MHz	1.5 dB/100ft
5.645 MHz	1.7 dB/100ft
6.144 MHz	1.8 dB/100ft
8.192 MHz	2 dB/100ft
11.29 MHz	2.2 dB/100ft
12.288 MHz	2.3 dB/100ft
24.576 MHz	3.1 dB/100ft

Delay

Nominal Velocity of Propagation (VP) [%]
76%

High Frequency

Frequency [MHz]
0.384 MHz
0.706 MHz
0.768 MHz
1.024 MHz
1.411 MHz
1.536 MHz
2.048 MHz
2.822 MHz
3.072 MHz
4.096 MHz
5.645 MHz
6.144 MHz
8.192 MHz
11.29 MHz
12.288 MHz
24.576 MHz

Temperature Range

UL Temp Rating:	60°C
Operating Temperature Range:	-30°C To +60°C

Mechanical Characteristics

Bulk Cable Weight:	558 lbs/1000ft
Max. Pull Tension:	400 lbs
Min. Bend Radius/Minor Axis:	12.1 in

Standards

NEC/(UL) Compliance:	CMG
CEC/C(UL) Compliance:	CMG
Other Specification:	AES/EBU

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes

EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
1852F Z4B500	Violet Z4B	Reel	500 ft	612825124467
1852F Z4B1000	Violet Z4B	Reel	1,000 ft	612825124450

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	Pair jackets and shields are bonded so both strip simultaneously with automatic stripping equipment. Datalene® insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.
--------	---

History

Update and Revision:	Revision Number: 0.350 Revision Date: 01-10-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1852F Z4B500](#) [1852F Z4B1000](#)