




Product: [1924A](#)



Audio Snake Cable, #24-24pr, BC, Individ. Shielded

## Product Description

Audio Snake Cable, 24-24 AWG bare copper pairs, polyolefin insulation, individually shielded with double serve "French Braid", drain, numbered/color-coded PVC jackets, flexible PVC jacket

## Technical Specifications

### Product Overview

Suitable Applications:	Multi-channel interconnect between audio equipment such as microphones, speakers, amplifiers, mixing consoles; Live events or studio sound; Analog audio
------------------------	--

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
24	41x40	BC - Bare Copper	0.0225 in	24

Conductor Count:	48
Total Number of Pairs:	24

#### Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PP - Polypropylene	0.04 in	0.008 in

#### Color Chart

Number	Color
1	Brown
2	Red
3	Orange
4	Yellow
5	Green
6	Blue
7	Purple
8	Gray
9	White
10	Black
11	Tan
12	Pink
13	Gray/Brown
14	Gray/Red
15	Gray/Orange
16	Gray/Yellow
17	Gray/Green
18	Gray/Blue
19	Gray/Purple
20	Gray/Gray
21	Gray/White
22	Gray/Black
23	Gray/Tan

24 Gray/Pink

#### Color Chart 2

Color
Red and Black

#### Inner Shield

Type	Material	Coverage [%]	Drainwire Material	Drainwire Diameter	Drainwire AWG	Drainwire Construction n x D
French Braid	Bare Copper (BC)	95%	TC - Tinned Copper	0.025 in	24	19x26

#### Inner Jacket

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.119 in	0.014 in

#### Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.825 in	0.09 in

## Construction and Dimensions

#### Stranding

Twists
12 twist/ft

## Electrical Characteristics

#### Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance
7.2 Ohm/1000ft	25.5 Ohm/1000ft	25.5 Ohm/1000ft	

#### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
26.1 pF/ft	47.5 pF/ft

#### Inductance

Nominal Inductance
0.18 $\mu$ H/ft

#### Impedance

Nominal Characteristic Impedance
60 Ohm

#### Delay

Nominal Velocity of Propagation (VP) [%]
66%

#### Current

Max. Recommended Current [A]
1.05 Amps per Conductor at 25°C

#### Voltage

UL Voltage Rating
300 V RMS

## Temperature Range

Operating Temperature Range:	-20°C To +60°C
------------------------------	----------------

## Mechanical Characteristics

Bulk Cable Weight:	397 lbs/1000ft
Max. Pull Tension:	700 lbs
Min. Bend Radius/Minor Axis:	8.25 in

## Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
----------------------	------------------------------

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Indoor:	Yes
-----------------------	-----

## Flammability, LSOH, Toxicity Testing

UL voltage rating:	300 V RMS
--------------------	-----------

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Related Part Numbers

### Variants

Item #	Color	Put-Up Type	Length	UPC
192A B59TEST	Black, Matte			
1924A B59500	Black, Matte	Reel	500 ft	612825126898

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## History

Update and Revision:	Revision Number: 0.350 Revision Date: 01-10-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1924A B59500](#) [1924A B59250](#)