



**Product:** [2285P](#)

Light Dimmer Cable, 2 Conductor 18 AWG BC, CMP

**Product Description**

Light Dimmer Cable, 2 Conductor 18 AWG solid bare copper conductors with Flamarrest® insulation, CMP rating, Flamarrest® Low Smoke PVC jacket with ripcord.

**Technical Specifications**

**Product Overview**

Suitable Applications:	Ballast Wiring and Connection, Addressable Fire Systems, Data Circuits, Monitor/Detection, Control Circuits, Initiating Circuits, Notification Circuits
Suitable Applications:	Ballast Wiring and Connection, Addressable Fire Systems, Data Circuits, Monitor/Detection, Control Circuits, Initiating Circuits, Notification Circuits

**Construction Details**

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	18 AWG	Solid	BC - Bare Copper

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	18 AWG	Solid	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.010 in (0.25 mm)	0.0605 in (1.54 mm)	Violet, Gray

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.010 in (0.25 mm)	0.0605 in (1.54 mm)	Violet, Gray

**Outer Shield**

Material
No Shield

**Outer Shield**

Material
No Shield

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.147 in	Yes

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.147 in	Yes

Overall Cable Diameter (Nominal):	0.147 in
Overall Cable Diameter (Nominal):	0.147 in

**Electrical Characteristics**

Electricals

Nom. Conductor DCR	Max. Current
6.4 Ohm/1000ft	5 Amps per Conductor at 25°C

Electricals

Nom. Conductor DCR	Max. Current
6.4 Ohm/1000ft	5 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-20°C To +75°C

Temperature

UL Temperature	Operating
75°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
1.47 in (37.3 mm)	1.47 in

Bend Radius

Stationary Min.	Installation Min.
1.47 in (37.3 mm)	1.47 in

Max. Pull Tension:	39.2 lbs (17.8 kg)
Max. Pull Tension:	39.2 lbs (17.8 kg)
Bulk Cable Weight:	15 lbs/1000ft
Bulk Cable Weight:	15 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Environmental Suitability:	Indoor - Plenum, Indoor
Flammability / Reaction to Fire:	NFPA 262 (UL 910), FT6
Flammability / Reaction to Fire:	NFPA 262 (UL 910), FT6
NEC / UL Compliance:	Article 800, CMP
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	2285R
Non-Plenum Number:	2285R

History

Update and Revision:	Revision Number: 0.220 Revision Date: 02-15-2024
Update and Revision:	Revision Number: 0.220 Revision Date: 02-15-2024

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
2285P 009500	White	Reel	500 ft	612825408024
2285P 0091000	White	Reel	1,000 ft	612825408017

**Variants**

Item #	Color	Putup Type	Length	UPC
2285P 009500	White	Reel	500 ft	612825408024
2285P 0091000	White	Reel	1,000 ft	612825408017

© 2024 Belden, Inc  
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[2285P 0091000](#) [2285P 009500](#) [2285R 008500](#)