



Product: [29535](#)

VFD, 3C 500MCM Str BC XLPE Ins + #2 Symm. Seg. Gnd (3 of #6) Str BC, CTS, Blk PVC Jkt, 2000V TC-ER 90C Dry/Wet 1000V CSA 22.2 No. 230 TC

[Request Sample](#)

Product Description

Belden Basics VFD, 3 Conductor 500MCM (37x.1162") Bare Copper XLPE Insulation M4 Color Code + 2AWG Symmetrical Segmented Ground (3 of 6AWG) Bare Copper Stranded, Overall Dual Copper Tapes Helically Applied Shield, Black PVC Outer Jacket, 2000V TC-ER 90C Dry/Wet 1000V CSA 22.2 No. 230 TC SUN RES DIR BUR Oil Resistant

Technical Specifications

Product Overview

Suitable Applications:	Variable Frequency Drives (VFD); AC Motor and Drive Systems
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material	Notes
Conductor(s)	3	500 MCM	37x0.1162 in.	BC - Bare Copper	
Ground Wire	3	6 AWG	7x14	BC - Bare Copper	Segmented Grounds

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	XLPE - Cross-Linked Polyethylene (Thermoset)	0.105 in (2.67 mm)	0.999 in (25.4 mm)	ICEA Method 4
Ground Wire	No Insulation			

Outer Shield

Shield Type	Material	Coverage
Helical Tape	Bare Copper (BC)	100%
Helical Tape	Bare Copper (BC)	100%

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.110 in (2.79 mm)	2.41 in (61.2 mm)	Yes

Overall Cable Diameter (Nominal):	2.41 in (61.2 mm)
-----------------------------------	-------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
Conductor(s)	0.02 Ohm/1000ft	30 pF/ft (98 pF/m)	54 pF/ft (180 pF/m)	62 Ohm	55%	430 Amps per Conductor at 30°C (per NEC)
	0.43 Ohm/1000ft (1.4 Ohm/km)					75 Amps per Conductor at 25°C

Voltage

UL Voltage Rating	Voltage Rating
2000 V (TC, UL44)	1000 V (CSA TC)

Mechanical Characteristics

Temperature

UL Temperature	Operating
90°C Dry, 90°C Wet	-40°C To +90°C

Bend Radius

Stationary Min.	Installation Min.
28.9 in (734 mm)	28.9 in (734 mm)

Max. Pull Tension:	1610 lbs (730 kg)
Bulk Cable Weight:	6749 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Burial
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1685 UL Loading, IEEE 1202 FT4, FT4
NEC / UL Compliance:	Article 336, TC-ER, RHW-2
CEC / C(UL) Compliance:	CSA TC
ICEA Compliance:	S-95-658
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.542 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
29535 0101300	Black	Reel	1,300 ft	612825138389

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[29535 0101300](#)