



**Product:** [3072F](#)

Blue Hose®, 1 Pr #18 Str TC, PP Ins, OS+TC Brd, PVC Jkt, 600V TC, PLTC

[Request Sample](#)

## Product Description

Blue Hose® for Data Highway Plus, 1 Pair 18AWG (7x26) Tinned Copper, PP Insulation, Overall Beldfoil®+Tinned Copper Braid(55%) Shield, PVC Outer Jacket, 600V TC, PLTC

## Technical Specifications

Suitable Applications:	harsh environment, IIoT, factory or process automation, video, audio, data communication, etc.
------------------------	--

### Conductor

Element	Number of Element	AWG	Stranding	Material
Pair(s)	1	18	7x26	TC - Tinned Copper

### Insulation

Element	Material	Thickness [in.]	Nom. Insulation Diameter	Color Code	Notes
Pair(s)	PP - Polypropylene	0.025	0.096	Blue & White	Flame Retardant

### Outer Shield Material

Shield Type	Material	Coverage	Drainwire Type
Tape + Braid	Bi-Laminate (Alum+Poly) + Tinned Copper (TC)	100% + 55%	20 AWG (7x28) TC

### Outer Jacket Material

Material	Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.053 in	0.324 in

Cable Diameter (Nominal):	0.324 in
---------------------------	----------

### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Characteristic Impedence	Nom. Velocity of Prop.
Pair(s)	6.9 Ohm/1000ft	19.5 pF/ft	78 Ohm	65%

Nom Outer Shield DCR:	3.2 Ohm/1000ft
-----------------------	----------------

### High Frequency (Nominal/Typical)

Element	Frequency [MHz]	Nom. Insertion Loss
Pair(s)	1 MHz	0.52 dB/100ft
	10 MHz	1.98 dB/100ft
	50 MHz	3.78 dB/100ft
	100 MHz	5.35 dB/100ft
	200 MHz	7.57 dB/100ft
	400 MHz	10.7 dB/100ft

### Voltage

UL Voltage Rating	Non-UL Voltage Rating
600 V (TC), 300 V (CMG, PLTC)	150 V (ITC)

### Temperature

UL Rating	Operating
75°C Dry	-40°C to +75°C

### Bend Radius

Stationary Min.	Installation Min.
3.25 in	4 in
Max. Pull Tension:	85 lbs
Bulk Cable Weight:	48 lbs/1000ft
Environmental Suitability:	Indoor, Sunlight Resistance
Flammability / Fire Resistance:	UL1685 UL Loading, FT4, FT4, 1202
NEC / UL Compliance:	Article 336, Article 725, Article 727, Article 800, CMG, ITC, PLTC, TC
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	P-MSHA-SC-182/7
Notes:	For CPE jacketed version, order Part No. YM45044.
Update and Revision:	Revision Number: 0.374 Revision Date: 09-30-2020

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Belden Wire & Cable:

[3072F C551000](#) [3072F C552500](#) [3072F C5510000](#) [3072F C555000](#) [3072F C55500](#) [3072F C55250](#)