



Product: [3125A](#)

DeviceBus® for Square D/Seriplex®, 2 Pr #16+22 Str TC, PVC+PO Ins, OS (Data), PVC Jkt, CM

[Request Sample](#)

Product Description

DeviceBus® for Square D/Seriplex®, 2 Pair 16+22AWG (26x30+7x30) Tinned Copper, PVC+PO Insulation, Overall Beldfoil® (Data Pair Only) Shield, PVC Outer Jacket, CM

Technical Specifications

Product Overview

Suitable Applications:	harsh environment, IIoT, factory or process automation, video, audio, data communication, etc.
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
16	26x30	TC - Tinned Copper	1
22	7x30	TC - Tinned Copper	1

Conductor Count:	4
------------------	---

Insulation

Element	Material	Nominal Wall Thickness
16 AWG	PE - Polyethylene (Foam)	0.025 in
22 AWG	PE - Polyethylene (Foam)	0.0405 in

Color Chart

Number	Color
1 (16 AWG)	Black and Red
2 (22 AWG)	Green and White

Outer Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	22	7x30

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness	Separator Material
PVC - Polyvinyl Chloride	0.368 in	0.039 in	PO - Polyolefin (Foam) Tape

Construction and Dimensions

Cabling

Lay Direction
Left Hand

Electrical Characteristics

Conductor DCR

Element	Nominal Conductor DCR	Nominal Outer Shield DCR
16 AWG	4.49 Ohm/1000ft	16 Ohm/1000ft
22 AWG	18.1 Ohm/1000ft	

Capacitance

Element	Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
22 AWG	16 pF/ft	28 pF/ft
16 AWG	9 pF/ft	16 pF/ft
22 AWG		
16 AWG		

Impedance

Nominal Characteristic Impedance
120 Ohm

Delay

Nominal Velocity of Propagation (VP) [%]	Nominal Velocity of Propagation (VP) Description
78%	16 AWG
78%	22 AWG

Voltage

UL Description	UL Voltage Rating
CM	300 V RMS
CL2	

Temperature Range

UL Temp Rating:	75°C
Operating Temperature Range:	-20°C to +75°C

Mechanical Characteristics

Bulk Cable Weight:	55.6 lbs/1000ft
Max. Pull Tension:	85 lbs

Standards

NEC Articles:	Article 725, Article 800
NEC/(UL) Compliance:	CL2, CM
CEC/C(UL) Compliance:	CM

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 UL Loading
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
3125A 0031000	Orange	Reel	1,000 ft	612825142027
3125A 0035000	Orange	Reel	5,000 ft	612825142034

Footnote:	C - CRATE REEL PUT-UP., Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.
-----------	--

History

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[3125A 0031000](#)