



Product: [33316](#)

Lead Wire, #16 Str TC, Silicone Ins, AWM 3212

Request Sample

Product Description

Low Temp Rubber Lead Wire, 16AWG (26x30) Tinned Copper, Silicone Insulation, AWM 3212 CSA TYPE AWM 600V 150C

Technical Specifications

Product Overview

Suitable Applications:	Class 155(F) or Class 180(H) motor lead systems , high temperature applications, internal wiring of lighting fixtures and appliances
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	16	26x30	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
Silicone Rubber	0.048 in (1.2 mm)	0.155 in (3.94 mm)

Overall Cable Diameter (Nominal):	0.155 in (3.94 mm)
-----------------------------------	--------------------

Electrical Characteristics

Voltage

UL Voltage Rating
600 V RMS

Mechanical Characteristics

Temperature

UL Temperature
150°C

Bend Radius

Stationary Min.	Installation Min.
0.62 in (16 mm)	0.62 in (16 mm)

Max. Pull Tension:	35.1 LBS
Recommended Max Baking Cycles:	24 Hours @ 410°F (210°C)
Bulk Cable Weight:	9.5 lbs/1000ft

Standards and Compliance

Sustainability:	CA Prop 65
AWM Compliance:	AWM 3212, CSA AWM I B
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Recommended Maximum Baking Cycles: 24 hours @ 410°F (210°C)
--------	---

History

Update and Revision:	Revision Number: 0.452 Revision Date: 07-03-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
33316 010500	Black	Reel	500 ft	612825143468	F
33316 009500	White	Reel	500 ft	612825143451	F

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[33316 009500](#) [33316 010500](#)