



Product: [34406](#)

Lead Wire, #6 Str TC, CSPE Ins, AWM 3192

Request Sample

Product Description

Low Temp Rubber Lead Wire, 6AWG (84x25) Tinned Copper, CSPE Insulation, AWM 3192 CSA TYPE CL1052 600V 105C

Technical Specifications

Product Overview

Suitable Applications:	Class 130(B) motor lead systems, internal wiring of appliances, oil resistance applications
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	6 AWG	84x25	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
CSPE - Chlorosulphonated Polyethylene	0.062 in (1.6 mm)	0.343 in (8.71 mm)

Overall Cable Diameter (Nominal):	0.343 in (8.71 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Max. Current
0.446 Ohm/1000ft	129.6 Amps per Conductor at 30°C

Voltage

UL Voltage Rating	Voltage Rating
600 V (AWM 3192)	300 V (CSA CL-1052)

Mechanical Characteristics

Temperature

UL Temperature	Operating
105°C	-30°C To +105°C

Bend Radius

Stationary Min.	Installation Min.
3.43 in (87.1 mm)	3.43 in (87.1 mm)

Max. Pull Tension:	304 lbs (138 kg)
Recommended Max Baking Cycles:	24 Hours @ 300°F (149°C)
Bulk Cable Weight:	129 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Oil Resistance
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	Horizontal flame

AWM Compliance:	AWM 3192
CEC / C(UL) Compliance:	CL-1052
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Separator material over conductor.
--------	------------------------------------

History

Update and Revision:	Revision Number: 0.491 Revision Date: 07-03-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
34406 010100	Black	Reel	100 ft	612825143765	
34406 010250	Black	Reel	250 ft	612825143789	C F
34406 0101000	Black	Reel	1,000 ft	612825143772	C F
34406 008100	Gray	Reel	100 ft	612825143758	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[34406 010100](#) [34406 010250](#) [34406 0101000](#) [34406 008100](#)