



Product: [50007TSF](#)

MarineTuff Cat7 S/FTP, 4 Pr #23 Str BC, FMPE Ins, LSZH Jkt



Product Description

Industrial Marine Ethernet Cat7 S/FTP, 4 Pr 23AWG Stranded Bare Copper, FoamPolyethylene Insulation, Low Smoke Zero Halogen (SHF1) Jacket, DNV

Technical Specifications

Product Overview

Suitable Applications:	marine, harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc.
Suitable Applications:	marine, harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc.

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs
23 AWG	Stranded	BC - Bare Copper	4

Conductor

Size	Stranding	Material	No. of Pairs
23 AWG	Stranded	BC - Bare Copper	4

Insulation

Material	Color Code
PO - Polyolefin (Foam)	White / Blue, White / Orange, White / Green, White / Brown

Insulation

Material	Color Code
PO - Polyolefin (Foam)	White / Blue, White / Orange, White / Green, White / Brown

Inner Shield

Shield Type	Material
Tape	Bi-Laminate (Alum+Poly)

Inner Shield

Shield Type	Material
Tape	Bi-Laminate (Alum+Poly)

Outer Shield

Shield Type	Material
Braid	Tinned Copper (TC)

Outer Shield

Shield Type	Material
Braid	Tinned Copper (TC)

Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	9.0 mm (0.35 in)

Outer Jacket

Material	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	9.0 mm (0.35 in)

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance	Nom. Characteristic Impedance
95 Ohm/km (29 Ohm/1000ft)	160 pF/100m	100 Ohm

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance	Nom. Characteristic Impedance
95 Ohm/km (29 Ohm/1000ft)	160 pF/100m	100 Ohm

Delay

Max. Delay	Max. Delay Skew
538 ns/100m @100MHz	25 ns/100m

Delay

Max. Delay	Max. Delay Skew
538 ns/100m @100MHz	25 ns/100m

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. TCL [dB]	Min. ELTCTL [dB]
1							40	35
4	3.7 dB/100m	78	75	78	75	23	34	23
8	5.2 dB/100m	78	75	77.2	74.2	24.5	31	16.9
10	5.9 dB/100m	78	75	75.3	723	25	30	15
16	7.4 dB/100m	78	75	71.2	68.2	25	28	10.9
20	8.3 dB/100m	78	75	69.3	66.3	25	27	9
25	9.3 dB/100m	78	75	67.3	64.3	24.3	26	7
31.25	10.4 dB/100m	78	75	65.4	62.4	23.6	25.1	
62.5	14.9 dB/100m	75.5	72.5	59.4	56.4	21.5	22	
100	19 dB/100m	72.4	69.4	55.3	52.3	20.1	20	
200	27.5 dB/100m	67.9	64.9	49.3	46.3	18	17	
250	31 dB/100m	66.4	63.4	47.3	44.3	17.3	16	
300	34.2 dB/100m	65.2	62.2	45.8	42.8	17.3		
500	45.3 dB/100m	61.9	58.9	41.3	38.3	17.3		
600	50.1 dB/100m	60.7	57.7	39.7	36.7	17.3		

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. TCL [dB]	Min. ELTCTL [dB]
1							40	35
4	3.7 dB/100m	78	75	78	75	23	34	23
8	5.2 dB/100m	78	75	77.2	74.2	24.5	31	16.9
10	5.9 dB/100m	78	75	75.3	723	25	30	15
16	7.4 dB/100m	78	75	71.2	68.2	25	28	10.9
20	8.3 dB/100m	78	75	69.3	66.3	25	27	9
25	9.3 dB/100m	78	75	67.3	64.3	24.3	26	7
31.25	10.4 dB/100m	78	75	65.4	62.4	23.6	25.1	
62.5	14.9 dB/100m	75.5	72.5	59.4	56.4	21.5	22	
100	19 dB/100m	72.4	69.4	55.3	52.3	20.1	20	
200	27.5 dB/100m	67.9	64.9	49.3	46.3	18	17	
250	31 dB/100m	66.4	63.4	47.3	44.3	17.3	16	
300	34.2 dB/100m	65.2	62.2	45.8	42.8	17.3		
500	45.3 dB/100m	61.9	58.9	41.3	38.3	17.3		
600	50.1 dB/100m	60.7	57.7	39.7	36.7	17.3		

Mechanical Characteristics

Temperature

Operating
-25°C To 80°C

Temperature

Operating
-25°C To 80°C

Bend Radius

Installation Min.
80 mm (3.1 in)

Bend Radius

Installation Min.
80 mm (3.1 in)

Bulk Cable Weight:	92 kg/km (62 lbs/1000ft)
Bulk Cable Weight:	92 kg/km (62 lbs/1000ft)

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Non-Halogenated, Sunlight Resistance - UL 1581 sec 1200, Oil Resistance - JIS C 3005
Environmental Suitability:	Indoor/Outdoor, Non-Halogenated, Sunlight Resistance - UL 1581 sec 1200, Oil Resistance - JIS C 3005
Flammability / Reaction to Fire:	IEC 60332-1-2, IEC 60332-3-22
Flammability / Reaction to Fire:	IEC 60332-1-2, IEC 60332-3-22
Data Category:	Category 7
Data Category:	Category 7
Third Party Performance Verification:	DNV GL certification
Third Party Performance Verification:	DNV GL certification
ISO/IEC Compliance:	ISO/IEC 11801-2, IEC 60092-360
ISO/IEC Compliance:	ISO/IEC 11801-2, IEC 60092-360
European Halogen Free Standards:	IEC 60754-1 - Halogen Amount = 0.5%, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 10 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Halogen Free Standards:	IEC 60754-1 - Halogen Amount = 0.5%, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 10 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU Directive 2011/65/EU (RoHS 2)
European Directive Compliance:	EU Directive 2011/65/EU (RoHS 2)

Product Notes

Notes:	DNV GL Certificate No: TAE00003K7, ABS certificate No: 19-SQ1877547-PDA
Notes:	DNV GL Certificate No: TAE00003K7, ABS certificate No: 19-SQ1877547-PDA

History

Update and Revision:	Revision Number: 0.380 Revision Date: 07-17-2024
Update and Revision:	Revision Number: 0.380 Revision Date: 07-17-2024

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
50007TSF 010305M	Black	Reel	305 m	
50007TSF-A500	Black	Reel	500 m	8719605188014
50007TSF-A1000	Black	Reel	1,000 m	8719605189097
50007TSF 006305M	Blue	Reel	305 m	
50007TSF 008305M	Gray	Reel	305 m	

Variants

Item #	Color	Putup Type	Length	EAN
50007TSF 010305M	Black	Reel	305 m	
50007TSF-A500	Black	Reel	500 m	8719605188014
50007TSF-A1000	Black	Reel	1,000 m	8719605189097
50007TSF 006305M	Blue	Reel	305 m	
50007TSF 008305M	Gray	Reel	305 m	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[50007TSF0101000](#)