


TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: PA66
FLAMMABILITY RATING: UL94-V0
COLOR: GREEN
CONTACT PIN: BRASS (CuZn)
SOLDER TAIL PLATING: TIN

ENVIRONMENTAL

OPERATING TEMPERATURE: -40 UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL	cULus	VDE
CURRENT RATING:	10 A	10.5 A
WORKING VOLTAGE:	300 VAC	300 VAC
WITHSTANDING VOLTAGE:	1.6 kV	2.5 kV
CONTACT RESISTANCE:	20 mOhm MAX	

STANDARD

 **CERTIFIED E315414**
 **CERTIFIED 40023195**

MECHANICAL

PITCH: 3.81 MM

SOLDERING

JEDEC LEAD FREE WAVE SOLDERING PROCESS

PACKAGING

BOX

DIMENSION

$$A = (\text{NB. PINS} - 1) \times \text{PITCH}$$
$$B = ((\text{NB. PINS} - 1) \times \text{PITCH}) + 5$$

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15	 WÜRTH ELEKTRONIK		
G								
F								
E								
D	07-APR-16	DRAWING	AK	APPROVAL: FBr	UNIT: MM	DESCRIPTION: SERIE 321 - 3.81MM VERTICAL PCB HEADERS WR-TBL		SIZE A4
C	12-OCT-09	STANDARD	JP		SCALE:			
B	29-OCT-08	CHARACTERISTICS	JP		SHEET: 1/2	WERI PART NO: 691 321 300 0xx		
A	31-OCT-07	PDF	EC		DRAW: MARVIN			
REV	DATE	FILE	BY					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691321300020](#)