


DESIGN KIT

SMD Common Mode Filters for Data Lines



SIZE:

WE-SLM, WE-SL3, WE-SL5, WE-SL1, WE-SL2,
WE-SL, WE-SCC, WE-UCF, WE-SL5HC


TECHNICAL DATA:

L: 1 ~ 100000 μ H
 Z max.: 100 ~ 600000 Ω
 I_R : 150 ~ 10000 mA
 R_{DC} : 0.0027 ~ 8.5 Ω

Order Code 744 725

Version 2.0

SMD Common Mode Chokes for USB, CAN, Firewire, Data Lines and Power Lines



WE-SLM			WE-SL3		
744 242 110	744 242 510	744 242 471	744 252 220	744 252 510	744 253 200
L: 2 x 11 μ H	L: 2 x 51 μ H	L: 2 x 470 μ H	L: 2 x 22 μ H	L: 2 x 51 μ H	L: 3 x 20 μ H
Z max.: 800 Ω	Z max.: 2500 Ω	Z max.: 2200 Ω	Z max.: 1600 Ω	Z max.: 3300 Ω	Z max.: 1250 Ω
I _R : 300 mA	I _R : 300 mA	I _R : 400 mA	I _R : 700 mA	I _R : 500 mA	I _R : 500 mA
R _{DC} : 0.18 Ω	R _{DC} : 0.32 Ω	R _{DC} : 0.70 Ω	R _{DC} : 0.14 Ω	R _{DC} : 0.25 Ω	R _{DC} : 0.16 Ω
744 253 101					
L: 3 x 100 μ H					
Z max.: 5000 Ω					
I _R : 450 mA					
R _{DC} : 0.45 Ω					
WE-SL5			WE-SL1		
744 272 121	744 272 251	744 272 102	744 272 472	744 212 100	744 212 820
L: 2 x 120 μ H	L: 2 x 250 μ H	L: 2 x 1000 μ H	L: 2 x 4700 μ H	L: 2 x 10 μ H	L: 2 x 82 μ H
Z max.: 460 Ω	Z max.: 970 Ω	Z max.: 3600 Ω	Z max.: 13000 Ω	Z max.: 1200 Ω	Z max.: 440 Ω
I _R : 2500 mA	I _R : 2000 mA	I _R : 950 mA	I _R : 350 mA	I _R : 300 mA	I _R : 300 mA
R _{DC} : 0.025 Ω	R _{DC} : 0.035 Ω	R _{DC} : 0.180 Ω	R _{DC} : 0.720 Ω	R _{DC} : 0.24 Ω	R _{DC} : 0.20 Ω
744 212 331					
L: 2 x 330 μ H					
Z max.: 2000 Ω					
I _R : 300 mA					
R _{DC} : 0.30 Ω					
WE-SL2					
744 226	744 226 S	744 227	744 227 S	744 224	744 222
L: 2 x 10 μ H	L: 2 x 10 μ H	L: 2 x 51 μ H	L: 2 x 51 μ H	L: 2 x 250 μ H	L: 2 x 1000 μ H
Z max.: 920 Ω	Z max.: 920 Ω	Z max.: 5500 Ω	Z max.: 5500 Ω	Z max.: 1800 Ω	Z max.: 6000 Ω
I _R : 1600 mA	I _R : 1600 mA	I _R : 1000 mA	I _R : 1000 mA	I _R : 1200 mA	I _R : 800 mA
R _{DC} : 0.08 Ω	R _{DC} : 0.08 Ω	R _{DC} : 0.16 Ω	R _{DC} : 0.16 Ω	R _{DC} : 0.13 Ω	R _{DC} : 0.31 Ω
744 229					
L: 2 x 6500 μ H					
Z max.: 18400 Ω					
I _R : 400 mA					
R _{DC} : 0.95 Ω					
WE-SL			WE-SCC		
744 206	744 205	744 201	744 281 100	744 281 471	744 282 010
L: 2 x 60 μ H	L: 4 x 100 μ H	L: 4 x 4700 μ H	L: 2 x 10 μ H	L: 2 x 470 μ H	L: 2 x 1 μ H
Z max.: 1600 Ω	Z max.: 900 Ω	Z max.: 14000 Ω	Z max.: 10000 Ω	Z max.: 100000 Ω	Z max.: 1600 Ω
I _R : 2000 mA	I _R : 700 mA	I _R : 200 mA	I _R : 1100 mA	I _R : 150 mA	I _R : 4750 mA
R _{DC} : 0.065 Ω	R _{DC} : 0.10 Ω	R _{DC} : 0.85 Ω	R _{DC} : 0.12 Ω	R _{DC} : 4.3 Ω	R _{DC} : 0.01 Ω
744 282 102					
L: 2 x 1000 μ H					
Z max.: 160000 Ω					
I _R : 250 mA					
R _{DC} : 2.8 Ω					
WE-UCF			WE-SL5HC		
744 290 130	744 290 321	744 290 152	744 290 103	744 290 104	744 273 501
L: 2 x 13 μ H	L: 2 x 320 μ H	L: 2 x 1500 μ H	L: 2 x 10000 μ H	L: 2 x 100000 μ H	L: 2 x 5 μ H
Z max.: 100 Ω	Z max.: 3000 Ω	Z max.: 10000 Ω	Z max.: 100000 Ω	Z max.: 600000 Ω	Z max.: 500 Ω
I _R : 10000 mA	I _R : 3250 mA	I _R : 1500 mA	I _R : 500 mA	I _R : 150 mA	I _R : 5000 mA
R _{DC} : 0.0027 m Ω	R _{DC} : 0.29 m Ω	R _{DC} : 0.12 m Ω	R _{DC} : 0.92 m Ω	R _{DC} : 8.5 m Ω	R _{DC} : 0.0055 m Ω
744 273 222					
L: 2 x 30 μ H					
Z max.: 1200 Ω					
I _R : 1400 mA					
R _{DC} : 0.060 m Ω					

EMC COMPONENTS | INDUCTORS | TRANSFORMERS | RF COMPONENTS | CIRCUIT PROTECTION | EMC SHIELDING MATERIAL | CONNECTORS | SWITCHES | ASSEMBLY TECHNIQUE | POWER ELEMENTS

Important information: Würth Elektronik's design kits contain reference components. These components correspond with the current product development status on the day of supply. Exchange of the reference components to components with up-to-date product development status is not carried out automatically. No liability is taken for the use of these reference components. Therefore, please request new samples prior to releases for series production and product release.

Please check datasheets on www.we-online.com for specifications. Würth Elektronik eiSos GmbH & Co. KG, EMC & Inductive Solutions. © 2014

www.we-online.com

All products
in stock!

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[744725](#)