



Product: [573945](#)

Surveillance CCTV, Mini-RG59 #25 BC, 94% BC Braid, CM

Product Description

Surveillance & CCTV Cable, mini-RG59, Rated-CM, 25 AWG solid bare copper, foam polyolefin core, 94% bare copper braid, PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Surveillance, CCTV Camera
------------------------	---------------------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
25	Solid	BC - Bare Copper	0.019 in	1

Insulation

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.085 in

Table Notes:	Gas Injected
--------------	--------------

Outer Shield

Type	Material	Coverage [%]
Braid	Bare Copper (BC)	95%

Outer Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.146 in

Weight:	0.8 lbs
---------	---------

Construction and Dimensions

OuterJacket1, Nominal Width:	0.85 mm
------------------------------	---------

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
31 Ohm/1000ft	31 Ohm/1000ft	5.6 Ohm/1000ft	5.6 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
16.8 pF/ft

Inductance

Nominal Inductance
0.109 µH/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.45 dB/100ft
5 MHz	0.9 dB/100ft
10 MHz	1.3 dB/100ft
50 MHz	3 dB/100ft
100 MHz	4.1 dB/100ft
200 MHz	6 dB/100ft
400 MHz	8.6 dB/100ft
700 MHz	11.6 dB/100ft
900 MHz	13.5 dB/100ft
1000 MHz	14.5 dB/100ft

Delay

Max. Delay Skew	Nominal Delay	Nominal Velocity of Propagation (VP) [%]
80 ns/100m	1.27 ns/ft	80%

Unbalanced Crosstalk

Typical Unbalanced NEXT %
0.8 MHz

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-30°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	14 lbs/1000ft
Max. Pull Tension:	28 lbs
Min. Bend Radius/Minor Axis:	1.5 in

Dimensions (WxHxD)

Height	Depth
0.87	0.87

Standards

NEC/(UL) Compliance:	CM
CEC/C(UL) Compliance:	CM
RG Type:	Mini 59

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	Yes - Black only, when supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT1
UL Flammability:	UL1685 UL Loading
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	673948

Part Number

Variants

Item #	Color	Put-Up Type	Length	UPC
573945 0101000	Black	Reel	1,000 ft	612825165088
573945 010U1000	Black	UnReel	1,000 ft	612825165071
573945 0061000	Blue	Reel	1,000 ft	612825165057
573945 006U1000	Blue	UnReel	1,000 ft	612825165040
573945 001U1000	Brown	UnReel	1,000 ft	612825165002
573945 0051000	Green	Reel	1,000 ft	612825165033
573945 0021000	Red	Reel	1,000 ft	612825165019
573945 0091000	White	Reel	1,000 ft	612825165064
573945 0041000	Yellow	Reel	1,000 ft	612825165026

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.407 Revision Date: 12-15-2021
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[573945 0091000](#) [573945 0101000](#) [573945 0041000](#) [573945 0051000](#) [573945 0021000](#) [573945 0061000](#)