

CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes





more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.095 ohms ±10%
D.C. RESISTANCE	3-4 @20°C	0.115 ohms ±10%
D.C. RESISTANCE	5-7 @20°C	0.040 ohms ±10%
D.C. RESISTANCE	6-8 @20°C	0.057 ohms ±10%
INDUCTANCE	3-4 10kHz, 100mVAC, Ls	63.0uH ±10%
⑥C SATURATION CURRENT	20% rolloff from initial	1.45A
LEAKAGE INDUCTANCE	3-4 tie(1+2, 5+6+7+8), 100kHz, 50mVAC, Ls	800nH max.
DIELECTRIC RATING	1-8 tie(2+3, 5+6), 1875VAC, 1 second	1500VAC, 1 minute
TURNS RATIO	(3-4):(5-7)	3:1, ±1%
TURNS RATIO	(3-4):(8-6)	3:1, ±1%
TURNS RATIO	(3-4):(2-1)	3:1, ±1%

TERM. NO.'s FOR REF. ONLY



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +85°C including temp rise.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0328 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750310564
6C	9/10			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750310564	SPECIFICATION SHEET 1 OF 1
6B	1/09					
6A	9/08	SEE REVISION SHEET FOR REVISION LEVEL				



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[750310564](#)