


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-3 @20°C	0.98 ohms ±10%
D.C. RESISTANCE	6-4 @20°C	0.055 ohms max.
INDUCTANCE	1-3 10kHz, 100mVAC, Ls	400uH ±10%
SATURATION CURRENT	20% rolloff from initial	580mA
LEAKAGE INDUCTANCE	1-3 tie(4+6), 100kHz, 100mVAC, Ls	4.0uH typ., 8.0uH max.
DIELECTRIC	1-6 1850VAC, 1 second	1500VAC, 1 minute
URNS RATIO	(1-2):(2-3)	1:1, ±1%
URNS RATIO	(1-3):(6-4)	7.111:1, ±1%

GENERAL SPECIFICATIONS:  
OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Safety Standard Undefined.

Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: <b>Tape &amp; Reel</b> PKG-0519 www.we-online.com/midcom		Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	<b>TRANSFORMER</b>	<b>750312366</b>
6B	2/21	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750312366	SPECIFICATION SHEET 1 OF 1
6A	01/12					



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[750312366](#)