



Product: [6320UL](#)

Fire Alarm, #18-2c BC, FPLP

Product Description

Fire Alarm Cable, Plenum-FPLP, 2-18 AWG solid bare copper conductors with Flamarrest® insulation, Flamarrest® jacket with ripcord

Technical Specifications

Product Overview

Suitable Applications:	Fire Alarm, Monitor/Detection, Circuits: Audio, Control, Initiating, Notification
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	18 AWG	Solid	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.008 in (0.20 mm)	0.057 in (1.4 mm)	Black, Red

Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.144 in (3.66 mm)	Yes

Overall Cable Diameter (Nominal):	0.144 in (3.66 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	6.4 Ohm/1000ft	31 pF/ft (100 pF/m)	14 Amps per conductor @ 25°C

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	0°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
1.15 in (29.2 mm)	1.15 in (29.2 mm)

Max. Pull Tension:	39 lbs (18 kg)
Bulk Cable Weight:	15 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum)
NEC / UL Compliance:	Article 760, FPLP
European Directive Compliance:	EU CE Mark
Other Standard Compliance(s):	California State Fire Marshall
Non-Plenum Number:	5320UL

History

Update and Revision:	Revision Number: 0.498 Revision Date: 06-21-2024
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
6320UL 0101000	Black	612825175919	
6320UL 010C500	Black	612825175896	
6320UL 010U1000	Black	612825175902	
6320UL D15C500	Blue	612825175766	
6320UL 0051000	Green, Dark	612825175841	
6320UL 005U1000	Green, Dark	612825175834	
6320UL 0031000	Orange	612825175810	
6320UL 003U1000	Orange	612825175803	
6320UL 012U1000	Pink	612825175926	
6320UL 0021000	Red	612825175797	C
6320UL 002U1000	Red	612825175773	
6320UL 002U500	Red	612825175780	
6320UL 007C500	Violet	612825175858	
6320UL 007U1000	Violet	612825175865	
6320UL 009C500	White	612825175872	
6320UL 009U1000	White	612825175889	
6320UL 004U1000	Yellow	612825175827	

© 2024 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[6320UL 0101000](#) [6320UL 007C500](#) [6320UL 0091000](#) [6320UL 009C500](#) [6320UL 0031000](#) [6320UL 0041000](#)
[6320UL 010C500](#) [6320UL 0051000](#) [6320UL 0021000](#) [6320UL D151000](#) [6320UL D15C500](#)