



Product: [639948](#)

PTZ, RG-6 #18, #18-2c, CMP, Siamese

Product Description

PTZ (CCTV + Power/Audio) Cable, Plenum-CMP, 1-RG6 18 AWG solid bare copper with foam FEP, 95% bare copper braid, 1-18 AWG stranded bare copper pair with Flamarrest® insulation, Siamese with Flamarrest® jacket

Technical Specifications

Product Overview

Suitable Applications:	Surveillance, CCTV Camera, PTZ (Pan-Tilt-Zoom)
------------------------	------------------------------------------------

Physical Characteristics (Overall)

Conductor						
Element	AWG	Stranding	Material	Nominal Diameter	No. of Conductors	No. of Coax
Coax(es)	18	Solid	BC - Bare Copper			1
Pair1	18	7x26	BC - Bare Copper	0.047 in	2	
Conductor Count:				3		

Insulation		
Element	Material	Nominal Diameter
Coax(es)	PE - Polyethylene (Foam)	0.170 in
Pair1	PVC - Polyvinyl Chloride	0.062 in
Table Notes:		Gas Injected

Color Chart	
Number	Color
Coax Core	White
Pair1	Black & Red

Inner Shield			
Element	Type	Material	Coverage [%]
Coax(es)	Braid	Bare Copper (BC)	95%
Pair1		No Shield	

Inner Jacket	
Nominal Diameter	
0.230 in	

Outer Jacket		
Material	Material Trade Name	Nominal Diameter
PVC - Polyvinyl Chloride	Flamarrest®	0.230 in x 0.424 in

Construction and Dimensions

OuterJacket1, Nominal Width:	0.0394 in
------------------------------	-----------

Electrical Characteristics

Conductor DCR

Element	Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Inner Shield DCR
Coax(es)	6.4 Ohm/1000ft	6.4 Ohm/1000ft	2.2 Ohm/1000ft
Pair1			

Capacitance

Element	Nom. Capacitance Conductor to Conductor
Coax(es)	16.1 pF/ft
Pair1	

Impedance

Element	Nominal Characteristic Impedance
Coax(es)	75 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]
1 MHz
5 MHz
10 MHz
50 MHz
100 MHz
200 MHz
400 MHz
700 MHz
900 MHz
1000 MHz

Delay

Element	Max. Delay Skew	Nominal Delay
Coax(es)	84 ns/100m	1.21 ns/ft

Current

Element
Coax(es)
Pair1

Temperature Range

Installation Temperature Range:	0°C To +75°C
UL Temp Rating:	75°C
Operating Temperature Range:	0°C To +75°C
Separation Temp Range:	0°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	55 lbs/1000ft
Max. Pull Tension:	89 lbs

Standards

NEC Articles:	Article 800
NEC/(UL) Compliance:	CMP
CEC/C(UL) Compliance:	CMP
CPR Euroclass:	Eca
RG Type:	6

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Plenum
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	Yes

EU CE Mark:	Yes
MIl Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	NFPA 262
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Related Part Numbers

Non-Plenum Number:	539945
--------------------	--------

Variants

Item #	Color	Put-Up Type	Length	UPC
639948 877500	Natural	Reel	500 ft	612825176558
639948 8771000	Natural	Reel	1,000 ft	612825176541

Product Notes

Notes:	18 AWG pair is unshielded
--------	---------------------------

History

Update and Revision:	Revision Number: 0.505 Revision Date: 04-29-2024
----------------------	--------------------------------------------------

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[639948 8771000](#) [639948 877500](#)