



Product: [73502T](#)

DS3/DS4 Central Office Coax, 2 x Sub-miniature RG-59, 26 AWG, Solid SC, Foil + 95% TC Braids, PVC Inner & Outer Jkts, Tracer, CMR

Product Description

DS3/DS4 Central Office Coax, 2 Coaxes, Sub-miniature RG-59, 26 AWG, Solid Silvered Copper Conductor, PE Insulation, Foil + 95% Tinned Copper Braid Shields, PVC Inner and Outer Jackets, Tracer Wire, CMR

Technical Specifications

Product Overview

Suitable Applications:	Central office wiring, DS3/DS4 interconnect, 734/735 telecommunications systems, switchboard communications
------------------------	---

Construction Details

RG Type:	Sub-miniature 59
----------	------------------

Conductor

Size	Stranding	Nom. Diameter	Material
26 AWG	Solid	0.016 in	SC - Silvered Copper

Insulation

Material	Nom. Insulation Diameter
PE - Polyethylene (Foam)	0.077 in (2.0 mm)

Inner Shield

Layer	Shield Type	Material	Material Trade Name	Coverage
1	Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%
2	Braid	Tinned Copper (TC)		95%

Inner Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.129 in (3.28 mm)

Table Notes:	One red, one gray
--------------	-------------------

Outer Jacket

Material
PVC - Polyvinyl Chloride

Table Notes:	0.308 in x 0.179 in, 22 AWG tracer wire on side
--------------	---

Electrical Characteristics

Return Loss (RL)

Frequency	Min. Return Loss
15 - 95 MHz	30 dB

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
41 Ohm/1000ft (130 Ohm/km)	17.7 pF/ft (58.1 pF/m)	75 Ohm	76%

Voltage

UL Voltage Rating

300 V (CMR, CMG)

Mechanical Characteristics

Temperature

Operating
-20°C to +75°C

Bend Radius

Installation Min.
3.1 in

Max. Pull Tension:	37 lbs (17 kg)
Bulk Cable Weight:	36 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL1666 Vertical Shaft
NEC / UL Compliance:	CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.190 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
73502T 008500	Gray	Reel	500 ft	612825185062	C
73502T 0081000	Gray	Reel	1,000 ft	612825185055	C

© 2024 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[735O2T 0081000](#) [735O2T 008500](#)