



**Product:** [7732A](#)

75 Ohm SDI Coax, RG-11, 14 AWG Solid BC, Foil + 95% TC Braid, PVDF Jkt, CMP

Product Description

75 Ohm SDI Coax, RG-11, 14 AWG Solid Bare Copper Conductor, FEP Insulation, Foil + 95% Tinned Copper Braid Shield, PVDF Jacket, CMP

Technical Specifications

Product Overview

Suitable Applications:	Digital Video, 6 Gb/s UHDTV, HD-SDI 1080p
------------------------	---

Construction Details

RG Type:	11
----------	----

Conductor

Size	Stranding	Nom. Diameter	Material
14 AWG	Solid	0.064 in	BC - Bare Copper

Insulation

Material	Nom. Insulation Diameter	Color Code
FEP - Fluorinated Ethylene Propylene (Foam)	0.274 in (6.96 mm)	White

Outer Shield

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
2	Braid	Tinned Copper (TC)		95%

Outer Jacket

Material	Nom. Diameter
PVDF - Polyvinylidene Fluoride	0.348 in (8.84 mm)

Overall Cable Diameter (Nominal):	0.348 in (8.84 mm)
-----------------------------------	--------------------

Electrical Characteristics

Return Loss (RL)

Frequency	Min. Return Loss
5 - 1600 MHz	23 dB
1600 - 4500 MHz	21 dB
4500 - 6000 MHz	15 dB

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.15 dB/100ft
3.58 MHz	0.26 dB/100ft
5 MHz	0.3 dB/100ft
7 MHz	0.34 dB/100ft
10 MHz	0.4 dB/100ft
67.5 MHz	1.2 dB/100ft
71.5 MHz	1.24 dB/100ft

88.5 MHz	1.4 dB/100ft
100 MHz	1.5 dB/100ft
135 MHz	1.55 dB/100ft
143 MHz	1.84 dB/100ft
180 MHz	2.09 dB/100ft
270 MHz	2.60 dB/100ft
360 MHz	3.10 dB/100ft
540 MHz	3.89 dB/100ft
720 MHz	4.57 dB/100ft
750 MHz	4.68 dB/100ft
1000 MHz	5.50 dB/100ft
1500 MHz	7.06 dB/100ft
2000 MHz	8.57 dB/100ft
2500 MHz	9.20 dB/100ft
3000 MHz	10.2 dB/100ft
4500 MHz	14.67 dB/100ft
6000 MHz	17.86 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
2.5 Ohm/1000ft	1.6 Ohm/1000ft (5.2 Ohm/km)	16.3 pF/ft (53.5 pF/m)	75 Ohm	83%

Voltage

UL Voltage Rating
300 V (CMP)

Mechanical Characteristics

Temperature

UL Temperature	Operating
125°C	-20°C to +125°C

Bend Radius

Installation Min.
3.5 in (89 mm)

Max. Pull Tension:	145 lbs (65.8 kg)
Bulk Cable Weight:	75 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/OutdoorIndoor - Plenum, Indoor, Outdoor, Sunlight Resistance, UV Resistance, Aerial - When supported by messenger wire
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	NFPA 262
NEC / UL Compliance:	CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Non-Plenum Number:	7731A

History

Update and Revision:	Revision Number: 0.512 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
7732A 010500	Black	Reel	500 ft	612825188872	C
7732A 0101000	Black	Reel	1,000 ft	612825188858	C
7732A 0101200	Black	Reel	1,200 ft	612825438250	
7732A 0103000	Black	Reel	3,000 ft	612825188865	
7732A 0061000	Blue, Light	Reel	1,000 ft	612825188841	C
7732A 877500	Natural	Reel	500 ft	612825188896	C
7732A 8771000	Natural	Reel	1,000 ft	612825188889	C

7732A 0041000	Yellow	Reel	1,000 ft	612825188834	C
---------------	--------	------	----------	--------------	---

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[7732A 0101000](#) [7732A 010500](#) [7732A 0061000](#) [7732A 8771000](#) [7732A 877500](#) [7732A 0041000](#)