

DESIGN KIT

WCAP-FTBP DC Film Capacitors

MKP – Metallized Polypropylene

**SIZE:**

7.5 – 27.5 mm Pitch

TECHNICAL DATA:

Capacitance Range: 33 – 6800 nF
Capacitance Tolerance: 5 %
Rated Voltages: 160 – 630 V_{DC}

Order Code 890 010

Version 1.0

DESIGN KIT

WCAP-FTBP DC Film Capacitors

MKP – Metallized Polypropylene



890 443 322 001 CS	
MPPP075104J160DCPB15004	
C:	100 nF
U _R :	160 V _{DC}
U _{RMS} :	90 V _{AC}
R _{ISO} :	> 30,000 MΩ
dV/dt:	300 V/μS
DF:	@ 1 kHz < 0.1 %
	@ 10 kHz 0.1 %
	@ 100 kHz 0.26 %

890 273 322 005 CS	
MPPP075154J250DCPB15004	
C:	150 nF
U _R :	250 V _{DC}
U _{RMS} :	160 V _{AC}
R _{ISO} :	> 30,000 MΩ
dV/dt:	340 V/μS
DF:	@ 1 kHz < 0.1 %
	@ 10 kHz 0.1 %
	@ 100 kHz 0.26 %

890 303 322 005 CS	
MPPP075333J630DCPB15004	
C:	33 nF
U _R :	630 V _{DC}
U _{RMS} :	250 V _{AC}
R _{ISO} :	> 30,000 MΩ
dV/dt:	700 V/μS
DF:	@ 1 kHz < 0.1 %
	@ 10 kHz 0.1 %
	@ 100 kHz 0.15 %

890 273 323 004 CS	
MPPP010224J250DCPB15004	
C:	220 nF
U _R :	250 V _{DC}
U _{RMS} :	160 V _{AC}
R _{ISO} :	> 30,000 MΩ
dV/dt:	250 V/μS
DF:	@ 1 kHz < 0.1 %
	@ 10 kHz 0.1 %
	@ 100 kHz 0.4 %

890 283 323 005 CS	
MPPP010104J400DCPB15004	
C:	100 nF
U _R :	400 V _{DC}
U _{RMS} :	220 V _{AC}
R _{ISO} :	> 30,000 MΩ
dV/dt:	300 V/μS
DF:	@ 1 kHz < 0.1 %
	@ 10 kHz 0.1 %
	@ 100 kHz 0.35 %

890 443 325 010 CS	
MPPP015225J160DCPB15004	
C:	2200 nF
U _R :	160 V _{DC}
U _{RMS} :	90 V _{AC}
R _{ISO} :	> 10,000 MΩ
dV/dt:	98 V/μS
DF:	@ 1 kHz < 0.1 %
	@ 10 kHz 0.28 %
	@ 100 kHz 1.6 %

890 273 325 009 CS	
MPPP015105J250DCPB15004	
C:	1000 nF
U _R :	250 V _{DC}
U _{RMS} :	160 V _{AC}
R _{ISO} :	> 10,000 MΩ*μF
dV/dt:	85 V/μS
DF:	@ 1 kHz < 0.1 %
	@ 10 kHz 0.28 %
	@ 100 kHz 1.5 %

890 283 325 008 CS	
MPPP015334J400DCPB15004	
C:	330 nF
U _R :	400 V _{DC}
U _{RMS} :	220 V _{AC}
R _{ISO} :	> 30,000 MΩ
dV/dt:	140 V/μS
DF:	@ 1 kHz < 0.1 %
	@ 10 kHz 0.15 %
	@ 100 kHz 0.92 %

890 303 325 010 CS	
MPPP015224J630DCPB15004	
C:	220 nF
U _R :	630 V _{DC}
U _{RMS} :	250 V _{AC}
R _{ISO} :	> 30,000 MΩ
dV/dt:	220 V/μS
DF:	@ 1 kHz < 0.1 %
	@ 10 kHz 0.15 %
	@ 100 kHz 0.68 %

890 273 326 007 CS	
MPPP225155J250DCPB45004	
C:	1500 nF
U _R :	250 V _{DC}
U _{RMS} :	160 V _{AC}
R _{ISO} :	> 10,000 MΩ*μF
dV/dt:	61 V/μS
DF:	@ 1 kHz < 0.1 %
	@ 10 kHz 0.4 %
	@ 100 kHz 3.4 %

890 283 326 009 CS	
MPPP225105J400DCPB45004	
C:	1000 nF
U _R :	400 V _{DC}
U _{RMS} :	220 V _{AC}
R _{ISO} :	> 10,000 MΩ*μF
dV/dt:	95 V/μS
DF:	@ 1 kHz < 0.1 %
	@ 10 kHz 0.32 %
	@ 100 kHz 2.2 %

890 303 326 009 CS	
MPPP225474J630DCPB45004	
C:	470 nF
U _R :	630 V _{DC}
U _{RMS} :	250 V _{AC}
R _{ISO} :	> 10,000 MΩ*μF
dV/dt:	130 V/μS
DF:	@ 1 kHz < 0.1 %
	@ 10 kHz 0.28 %
	@ 100 kHz 1.5 %

890 443 327 007 CS	
MPPP275685J160DCPB55004	
C:	6800 nF
U _R :	160 V _{DC}
U _{RMS} :	90 V _{AC}
R _{ISO} :	> 10,000 MΩ*μF
dV/dt:	46 V/μS
DF:	@ 1 kHz < 0.1 %
	@ 10 kHz 0.75 %
	@ 100 kHz 5.9 %

890 283 327 008 CS	
MPPP275225J400DCPB55004	
C:	2200 nF
U _R :	400 V _{DC}
U _{RMS} :	220 V _{AC}
R _{ISO} :	> 10,000 MΩ*μF
dV/dt:	98 V/μS
DF:	@ 1 kHz < 0.1 %
	@ 10 kHz 0.4 %
	@ 100 kHz 3.4 %

890 303 327 008 CS	
MPPP275155J630DCPB55004	
C:	1500 nF
U _R :	630 V _{DC}
U _{RMS} :	250 V _{AC}
R _{ISO} :	> 10,000 MΩ*μF
dV/dt:	130 V/μS
DF:	@ 1 kHz < 0.1 %
	@ 10 kHz 0.34 %
	@ 100 kHz 2.3 %

Technical Data

MKP – Metallized Polypropylene
Climate Category: 40 / 105 / 56

- Pitch 7.5 mm
- Pitch 10.0 mm
- Pitch 15.0 mm
- Pitch 22.5 mm
- Pitch 27.5 mm



EMC COMPONENTS | INDUCTORS | TRANSFORMERS | RF COMPONENTS | CIRCUIT PROTECTION | EMC SHIELDING MATERIAL | LEDs | CONNECTORS | SWITCHES | ASSEMBLY TECHNIQUE | REDCUBE TERMINALS | CAPACITORS

Important information: Würth Elektronik's design kits contain reference components. These components correspond with the current product development status on the day of supply. Exchange of the reference components to components with up-to-date product development status is not carried out automatically. No liability is taken for the use of these reference components. Therefore, please request new samples prior to releases for series production and product release.

All products
ex stock!

Please check datasheets on www.we-online.com for specifications. Würth Elektronik eiSos GmbH & Co. KG, EMC & Inductive Solutions. © 2017

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[890010](#)