



Product: [8241](#) 

75 Ohm Analog Video Coax, RG-59, 23 AWG Solid BCCS, 95% BC Braid, PVC Jkt, CM

Product Description

75 Ohm Analog Video Coax, RG-59, 23 AWG Solid Bare Copper Covered Steel Conductor , PE Insulation, 95% Bare Copper Braid Shield, PVC Jacket, CM

Technical Specifications

Product Overview

Suitable Applications:	Standard analog video
------------------------	-----------------------

Construction Details

RG Type:	59
----------	----

Conductor

AWG	Stranding	Nom. Diameter	Material
23	Solid	0.023 in	BCCS - Bare Copper Covered Steel

Insulation

Material	Nom. Diameter
PE - Polyethylene	0.146 in

Outer Shield Material

Outer Shield Type	Material	Coverage
Braid	Bare Copper (BC)	95%

Outer Jacket Material

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.240 in

Electrical Characteristics

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.6 dB/100ft
10 MHz	1.1 dB/100ft
50 MHz	2.4 dB/100ft
100 MHz	3.4 dB/100ft
200 MHz	4.9 dB/100ft
400 MHz	7.0 dB/100ft
700 MHz	9.7 dB/100ft
900 MHz	11.1 dB/100ft
1000 MHz	12.0 dB/100ft

Power Rating

Frequency [MHz]	Max. Power Rating [W]
50 MHz	470 W
100 MHz	310 W
300 MHz	160 W

500 MHz	115 W
1,000 MHz	76 W

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Impedance	Nom. Velocity
49 Ohm/1000ft	2.6 Ohm/1000ft	20.4 pF/ft	75 Ohm	66%

Voltage

UL Voltage Rating	Non-UL Voltage Rating
300 V (CM), 30 V (UL AWM 1354)	1700 V

Mechanical Characteristics

Temperature

UL Rating	Operating
75°C	-30°C to +75°C

Bend Radius

Installation Min.
2.4 in

Bulk Cable Weight:	37 lbs/1000ft
Max. Pull Tension:	63 lbs

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor
Sustainability:	CA Prop 65
Flammability / Fire Resistance:	UL1685 UL Loading
NEC / UL Compliance:	CM
AWM Compliance:	1354
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	88241, 82241

History

Update and Revision:	Revision Number: 0.316 Revision Date: 09-30-2020
----------------------	--------------------------------------------------

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[8241 0101000](#) [8241 010U1000](#) [8241 010U500](#) [8241 002U1000](#) [8241 010100](#) [8241 010500](#) [8241 006U1000](#) [8241 009U1000](#) [8241 0105000](#) [8241 0102000](#) [8241 003U1000](#) [8241 005U1000](#) [8241 004U1000](#)