

DATA SHEET

**ELECTROSTATIC DISCHARGE
PROTECTION DEVICES**


INDUSTRIAL / CONSUMER

SJD16AXXL01 SERIES

RoHS compliant & Halogen free



Product specification— December 03, 2023 V.5



Electrostatic Discharged Protection Devices (ESD) Data Sheet

Description

Brightking's SJD16AXXL01 series are designed to protect power port and the chip Vbus interfaces. It has been specifically designed to protect sensitive components which are connected to power lines from overvoltage caused by electrostatic discharge (ESD), cable discharge events (CDE) and lightning.

These devices integrate a high power transient voltage suppressor (TVS) and small package. It features solid-state silicon-avalanche technology for unmatched transient protection without device degradation. It offers superior electrical characteristics including fast response time, low clamping voltage and no device degradation. This allows the designer maximum flexibility and reduces parts count.

The series devices may be used to meet the immunity requirements of IEC61000-4-2 (ESD), IEC61000-4-4 (EFT), IEC61000-4-5 (Surge).




Contact : $\pm 30\text{kV}$
Air : $\pm 30\text{kV}$



Features

- IEC61000-4-2 ESD 30KV Air, 30KV contact compliance
- DFN1610 surface mount package
- Protects power line
- Working voltage: 7V, 10V, 12V
- SJD16A07L01~SJD16A12L01, Cathode rays on the Pin1
- Low leakage current
- Low clamping voltage
- Solid-state silicon avalanche technology
- RoHS compliant
- Solder reflow temperature: Pure Tin-Sn, 260~270°C
- Flammability rating UL 94V-0
- Meets MSL level 1, per J-STD-020



SJD16A07L01~SJD16A12L01

Pin Configuration

Applications

- Power port
- I²C bus protection

Maximum Ratings

Rating	Symbol	Value	Unit
Peak pulse power (tp=10/1000μs waveform)	P _{pp}	120	W
Peak pulse power(tp=8/20μs waveform) SJD16A07L01~SJD16A12L01	P _{pp}	2000	W
ESD voltage (Contact discharge)	V _{ESD}	±30	kV
ESD voltage (Air discharge)		±30	
Storage & operating temperature range	T _{STG} , T _J	-55~+150	°C

Electrical Characteristics (T_J=25°C)

SJD16A07L01(Marking: J07)

Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
Reverse stand-off voltage	V _{RWM}				7	V
Reverse breakdown voltage	V _{BR}	I _{BR} =1.0mA	7.3			V
Reverse leakage current	I _R	V _R =7.0V			1.0	μA
Clamping voltage (tp=8/20μs)	V _C	I _{PP} =80A		30		V
Peak Pulse Current(tp=8/20μs)	I _{PP}				80	A
Off state junction capacitance	C _J	0Vdc,f=1MHz Between I/O pins and GND		650		pF

Electrical Characteristics (T_J=25°C)

SJD16A10L01(Marking: J10)



Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
Reverse stand-off voltage	V _{RWM}				10	V
Reverse breakdown voltage	V _{BR}	I _{BR} =1.0mA	11			V
Reverse leakage current	I _R	V _R =10V			1.0	μA
Clamping voltage (tp=8/20μs)	V _C	I _{PP} =60A		35		V
Peak Pulse Current(tp=8/20μs)	I _{PP}				60	A
Off state junction capacitance	C _J	0Vdc,f=1MHz Between I/O pins and GND		400		pF

SJD16A12L01 (Marking: J12)

Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
Reverse stand-off voltage	V_{RWM}				12	V
Reverse breakdown voltage	V_{BR}	$I_{BR}=1.0mA$	13			V
Reverse leakage current	I_R	$V_R=12V$			1.0	μA
Clamping voltage ($t_p=8/20\mu s$)	V_C	$I_{PP}=47A$		43		V
Peak Pulse Current($t_p=8/20\mu s$)	I_{PP}				47	A
Off state junction capacitance	C_J	0Vdc, f=1MHz Between I/O pins and GND		365		pF

Typical Characteristics Curves

Figure 1. Power Derating Curve

Figure 2. 8/20 μs Pulse Waveforms

Typical Characteristics Curves

Figure 3. Clamping Voltage vs. Peak Pulse Current




Figure 4. ESD Clamping (8kV Contact IEC61000-4-2)




Figure 5. 10/1000μs Pulse Waveform






Figure 6. Typical Junction Capacitance



Recommended Soldering Conditions

Reflow Soldering



Recommended Conditions

Profile Feature	Pb-Free Assembly
Average ramp-up rate (TL to TP)	3°C/second max.
Preheat	
-Temperature Min (TS min)	150°C
-Temperature Max (TS max)	200°C
-Time (min to max) (ts)	60-180 seconds
TS max to TL	
-Ramp-up Rate	3°C/second max.
Time maintained above:	
-Temperature (TL)	217°C
-Time (tL)	60-150 seconds
Peak Temperature (TP)	260°C
Time within 5°C of actual Peak Temperature (tP)	20-40 seconds
Ramp-down Rate	6°C/second max.
Time 25°C to Peak Temperature	8 minutes max.

Dimensions (DFN1610)

Symbol	Dimension			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.55	0.66	0.022	0.026
A1	0.00	0.05	0.000	0.002
D	1.55	1.68	0.061	0.066
E	0.95	1.08	0.037	0.043
b	0.8 TYP		0.031 TYP	
e	1.1 TYP		0.043 TYP	
L	0.35	0.45	0.014	0.018
h	0.15	0.25	0.006	0.010

Packaging

Tape	Symbol	Dimension (mm)
	W	8.00±0.30
	P0	4.00±0.10
	P1	2.00±0.10
	P2	2.00±0.10
	D0	Φ1.50±0.10
	E	1.75±0.05
	F	3.50±0.10
	B0	1.72±0.05
Reel	D	Φ178.0±2.0
	D2	Φ54.50±1.0
	W1	9.5±2.0
	W2	12.30±1.5
	Quantity: 5000PCS	

LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non -infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[YAGEO:](#)

[SJD16A10L01](#) [SJD16A12L01](#) [SJD16A15L01](#) [SJD16A07L01](#)