







MD	Description	Please follow Pulse Limits for the hazardous substances (RoHS, halogens) in the document "Pulse Hazardous Substances (HS) Limits (RPG002-03)" and "Vendor Survey Questionnaire, Material Composition (LDM-SAF-L0040)".	Reliability Test Spec according to WIHS7.5.33 (Reliability Test Working Instruction) Default test standard is Test Standard A if no definition			
P3	Change the Logo					




NOTES:

1. MATERIAL: SUS301-H
2. NO CRACK APPEARS ON CONTACT BALL SHAPE.
3. NO LINES APPEARS ON BENDING AREA.
4. ALL UNSPECIFIED RADII TO BE 0.05 MAXIMUM .
5. BURR:0.03MAX;CUMBER:1.5MM MAX/500MM; TWIST:20°/500MM.
6. PRE-LOAD FORCE:0.3N ON CONTACT POINT
7. PLATING: 5u"MIN GOLD PLATING ON CONTACT AREA, GOLD FLASH PLATING ON SOLDER AREA, 50~100u" NICKEL PLATING OVER ALL



RECOMMENDED PCB LAYOUT  
TOLERANCE ±0.05MM



STATE AT WORKING HIGHT 0.45mm

Confidential  
This is a proprietary information of Pulse Suzhou.  
No reproduction/copying is allowed without permission.

Functional Characteristics Key (Cpk requirement : Cpk) >  
> Process Capability Studies required ( total pcs )  
> Ongoing Statistical Process Control Required ( total pcs )  
> Critical dimension need to be measured, no CPK requirement ( total pcs )

- .X± 0.15
- .XX± 0.10
- .XXX± 0.05
- X: ± 5°

PULSE (SUZHOU) WIRELESS PRODUCTS CO.LTD.

99 HUOJU RD. SUZHOU  
NEW DISTRICT  
215009  
P.R.CHINA

PRODUCT(S)  
SW0166N

ITEM  
TX13003-001(CLIP)

THIRD ANGLE PROJECTION	SHEET NUMBER		1 / 1					
	GENERAL TOLERANCE							
SCALE	CUSTOMER NUMBER							
	DESIGN	CHRIS	Nov-22-17					
	CHECKED	MARK	Nov-22-17					
DOCUMENT NUMBER	APPROVED	JAMES	Nov-22-17	P3	March-07-19	CHRIS		
	PART VERSION	P01	DOCUMENT VERSION	P3	P2	SEP-22-18	CHRIS	
				P1	Nov-22-17	CHRIS		
				MOD	DATE	NAME		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[SW0166N](#)