

# DATA SHEET

## MELF METAL FILM RESISTORS

High Power  
MMP Series

$\pm 1\%$ ,  $\pm 2\%$ ,  $\pm 5\%$

1W AND 2W

RoHS compliant & Halogen Free



**YAGEO**

Product specification – August 13, 2021 V.0





## APPLICATIONS

- All general purpose applications
- Power applications
- Energy meter

## FEATURES

- AEC-Q200 qualified
- MELF, SMD package
- Excellent pulse withstanding capability
- Ultra miniature size
- Higher power rating
- RoHS compliant and halogen free

## ORDERING INFORMATION

Part number of the power MELF metal film resistor is identified by the series, power rating, tolerance, packing, temperature coefficient and resistance value.

## PART NUMBER

<u>MMP</u>	<u>100</u>	<u>J</u>	<u>R</u>	<u>-</u>	<u>100R</u>
(1)	(2)	(3)	(4)	(5)	(6)

### (1) SERIES

MMP Series

### (2) POWER RATING

100 = 1W

200 = 2W

### (3) TOLERANCE

F =  $\pm 1\%$

J =  $\pm 5\%$

G =  $\pm 2\%$

- = Based on spec.

### (4) PACKAGING

R = Reel Pack

### (5) TEMPERATURE COEFFICIENT OF RESISTANCE

E =  $\pm 50\text{ppm}/^\circ\text{C}$

- = Based on spec.

F =  $\pm 100\text{ppm}/^\circ\text{C}$

### (6) RESISTANCE VALUE


E24 & E96 Series value

Example:

1R = 1 $\Omega$ , 10K = 10,000 $\Omega$ , 1M = 1,000,000 $\Omega$

**DIMENSIONS**


Unit: mm




Ultra Miniature	L	D	C Min.
MMP100	$5.90 \pm 0.2$	$2.20 \pm 0.1$	0.5
MMP200	$8.50 \pm 0.2$	$3.20 \pm 0.2$	0.5

**SUGGESTED PAD LAYOUT**

Unit: mm



Ultra Miniature	Soldering Mode	L Min.	P	W Min.
MMP100	Reflow	2.0	$3.0 \pm 0.1$	3.0
	Wave	2.5	$3.0 \pm 0.1$	3.0
MMP200	Reflow	2.3	$5.5 \pm 0.2$	4.0
	Wave	2.8	$5.5 \pm 0.2$	4.0

**DERATING CURVE**

**ELECTRICAL CHARACTERISTICS**

CHARACTERISTICS	MMP100	MMP200
Power Rating at 70 °C	1W	2W
Maximum Working Voltage	350V	350V
Maximum Overload Voltage	700V	700V
Voltage Proof on Insulation	500V	500V
Resistance Range	1Ω ~ 1MΩ & 0Ω for E24 & E96 series value	
Operating Temp. Range	- 55°C to +155°C	
Temperature Coefficient	±50ppm/°C, ±100ppm/°C	

Note: For resistance value out of above range is by request.

**TEST AND REQUIRMENTS**

TEST	TEST METHOD	PROCEDURE	APPRAISE
Short Time Overload	IEC 60115-1 4.13	2.5 times RCWV for 5 sec.(Not more than maximum overload voltage)	±0.5%+0.05Ω
Voltage Proof on Insulation	IEC 60115-1 4.7	In V-Block for 60 sec. test voltage as above table	No Breakdown
Temperature Coefficient	IEC 60115-1 4.8	Between -55°C to +155°C	By Type
Insulation Resistance	IEC 60115-1 4.6	In V-Block for 60 sec.	>10,000MΩ
Solderability	IEC 60115-1 4.17	245±5°C for 3±0.5 Sec.	95% Min. coverage
Solvent Resistance of Marking	IEC 60115-1 4.30	IPA for 5±0.5 Min. with ultrasonic	No deterioration of coatings and markings
Periodic-pulse Overload	IEC 60115-1 4.39	4 times RCWV 10,000 cycles (1 Sec. on, 25 Sec.off)	±1.0%+0.05Ω
Damp Heat Steady State	IEC 60115-1 4.24	40±2°C,90-95% RH for 56 days, loaded with 0.1 times RCWV	±2.0%+0.05Ω
Endurance at 70°C	IEC 60115-1 4.25	70±2°C at RCWV(or Umax., whichever less) for 1,000 Hr.(1.5 Hr.on,0.5 Hr. off)	±2.0%+0.05Ω
Temperature Cycling	IEC 60115-1 4.19	➔ -55°C ➔ Room Temp. ➔ +155°C Room Temp.(5 cycles)	±0.75%+0.05Ω
Resistance to Soldering Heat	IEC 60115-1 4.18	260±3°C for 10±1 Sec., immersed to a point 3±0.5mm from the body	±0.5%+0.05Ω

Note:

### RCWV (Rated Continuous Working Voltage ):

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V = \sqrt{P \times R}$$

or max. working voltage whichever is less

Where

V=Continuous rated DC or  
AC (rms) working voltage (V)

P=Rated power (W)

R=Resistance value ( $\Omega$ )

### PACKING

TYPE

Unit: piece

Ultra Miniature	Packaging	Quantity Per Reel
MMP100	7"	2,000
MMP200	13"	2,500

**MARKING**

3-BAND-CODE

 $\pm 2\%$ ,  $\pm 5\%$ 

COLOR	1st BAND	2nd BAND	3rd BAND	MULTIPLIER
BLACK	0	0	0	1 $\Omega$
BROWN	1	1	1	10 $\Omega$
RED	2	2	2	100 $\Omega$
ORANGE	3	3	3	1K $\Omega$
YELLOW	4	4	4	10K $\Omega$
GREEN	5	5	5	100K
BLUE	6	6	6	1M $\Omega$
VIOLET	7	7	7	10M $\Omega$
GREY	8	8	8	0.001 $\Omega$
WHITE	9	9	9	0.0001 $\Omega$
GOLD				0.1 $\Omega$
SILVER				0.01 $\Omega$

 $\pm 1\%$ 

5-BAND-CODE



**REVISION HISTORY**

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 0	Aug.2, 2021	-	- First issue of this specification

*“ Yageo reserves all the rights for revising the content of this datasheet without further notification, as long as the products itse lf are unchanged. Any product change will be announced by PCN.”*

## LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, “YAGEO”), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non-infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial, automotive, and/or COTS grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## YAGEO:

[MMP100FRE300R](#) [MMP100FRE390R](#) [MMP100FRE33R](#) [MMP100FRF100K](#) [MMP100FRF56K](#) [MMP100FRF10R](#)  
[MMP100FRE10K](#) [MMP100FRF1K](#) [MMP100FRF510R](#) [MMP100FRE51R](#) [MMP100FRF100R](#) [MMP100FRE2K4](#)  
[MMP100FRE464K](#) [MMP100FRE11R](#) [MMP100FRE1M](#) [MMP100FRF330R](#) [MMP100FRE4K02](#) [MMP100FRE2K7](#)  
[MMP100FRE470R](#) [MMP100FRE15K](#) [MMP100FRE330K](#) [MMP100FRE10R](#) [MMP100FRE4K7](#) [MMP100FRE12R](#)  
[MMP100FRE909K](#) [MMP100FRE2M2](#) [MMP100FRE8K2](#) [MMP100FRE390K](#) [MMP100FRE560K](#) [MMP100FRE3K3](#)  
[MMP100JR-0R1](#) [MMP100FRE27R](#) [MMP100FRE1K](#) [MMP100FRE20R](#) [MMP100FRE22R](#) [MMP100FRE560R](#)  
[MMP100FRE680R](#) [MMP100FRE39R](#) [MMP100FRE1M5](#) [MMP100FRE1K8](#) [MMP100FRE6K8](#) [MMP100FRE220K](#)  
[MMP100FRE2K2](#) [MMP100FRE3K9](#) [MMP100FRE68K](#) [MMP100FRE3M3](#) [MMP100FRE47R](#) [MMP100FRE4M7](#)  
[MMP100FRE200R](#)