


Metal Film Resistors

Professional Type

Miniature Style [MF0 Series]



INTRODUCTION


The MF0 Series Metal Film Professional Resistors are manufactured using a vacuum sputtering system to deposit multiple layers of mixed metal alloys and passivative materials onto a carefully treated high grade ceramic substrate. After a helical groove has been cut in the resistive layer; tinned connecting leads of electrolytic copper are welded to the end-caps. The resistors are coated with layers of blue color lacquer.

FEATURES

Power Rating	0.4W, 0.6W
Resistance Tolerance	$\pm 0.5\%$, $\pm 1\%$, $\pm 2\%$, $\pm 5\%$,
T.C.R.	$\pm 50\text{ppm}/^{\circ}\text{C}$, $\pm 100\text{ppm}/^{\circ}\text{C}$

DERATING CURVE

For resistors operated in ambient temperatures above 70°C , power rating must be derated in accordance with the curve below.



DIMENSIONS



Unit: mm

STYLE	DIMENSION			
Miniature	L	øD	H	ød
MF0204	3.4 ± 0.3	1.9 ± 0.2	28 ± 2.0	0.45 ± 0.05
MF0207	6.3 ± 0.5	2.4 ± 0.2	28 ± 2.0	0.55 ± 0.05

Note:

ELECTRICAL CHARACTERISTICS

STYLE	MF0204	MF0207
Power Rating at 70°C	0.4W	0.6W
Maximum Working Voltage	250V	350V
Maximum Overload Voltage	500V	700V
Voltage Proof on Insulation	300V	500V
Resistance Range	1Ω - 4M7Ω & 0Ω for E24 & E96 series value	
Operating Temp. Range	-55°C to +155°C	
Temperature Coefficient	±50ppm/°C , ±100ppm/°C	

Note: Special value is available on request

ENVIRONMENTAL CHARACTERISTICS

PERFORMANCE TEST	TEST METHOD		APPRAISE
Short Time Overload	IEC 60115-1 4.13	2.5 times RCWV for 5 sec. (Not more than maximum Overload Voltage)	±0.25%+0.05Ω
Voltage Proof on Insulation	IEC 60115-1 4.7	In V-Block for 60 sec., test voltage as above table	No Breakdown
Temperature Coefficient	IEC 60115-1 4.8	Between -55°C to +155°C	By type
Insulation Resistance	IEC 60115-1 4.6	in V-block for 60 Sec.	>10,000MΩ
Solderability	IEC 60115-1 4.17	245±5°C for 3±0.5 Sec.	95% Min. coverage
Solvent Resistance of Marking	IEC 60115-1 4.30	IPA for 5±0.5 Min. with ultrasonic	No deterioration of coatings and markings
Robustness of Terminations	IEC 60115-1 4.16	Direct load for 10 Sec. in the direction of the terminal leads	≥2.5kg (24.5N)
Periodic-pulse Overload	IEC 60115-1 4.39	4 times RCWV 10,000 cycles (1 Sec. on, 25 Sec. off)	±1.0%+0.05Ω
Damp Heat Steady State	IEC 60115-1 4.24	40±2°C, 90-95% RH for 56 days, loaded with 0.1 times RCWV	±1.5%+0.05Ω
Endurance at 70°C	IEC 60115-1 4.25	70±2°C at RCWV (or Umax., Whichever less) for 1,000 Hr. (1.5Hr: on, 0.5Hr: Off)	±1.5%+0.05Ω
Temperature Cycling	IEC 60115-1 4.19	-55°C ⇒ Room Temp. ⇒ +155°C ⇒ Room Temp. (5 cycles)	±0.75%+0.05Ω
Resistance to Soldering Heat	IEC 60115-1 4.18	260±3°C for 10±1 Sec., immersed to a point 3±0.5mm from the body	±0.25%+0.05Ω

Note: RCWV(Rated Continuous Working Voltage) = $\sqrt{\text{Power Rating} \times \text{Resistance Value}}$ or Max. working voltage listed above, whichever less.

Revision: 2020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Yageo:

[MF0207JT-52-0R33](#) [MF0207BTD52-11K](#) [MF0207FTF52-0R82](#) [MF0207JT-52-0R68](#) [MF0207JT-52-0R39](#)
[MF0207FTE52-6M9](#) [MF0207JR-52-0R68](#) [MF0207BTD52-6K8](#) [MF0207JR-52-0R47](#) [MF0207BTD52-30K](#)
[MF0207BTD52-6K42](#) [MF0207JT-52-0R56](#) [MF0207BTD52-15R](#) [MF0207JR-52-0R24](#) [MF0207FTF52-0R12](#)
[MF0207BTD52-2K7](#) [MF0207JT-52-0R3](#) [MF0207JR-52-0R82](#) [MF0207BTD52-330R](#) [MF0207JR-52-0R75](#)
[MF0207BTD52-20K](#) [MF0207JR-52-0R33](#) [MF0207BTD52-5K6](#) [MF0207GT-52-0R82](#) [MF0207BTD52-150K](#)
[MF0207BTD52-330K](#) [MF0207JR-52-0R39](#) [MF0207BTD52-40K2](#) [MF0207JR-52-0R62](#) [MF0207JR-52-0R51](#)
[MF0207FTE52-10M](#) [MF0207BTD52-120K](#) [MF0207BTD52-470K](#) [MF0207JR-52-0R91](#) [MF0207BTD52-1K](#)
[MF0207BTD52-2K2](#) [MF0207BTD52-25R5](#) [MF0204FTE52-165RSM](#) [MF0207FTE52-100KSM](#) [MF0204FTE52-120KSM](#)
[MF0207FRE52-165K](#)

YAGEO:

[MF0204FTE52-13R](#) [MF0204FTE52-22KSM](#) [MF0204FTE52-2R71](#) [MF0204FTE52-3M3](#) [MF0207BTD52-110K](#)
[MF0207BTD52-113K](#) [MF0207BTD52-11R](#) [MF0207BTD52-180R](#) [MF0207BTD52-18K](#) [MF0207BTD52-249R](#)
[MF0207BTD52-24R9](#) [MF0207BTD52-270R](#) [MF0207BTD52-34K](#) [MF0207BTD52-360K](#) [MF0207BTD52-365K](#)
[MF0207BTD52-43R](#) [MF0207BTD52-47R](#) [MF0207BTD52-576R](#) [MF0207BTD52-620K](#) [MF0207BTD52-82R](#)
[MF0204DRE52-24R3](#) [MF0204FTE52-120RSM](#) [MF0204FTE52-16R9](#) [MF0204FTE52-1M3](#) [MF0204FTE52-1R3](#)
[MF0204FTE52-2M71](#) [MF0204FTE52-2R4](#) [MF0204FTE52-5M1](#) [MF0204FTE52-5M62](#) [MF0204FTE52-1R69](#)
[MF0204FTE52-271R](#) [MF0204FTE52-31R6](#) [MF0204FTE52-3M6](#) [MF0204FTE52-40R2](#) [MF0204FTE52-43R](#)
[MF0204FTE52-4M87](#) [MF0204FTE52-4R32](#) [MF0204FTE52-910R](#) [MF0207BTD52-226R](#) [MF0207BTD52-2K05](#)
[MF0207BTD52-33K](#) [MF0207BTD52-37K4](#) [MF0207BTD52-402K](#) [MF0207BTD52-680K](#) [MF0204FTE52-16K](#)
[MF0204FTE52-23R7](#) [MF0204FTE52-300K](#) [MF0204FTE52-30R](#) [MF0204FTE52-3K9SM](#) [MF0204FTE52-3KSM](#)
[MF0204FTE52-3M](#) [MF0204FTE52-3M01](#) [MF0204FTE52-48R7](#) [MF0204FTE52-5R1](#) [MF0204FTE52-61R9](#)
[MF0204FTE52-620K](#) [MF0204FTE52-7M5](#) [MF0204FTE52-80R6](#) [MF0204DRE52-6K2](#) [MF0204FRE52-397K](#)
[MF0204FTE52-1M6](#) [MF0204FTE52-1M8](#) [MF0204FTE52-1R1](#) [MF0204FTE52-29R4](#) [MF0204FTE52-3R92](#)
[MF0204FTE52-50K](#) [MF0204FTE52-510K](#) [MF0204FTE52-6K8SM](#) [MF0204FTE52-9M09](#) [MF0207BTD52-15K4](#)
[MF0207BTD52-20R](#) [MF0207BTD52-2K21](#) [MF0207BTD52-2K49](#) [MF0207BTD52-39R](#) [MF0207BTD52-3K](#)
[MF0207BTD52-510K](#) [MF0207BTD52-549K](#) [MF0207BTD52-68R](#) [MF0204FTE52-62K](#) [MF0204FTE52-6R8](#)
[MF0204FTE52-76R8](#) [MF0204FTE52-9R1](#) [MF0204JR-52-0R82](#) [MF0207BTD52-12R](#) [MF0207BTD52-160R](#)
[MF0207BTD52-22K3](#) [MF0207BTD52-332K](#) [MF0207BTD52-43K](#) [MF0207BTD52-499R](#) [MF0207BTD52-4K7](#)

[MF0207BTD52-560R](#) [MF0204FTE52-15KSM](#) [MF0204FTE52-16R](#) [MF0204FTE52-20R5](#) [MF0204FTE52-24R](#)
[MF0204FTE52-2R7](#) [MF0204FTE52-47R5](#) [MF0204FTE52-4M32](#) [MF0204FTE52-4M64](#) [MF0204FTE52-5R11](#)