

Melf Metal Film Resistors

High Power Type

Ultra Miniature Style [MMP Series]



INTRODUCTION


The MMP Series Melf Metal Film High Power Resistors are manufactured using a vacuum sputtering system to deposit multiple layers of mixed metal alloys and passivative materials onto a carefully treated high grade ceramic substrate. SMD enabled structure and high power in small packages.

FEATURES

Power Rating	1W, 2W
Resistance Tolerance	$\pm 1\%$, $\pm 2\%$, $\pm 5\%$
T.C.R.	$\pm 50\text{ppm}/^{\circ}\text{C}$, $\pm 100\text{ppm}/^{\circ}\text{C}$


DERATING CURVE

For resistors operated in ambient temperatures above 70°C , power rating must be derated in accordance with the curve below.



DIMENSIONS

Unit: mm



STYLE	DIMENSION		
Ultra Miniature	L	D	C Min.
MMP100	5.9 ± 0.2	2.2 ± 0.1	0.5
MMP200	8.5 ± 0.2	3.2 ± 0.2	0.5

Note:

ELECTRICAL CHARACTERISTICS

STYLE	MMP100	MMP200
Power Rating at 70°C	1W	2W
Maximum Working Voltage	350V	
Maximum Overload Voltage	700V	
Voltage Proof on Insulation	500V	
Resistance Range	1Ω - 1MΩ & 0Ω for E24 & E96 series value	
Operating Temp. Range	-55°C to +155°C	
Temperature Coefficient	±50ppm/°C, ±100ppm/°C	

Note: Special value is available on request

ENVIRONMENTAL CHARACTERISTICS

PERFORMANCE TEST	TEST METHOD		APPRAISE
Short Time Overload	IEC 60115-1 4.13	2.5 times RCWV for 5 sec. (Not more than maximum Overload Voltage)	±0.5%+0.05Ω
Voltage Proof on Insulation	IEC 60115-1 4.7	In V-Block for 60 sec., test voltage as above table	No Breakdown
Temperature Coefficient	IEC 60115-1 4.8	Between -55°C to +155°C	By type
Insulation Resistance	IEC 60115-1 4.6	in V-block for 60 Sec.	>10,000MΩ
Solderability	IEC 60115-1 4.17	245±5°C for 3±0.5 Sec.	95% Min. coverage
Solvent Resistance of Marking	IEC 60115-1 4.30	IPA for 5±0.5 Min. with ultrasonic	No deterioration of coatings and markings
Periodic-pulse Overload	IEC 60115-1 4.39	4 times RCWV 10,000 cycles (1 Sec. on, 25 Sec. off)	±1.0%+0.05Ω
Damp Heat Steady State	IEC 60115-1 4.24	40±2°C, 90-95% RH for 56 days, loaded with 0.1 times RCWV	±2.0%+0.1Ω
Endurance at 70°C	IEC 60115-1 4.25	70±2°C at RCWV (or Umax., Whichever less) for 1,000 Hr. (1.5Hr: on, 0.5Hr: Off)	±2.0%+0.1Ω
Temperature Cycling	IEC 60115-1 4.19	-55°C ⇄ Room Temp. ⇄ +155°C ⇄ Room Temp. (5 cycles)	±0.75%+0.05Ω
Resistance to Soldering Heat	IEC 60115-1 4.18	260±3°C for 10±1 Sec., immersed to a point 3±0.5mm from the body	±0.5%+0.05Ω

Note: RCWV(Rated Continuous Working Voltage) = $\sqrt{\text{Power Rating} \times \text{Resistance Value}}$ or Max. working voltage listed above, whichever less.

Revision: 2020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Yageo:

[MMP100FRE1R](#) [MMP100FRE270RSJ](#) [MMP100FRE3R3](#) [MMP100FRE4R7](#) [MMP100FRE2R2](#) [MMP100FRE100KSJ](#)
[MMP100FRE2R7](#) [MMP100FRE150KSJ](#) [MMP100FRE1K5SJ](#) [MMP100FRE2R21](#) [MMP100FRE3R9](#)
[MMP100FRE1R5](#) [MMP100FRE51KSJ](#) [MMP100FRE6R8](#) [MMP100FRE1R3](#) [MMP100FRE220RSJ](#)
[MMP100FRE5K6SJ](#) [MMP100FRE5R1](#) [MMP100FRE5R6](#) [MMP100FRE1K2SJ](#) [MMP100-R-0R](#) [MMP100FRE2R](#)
[MMP100FRE3R](#) [MMP100FRE9R1](#) [MMP100FRE1R6](#) [MMP100FRE10KSJ](#) [MMP100FRE2R49](#) [MMP100FRE0R](#)
[MMP100FRE120RSJ](#) [MMP100FRE2R43](#) [MMP100FRE36KSJ](#) [MMP100FRE86R6](#) [MMP100FRE270K](#)
[MMP100FRE56K](#) [MMP100FRE62R](#) [MMP100FRE750K](#) [MMP100FRF750K](#) [MMP100FRE221R](#) [MMP100FRE226R](#)
[MMP100FRE5K1](#) [MMP100FRE75R](#) [MMP100FRE7K5](#) [MMP100FRE220R](#) [MMP100FRE3K09](#) [MMP100FRE470K](#)
[MMP100FRE95R3](#) [MMP100FRE237R](#) [MMP100FRE75K](#) [MMP100FRE24K3](#) [MMP100FRE36K](#) [MMP100FRE51K](#)
[MMP100FRE73R2](#) [MMP100FRF1K1](#) [MMP100FRF1K5](#) [MMP100FRE2K](#) [MMP100FRE47K](#) [MMP100FRF1M](#)
[MMP100FRF2K2](#) [MMP100FRF909K](#) [MMP100FRE270R](#) [MMP100FRE56R](#) [MMP100FRF47K](#) [MMP100FRE5K6](#)
[MMP100FRE22K](#) [MMP100FRE280R](#) [MMP100FRE510K](#) [MMP100FRE59R](#) [MMP100FRE820K](#) [MMP100FRE93R1](#)
[MMP100FRE20K](#) [MMP100FRE240R](#) [MMP100FRE243R](#) [MMP100FRE330R](#) [MMP100FRE3K6](#) [MMP100FRE76R8](#)
[MMP100FRE80R6](#) [MMP100FRF22K](#) [MMP100FRE200K](#) [MMP100FRE249R](#) [MMP100FRE4K02](#) [MMP100FRE64R9](#)
[MMP100FRE82R](#)

YAGEO:

[MMP100FRE499K](#)