



Product: [8466](#)

Electronic, 12 C #18 Str TC, PVC Ins, PVC Jkt, CMG

Request Sample

Product Description

Electronic, 12 Conductor 18AWG (19x30) Tinned Copper, PVC Insulation, PVC Outer Jacket, CMG

Technical Specifications

Product Overview

| | |
|------------------------|---|
| Suitable Applications: | low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring |
|------------------------|---|

Construction Details

Conductor

| Element | No. of Elements | Size | Stranding | Material |
|--------------|-----------------|--------|-----------|--------------------|
| Conductor(s) | 12 | 18 AWG | 19x30 | TC - Tinned Copper |

Insulation

| Element | Material | Nom. Thickness | Nom. Insulation Diameter | Color Code |
|--------------|--------------------------|--------------------|--------------------------|--|
| Conductor(s) | PVC - Polyvinyl Chloride | 0.018 in (0.46 mm) | 0.080 in (2.0 mm) | Black, White, Red, Green, Orange, Blue, White/Black Stripe, Red/Black Stripe, Green/Black Stripe, Orange/Black Stripe, Blue/Black Stripe, Black/White Stripe |

Outer Jacket

| Material | Nom. Thickness | Nom. Diameter |
|-----------------------------------|-------------------|--------------------|
| PVC - Polyvinyl Chloride | 0.040 in (1.0 mm) | 0.412 in (10.5 mm) |
| Overall Cable Diameter (Nominal): | | 0.412 in (10.5 mm) |

Electrical Characteristics

| Electricals | | | |
|----------------------------------|--------------------|-------------------------------|--------------------------------|
| Element | Nom. Conductor DCR | Nom. Capacitance Cond-to-Cond | Max. Current |
| Conductor(s) | 7.13 Ohm/1000ft | 26 pF/ft (85 pF/m) | 9.8 Amps per Conductor at 30°C |
| Voltage | | | |
| UL Voltage Rating | | | |
| 300 V (CMG), 300 V (UL AWM 2598) | | | |

Mechanical Characteristics

| Temperature | |
|--------------------|-------------------|
| UL Temperature | Operating |
| 60°C | -20°C to +60°C |
| Bend Radius | |
| Stationary Min. | Installation Min. |
| 4.1 in (100 mm) | 4.1 in (100 mm) |
| Max. Pull Tension: | |
| 296 lbs (134 kg) | |
| Bulk Cable Weight: | |
| 113 lbs/1000ft | |

Standards and Compliance

| | |
|----------------------------------|---|
| Environmental Suitability: | Indoor |
| Flammability / Reaction to Fire: | UL 1685 FT4 Loading, FT4, IEC 60332-1-2 |
| CPR Compliance: | CPR Euroclass: Eca |
| NEC / UL Compliance: | Article 800, CMG |
| AWM Compliance: | AWM 2598 |
| CEC / C(UL) Compliance: | CMG |
| European Directive Compliance: | EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE) |
| UK Regulation Compliance: | UKCA Mark |
| APAC Compliance: | China RoHS II (GB/T 26572-2011) |

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.503 Revision Date: 01-20-2023 |
|----------------------|--|

Part Numbers

Variants

| Item # | Color | Putup Type | Length | UPC | Footnote |
|--------------|--------|------------|----------|--------------|----------|
| 8466 060100 | Chrome | Reel | 100 ft | 612825208297 | |
| 8466 060250 | Chrome | Reel | 250 ft | 612825208310 | C |
| 8466 060500 | Chrome | Reel | 500 ft | 612825208327 | C |
| 8466 0601000 | Chrome | Reel | 1,000 ft | 612825208303 | C |
| 8466 0605000 | Chrome | Reel | 5,000 ft | 612825208334 | C Z |

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[8466 060250](#)