


Wirewound Resistors

Flame-Proof & Non-Inductive Type

Normal & Miniature Style [NKN Series]



INTRODUCTION


The resistor element is a resistive wire which is wound in a single layer on a ceramic rod, with tinned connecting wires of electrolytic copper welded to the end-caps. The ends of the resistive wire are connected to the caps by welding. The resistors are coated with layers of green color flame-proof lacquer. The 5th color band is black to represent NKN series.

FEATURES

Power Rating	1/2W, 1W, 2W, 3W, 4W, 5W, 7W
Resistance Tolerance	$\pm 2\%$, $\pm 5\%$
T.C.R.	$\pm 300\text{ppm}/^\circ\text{C}$
Flameproof Multi-layer Coating Meets	UL-94V-0
Flameproof Feature Meets Overload Test	UL-1412


DERATING CURVE

For resistors operated in ambient temperatures above 40°C , power rating must be derated in accordance with the curve below.



DIMENSIONS

Unit: mm



5th color code: black

STYLE		DIMENSION			
Normal	Miniature	L	øD	H	ød
NKN50	NKN1WS	9.0 ± 0.5	$3.5 + 0.6/-0.3$	26 ± 2.0	0.55 ± 0.05
NKN100	NKN2WS	11.5 ± 1.0	$4.6 + 1.0/-0.5$	35 ± 2.0	0.8 ± 0.05
NKN200	NKN3WS	15.5 ± 1.0	$5.2 + 1.0/-0.5$	33 ± 2.0	0.8 ± 0.05
NKN300					
NKN400	NKN5WS	17.5 ± 1.0	6.5 ± 1.0	32 ± 2.0	0.8 ± 0.05
NKN500	NKN7WS	24.5 ± 1.0	8.5 ± 1.0	38 ± 2.0	0.8 ± 0.05

ELECTRICAL CHARACTERISTICS

NORMAL STYLE

STYLE	NKN-50	NKN100	NKN200	NKN300	NKN400	NKN500
Power Rating at 40°C				3W	4W	5W
Power Rating at 70°C	1/2W	1W	2W			
Maximum working voltage	$\sqrt{P \times R}$					
Voltage Proof on Insulation	250V	400V				
Resistance Range	0.08Ω - 15Ω	0.1Ω - 40Ω	0.1Ω - 90Ω	0.1Ω - 120Ω		0.18Ω - 220Ω
Operating Temp. Range	-40°C to +200°C					
Temperature Coefficient	±300ppm/°C					

Note: Special value is available on request

MINIATURE STYLE

STYLE	NKNIWS	NKN2WS	NKN3WS	NKN5WS	NKN7WS
Power Rating at 40°C				5W	7W
Power Rating at 70°C	1W	2W	3W		
Maximum working voltage	$\sqrt{P \times R}$				
Voltage Proof on Insulation	250V	400V			
Resistance Range	0.08Ω - 15Ω	0.1Ω - 40Ω	0.1Ω - 90Ω	0.1Ω - 120Ω	0.18Ω - 220Ω
Operating Temp. Range	-40°C to +200°C				
Temperature Coefficient	±300ppm/°C				

Note: Special value is available on request

ENVIRONMENTAL CHARACTERISTICS

PERFORMANCE TEST	TEST METHOD		APPRAISE
Short Time Overload	IEC 60115-1 4.13	10 times rated power for 5 Sec.	±2.0%+0.05Ω
Voltage Proof on Insulation	IEC 60115-1 4.7	In V-Block for 60 sec., test voltage as above table	No Breakdown
Temperature Coefficient	IEC 60115-1 4.8	Between -40°C to +155°C	By type
Insulation Resistance	IEC 60115-1 4.6	in V-block for 60 Sec.	>100MΩ
Solderability	IEC 60115-1 4.17	245±5°C for 3±0.5 Sec.	95% Min. coverage
Solvent Resistance of Marking	IEC 60115-1 4.30	IPA for 5±0.5 Min. with ultrasonic	No deterioration of coatings and markings
Robustness of Terminations	IEC 60115-1 4.16	Direct load for 10 Sec. in the direction of the terminal leads	≥2.5kg (24.5N)
Damp Heat Steady State	IEC 60115-1 4.24	40±2°C, 90-95% RH for 56 days, loaded with 0.1 times RCWV	±5.0%+0.05Ω
Endurance at 70°C	IEC 60115-1 4.25	70±2°C at RCWV (or Umax., Whichever less) for 1,000 Hr. (1.5Hr: on, 0.5Hr: Off)	±5.0%+0.05Ω
Temperature Cycling	IEC 60115-1 4.19	-55°C ⇄ Room Temp. ⇄ +155°C ⇄ Room Temp. (5 cycles)	±1.0%+0.05Ω
Resistance to Soldering Heat	IEC 60115-1 4.18	260±3°C for 10±1 Sec., immersed to a point 3±0.5mm from the body	±1.0%+0.05Ω
Accidental Overload Test	IEC 60115-1 4.26	4 times RCWV for 1 Min.	No evidence of flaming or arcing

Note: Rated Continuous Working Voltage (RCWV) = $\sqrt{\text{Power Rating} \times \text{Resistance Value}}$ or Max. working voltage listed above, whichever less.

Revision: 2020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Yageo:

[NKN3WSJT-73-0R04](#) [NKN3WSJT-73-0R05](#) [NKN200JT-73-0R43](#) [NKN2WSJT-52-0R68](#) [NKN2WSJT-73-0R3](#)
[NKN3WSJT-73-0R027](#) [NKN2WSJT-PN0R075](#) [NKN1WSJT-52-3R](#) [NKN200JT-73-0R56](#) [NKN2WSJT-73-0R13](#)
[NKN2WSJT-73-0R51](#) [NKN2WSJT-52-0R43](#) [NKN2WSJT-52-0R5](#) [NKN2WSJT-52-0R56](#) [NKN2WSJT-PN0R068](#)
[NKN2WSJT-52-0R26](#) [NKN2WSJT-73-0R12](#) [NKN2WSJT-73-0R14](#) [NKN2WSJT-73-0R43](#) [NKN2WSJT-52-0R11](#)
[NKN2WSJT-52-0R12](#) [NKN2WSJT-73-0R5](#) [NKN1WSJT-52-1R8](#) [NKN200JT-73-0R5](#) [NKN200JT-73-0R62](#)
[NKN2WSJT-52-0R22](#) [NKN2WSJT-73-0R11](#) [NKN2WSJT-73-0R47](#) [NKN3WSJT-73-0R043](#) [NKN2WSJT-52-0R17](#)
[NKN2WSJT-73-0R1](#) [NKN2WSJT-73-0R62](#) [NKN2WSJT-73-0R75](#) [NKN2WSJT-PN0R082](#) [NKN200JT-73-15R](#)
[NKN2WSJT-52-0R1](#) [NKN2WSJT-52-0R15](#) [NKN200JT-73-0R24](#) [NKN200JT-73-0R3](#) [NKN2WSJT-52-0R13](#)
[NKN2WSJT-52-0R14](#) [NKN2WSJT-73-0R19](#) [NKN2WSJT-73-0R22](#) [NKN1WSJT-52-7R5](#) [NKN200JT-73-0R12](#)
[NKN2WSJT-52-0R3](#) [NKN2WSJT-52-0R36](#) [NKN2WSJT-73-0R15](#) [NKN2WSJT-73-0R17](#) [NKN2WSJT-73-0R37](#)
[NKN200JT-73-0R1](#) [NKN200JT-73-0R39](#) [NKN2WSJT-52-0R27](#) [NKN2WSJT-52-0R62](#) [NKN2WSJT-52-0R91](#)
[NKN2WSJT-73-0R39](#) [NKN1WSJT-52-1R5](#) [NKN200JT-73-0R36](#) [NKN1WSJT-52-1R6](#) [NKN1WSJT-52-3R2](#)
[NKN200JT-73-0R75](#) [NKN200JT-73-10R](#) [NKN2WSJT-52-0R2](#) [NKN2WSJT-52-0R24](#) [NKN200JT-73-0R33](#) [NKN200JT-](#)
[73-30R](#) [NKN2WSJT-52-0R18](#) [NKN2WSJT-52-0R33](#) [NKN2WSJT-52-0R39](#) [NKN2WSJT-73-0R16](#) [NKN2WSJT-73-](#)
[0R28](#) [NKN2WSJT-73-0R33](#) [NKN2WSJT-73-0R68](#) [NKN3WSJT-73-0R02](#) [NKN200JT-73-0R22](#) [NKN200JT-73-0R27](#)
[NKN2WSJT-52-0R47](#) [NKN2WSJT-73-0R24](#) [NKN2WSJT-73-0R27](#) [NKN2WSJT-PN0R056](#) [NKN2WSJT-PN0R062](#)
[NKN1WSJT-52-1R](#) [NKN200JT-73-0R18](#) [NKN200JT-73-12R](#) [NKN2WSJT-52-0R16](#) [NKN2WSJT-73-0R18](#)
[NKN2WSJT-73-0R56](#) [NKN3WSJT-73-0R033](#) [NKN1WSJT-52-1R2](#)